




Application Tooling > Connector Seating Machines



Tooling Type: **Seating**

Features

Other

Tooling Type	Seating
--------------	---------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # CAT-472-Z12553
HM Receptacle Connector: Traditional Backplane, Coplanar, 2mm



TE Part # CAT-CAP-6T
CONNECTOR PRESS FIT MACHINE



TE Part # CAT-CAPI-6T
CONNECTOR PRESS FIT MACHINE



TE Part # CAT-CBP-5T
CBP-5T MKII Benchtop Press - Servo Electric



TE Part # CAT-CMP-10TMKII
CONNECTOR PRESS FIT MACHINE




TE Part # CAT-CMP-5TMKII
CONNECTOR PRESS FIT MACHINE




TE Part # CAT-CSP-5T
CSP-5T MKII Shuttle Electric Press Machine


Customers Also Bought




TE Part #3-647609-2
Polyester Vertical PCB Header: 2.54 mm, Unshrouded, No Mating Alignment




TE Part #280388-2
2X22P MODU II SHRD HDR,ST, 0.38AU




TE Part #9-2176401-5
3540 100R 5%




TE Part #2-2176329-6
CRGP 1210 1K2 1%




TE Part #3-5499374-2
A/L UNIV HDR 64P VERT SHT LAT BLUE



TE Part #224671-2
HM 2MM Z PK SEATING TL ASSY



TE Part #2-164306-1
32P.IEC-F MALE CONN



TE Part #2-1825138-6
A201SYWQ04

Documents

Datasheets & Catalog Pages

TE Press-Fit Machines

English

Instruction Sheets

CONNECTOR SEATING MACHINES DOCUMENTATION REQUEST



English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[318866-1](#)