

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED	01JUN2015	T.S	N.Y

WIRING SCHEMATIC

PIN NO.

NOTES:

- GENERAL TOLERANCE: ± 0.3 .
- CAN NOT BE MATED WITH CABLE.
- THE PACKAGE OF 1971153-1 REFER TO FGPI-1971153-1
THE PACKAGE OF 1971153-2 REFER TO FGPI-1971153-2

-	-	1	1	POLYAMID OF GLASS FIBER PLASTIC UL94V-0	HOUSING	2
-	-	1	1	COPPER ALLOY UNDER ALL SURFACE Ni PLATING 1.27 μm MIN. CONTACT AREA Au Plating 0.3 μm MIN.	CONTACT	1
-	-	-	-	MATERIAL/FINISH	PART NAME	ITEM NO

S08-037
PROJECT NO.

QTY REQD PER ASSY
-2 1971053-1

PARTS LIST

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25JUN2008 SAMUEL SUN		
DIMENSIONS: mm		CHK 26JUN2008 ROCK LV		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 27JUN2008 JULIAN ZHOU	NAME ASSEMBLY INDUSTRIAL MINI I/O BY-PASS CONNECTOR	
0 PLC \pm		PRODUCT SPEC 108-106021	RESTRICTED TO	
1 PLC ± 0.5		APPLICATION SPEC	SIZE A3	CAGE CODE 00779
2 PLC ± 0.13		WEIGHT 1.3g	DRAWING NO C-1971153	SCALE 5:1
3 PLC ± 0.013			SHEET 1 OF 1	REV B
4 PLC ± 0.0001				
ANGLES \pm				
MATERIAL		Customer Drawing		
FINISH				

1470-19 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1971153-1](#)