

THIS DRAWING IS UNPUBLISHED.
 RELEASED FOR PUBLICATION
 ALL RIGHTS RESERVED.

© COPYRIGHT - BY -

ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
A		REV PER ECO 14-000634	2-17-14	CT KH

D

C

B


A

D

C

B

A



1) FRONT & REAR INSULATOR: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.
 CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
 REAR GROMMET: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B, EXCEPT 4.6.6.1

2) TE LOGO, TE PART NO AND DATE CODE (YYWW) MARKED IN THIS AREA.
 TE PART NUMBER MAY BE MARKED EITHER ON THE REAR INSULATOR OR GROMMET.

3. DESCRIPTIVE PART NUMBER: GPRBE22VSA
 THIS INSERT CONTAINS: 16 CAVITIES FOR SIZE 20 SOCKET CONTACTS,
 6 CAVITIES FOR SIZE 16 SOCKET CONTACTS.

4. THIS PRODUCT IS SOLD BY TE CONNECTIVITY UNDER A LICENSE FROM RADIALL SA.

2000126-1

PART NUMBER



TE Connectivity

THIS DRAWING IS A CONTROLLED DOCUMENT.		NAME	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
DWN	2-17-14					
C.C. THOMAS	2-17-14	K. HOGAN	2-17-14	A200779	C=2000126	-
CHK	2-17-14					
APVD		K. HOGAN	2-17-14			
PRODUCT SPEC						
APPLICATION SPEC		-	-			
MATERIAL						
FINISH		1	-	4:1	1 OF 1	REV A
ANGLE						
CUSTOMER DRAWING		-	-	-	-	-
SCALE						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2000126-1](#)