



A 90-3144

RAW MAT. SPEC. WITH
PART NO. AND AMOUNT REQ'D.

*.068 X .035 DEEP KEYWAY.
.071*




*15-32 THRD'S.
32 PER INCH.*

*.34
±.005*

*9
16 - DIAM.*

*.210 DIAM.
±.05*



*4-#6-32 BINDING -
HEAD SCREWS 1/4" LONG*

BULLETIN



DIMENSIONS FOR 10 AMP. 250 V. ONE HOLE MTG. TOOL HANDLE SH.

A	16.F.L.	9.9.	2-8	DR. R. ARTIN	3-30	FIRST ASSEM. WHERE LISTED
B			62	CHK. L. SOTO	-61	A90-3143
C				BY J.E. BURGESS	4-4	SUP. S.
D				DO NOT SCALE DRAWING. WORK ACCORDING TO DIMENSIONS.		NON-INTERCHANGEABLE
E				STANDARD TOLERANCES 50-275 APPLY TO DIMENSIONS FOR WHICH TOLERANCES ARE NOT SPECIFIED.		SUP. D BY
F				ORDER NO.		NON-INTERCHANGEABLE - SURFACE COATING
CUTLER-HAMMER, INC. MILWAUKEE OH NEW YORK					8 53 11 57A	SCALE 1" = 1"
					A 90-3144	

NOTES:

1. SCREWS, WASHER AND HEX
NUTS SHIPPED UNASSEMBLED.

$.072 \pm .003$
 $-.004$ X $.035$ DEEP KEYWAY



TITLE DIMENSIONS FOR 10-20A TOGGLE WITH LEVER SEAL


ORDER NO. 9100N 76

BASIC SPECS. SUMMARY

A			DR. G. STORY	12/1/84	APP. <i>[Signature]</i> 12/1/84
B			CHK. C. Mardine	12/1/84	FIRST ASSEM. WHERE LISTED
C			Cutler-Hammer F.T.N. Electrical / Electronic Control		

A 90-12054

FORM 808



NOTE:

1. UNLESS OTHERWISE SPECIFIED ALL TOLERANCES TO BE ±.016.

ORDER NO. 93719990

A	REMOVED 15-192 NUT NOTE, ADDED "2" TO 15-966-2 NUT NOTE.	6/29/94	D				
B		93719990	E				
C			F				



EATON

TITLE: DIM DWG FOR 8910K223			
DR. W. HANSON	2/1/92	SURFACE COATING	FIRST ASSEM. WHERE LISTED 8910K223
CHK. W. LEONARD	2/3/92	SCALE	SUP'S
APP. M.R. DUMMER	2/3/92	DO NOT SCALE DRAWING	SUP'D BY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8910K7](#)