





8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				20			
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.							
PART NUMBER		REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION	
1852392-1		A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER	
1852392-2		A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER	
1852392-3		A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER	
1852392-6		A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER	
7-1852392-7		A	-	-	-	SPARE PARTS	

△ RECOMMENDED SPARE PARTS


△ GREASE LIGHTLY

△ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE

△ SEE APPLICATION SPECIFICATION FOR SPECIFIC WIRE DETAILS.



TERMINAL NAME: 2.3 UNSEALED TAB TERMINAL					
1612891-1	-	AMP TERMINAL - AMP CRIMP SPECS			
-	-				
-	-	PAD LTR	CRIMP HEIGHT	WIRE SIZE	
-	-	A	1.07±0.05mm [.042±.002]	0.5mm2	
-	-	B	1.05±0.05mm [.041±.002]	0.5 fmm2	
-	-	C	1.00±0.05mm [.039±.002]	0.3mm2	
-	-	D	-	-	
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	1.96mm [.077]	F	0.3-0.5mm2
-	-	INSUL	2.54mm [.100]	OV	1.1-2.2mm
WIRE STRIP LENGTH	TERM APPL SPEC	FEED	APPLICATOR INSTRUCTIONS		SET UP GAGE
4.06-4.45mm	114-5324	11.00mm	408-8040		458637-1



-	2	2	2	2	-	5-354779-0	PIN, WIRE DISC, .3240	128
-	2	2	2	2	-	4-354779-3	PIN, WIRE DISC, .3205	127
-	2	2	2	2	-	4-354779-4	PIN, WIRE DISC, .3210	126
-	-	-	REF	-	..	455749-1	GUARD WINDOW	116
-	-	REF	-	-	..	679532-1	INSERT, GUARD	115
-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71
-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 x .25	62
-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
-	1	1	1	1	-	458537-2	PAWL, FEED	56
-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
-	2	2	2	2	-	2-21000-8	SCR, SKT HD CAP 8-32 X .625	53
-	1	1	1	1	-	21018-5	NUT, HEX, REG 6-32	52
-	1	1	1	1	-	811242-2	BUMPER, HOLD DOWN	51
-	1	1	1	1	-	690753-1	SPACER, TONKER	50
-	-	1	-	-	..	690602-6	CAM, PRE FEED, 1 5/8	49
-	-	-	1	-	..	690602-5	CAM, PRE FEED, 1 1/8	48
-	1	-	-	1	-	690501-4	CAM, POST FEED, 1 5/8	47
-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MQCA)	46
-	1	1	1	1	-	690191-1	PLUG,NYLON	45
-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44
-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43
-	1	1	1	1	-	1-690124-4	WASHER, RAM (.120)	42
-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
-	1	1	1	1	-	23241-6	BALL, STEEL	40
-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39
-	1	1	1	1	-	690142-4	DISC, INSULATION	38
-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37
-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36
-	1	1	1	1	-	690212-1	POST, RAM	35
-	1	1	1	1	-	690786-3	TERMINAL SUPPORT	34
-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
-	1	1	1	1	-	1-1320908-5	SPACER, STRIP GUIDE	30
-	1	1	1	1	-	1633091-1	ASSEMBLY, STRIP GUIDE	29
-	1	1	1	1	-	1-455888-0	SPACER, CRIMPER	28
-	1	1	1	1	-	1320928-1	PLATE, STRIP GUIDE	24
-	1	-	-	1	-	690472-2	STRIPPER	22
-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	-	1	1	-	-	691353-1	STRIPPER	19
-	1	-	-	-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	17
-	1	1	1	1	-	3-22280-3	SPRING, COMPRESSION	12
-	1	1	1	1	-	690461-1	STOP, SHEAR	11
-	-	1	1	1	-	690459-1	SHEAR HOLDER, FRONT	10
-	1	1	1	1	-	462006-1	FLOATING SHEAR, FRONT	9
1	1	1	1	1	-	9-1633116-1	ANVIL, COMBINATION	8
-	1	1	1	1	-	240641-5	SPACER	7
-	1	1	1	1	-	2-455889-0	DEPRESSOR, SHEAR	5
-	1	1	1	1	-	3-238011-5	BLOCK, CRIMPER SPACER	4
1	1	1	1	1	-	1333273-1	CRIMPER, INSULATION SPECIAL	3
-	1	1	1	1	-	455888-2	SPACER, CRIMPER	2
1	1	1	1	1	-	1463696-1	CRIMPER, WIRE	1

-77 -6 -3 -2 -1 U/M		PART NO		DESCRIPTION		ITEM NO			
THIS DRAWING IS A CONTROLLER DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE WITHOUT NOTICE AND NO ASSURANCE OR GUARANTEE OF ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				DATE					
DIMENSIONS: INCHES		Q. RN 1DEC2006		tyco Tyco Electronics Electronics Harrisburg, PA 17105-3608					
		C. RN C. REICHELDERFER 1DEC2006							
		T. ELBIN 1DEC2006		SIDE FEED HDM APPLICATOR - -					
		T. BENCHOFF 1DEC2006							
		APVD					NAME		
		PRODUCT SPEC					SIZE		
		APPLICATION SPEC		CAGE CODE					
		ANGLES		DRAWING NO					
		RESTRICTED TO							
MATERIAL		FINISH		WEIGHT					
-		-		A 00779 C=1852392					
CUSTOMER DRAWING				SCALE 3:5 SHEET 1 OF 1 REV A					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852392-3](#)