




Wire Protection & Management > Heat Shrink Molded Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**
Number of Branches & Legs: **5**
Material Code: **100**
Material Systems Code: **100**
Adhesive Requirement: **Adhesive Precoat**

Features

Product Type Features

Molded Part Shape	Y Shape
Size Code	022

Configuration Features

Number of Branches & Legs	5
Adhesive Requirement	Adhesive Precoat

Body Features

Material	Low Fire Hazard Material
Material Code	100
Material Systems Code	100

Dimensions

Inside Diameter Range (Leg 2)	5.3 – 9.4 mm[.21 – .37 in]
Inside Diameter Range (Leg 3)	5.3 – 9.4 mm[.21 – .37 in]
Inside Diameter Range (Body)	9.7 – 19.3 mm[.38 – .76 in]
Inside Diameter Range (Leg 1)	5.3 – 9.4 mm[.21 – .37 in]
Inside Diameter Range (Leg 4)	5.3 – 9.4 mm[.21 – .37 in]

Usage Conditions

Flammability	Low Fire Hazard
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]



Operation/Application

Emission Features	Halogen-Free
Power Cable Accessory	No

Industry Standards

Government Qualified	No
----------------------	----

Other

Adhesive Code	86
Molded Part Shape Code	562A
Fluid & Chemical Resistance	Long-Term Exposure at High Temperature
Adhesive Options	/86 Precoat

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought

TE Part #91367-1
PRO-CRIMPER TOOL & DIE

TE Part #1617132-5
JMSWD-48XM = M39016/16-022M

TE Part #1856390-6
Fiche cyl Femel 4mm Rouge PIDG

TE Part #ZPF000000000036665
983-6S 20-16 PN-L

Documents

Product Drawings
562A022-100/86-0

English

Datasheets & Catalog Pages
1654025_Sec4_-100

English

Raychem Molded Parts Visual Guide
English

Product Environmental Compliance
Safety Datasheet

English

Safety Datasheet

Safety Datasheet

Safety Datasheet

English

Safety Datasheet

French

Safety Datasheet

German

Safety Datasheet

Safety Datasheet

Safety Datasheet



[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[562A022-100/86-0](#)