

4





3

2

1

## CONVERSION CHART

INCH	MM
.002	0.05
.010	0.25
.016	0.40
.020	0.50
.024	0.60
.035	0.88
.039	0.99
.059	1.49
.079	2.00
.090	2.28
.098	2.48
.115	2.92
.138	3.50
.157	3.98
.167	4.24
.216	5.48
.270	6.85
.276	7.01
.344	8.73
.368	9.34
.400	10.16
.410	10.41
.472	11.98
.512	13.00
.905	22.98
.945	24.03



**PC BOARD LAYOUT, TOP VIEW**  
RECOMMENDED TOLERANCES  $\pm .002$

**SPECIFICATIONS:****MATERIALS:**

CASE: COLD ROLLED STEEL.  
ACTUATOR: POLYESTER, UL94V-0.  
TERMINALS: GOLD OR SILVER PLATE.  
TERMINAL SEAL: EPOXY.  
CONTACTS, MOVING: COPPER ALLOY, GOLD OR SILVER PLATE.  
CONTACTS, FIXED: COPPER ALLOY, GOLD OR SILVER PLATE.

**ELECTRICAL:**

CONTACT RATING, SILVER: 300 MA  $\bullet$  125 VAC.  
CONTACT RATING, GOLD: 0.4 VA MAX.  $\bullet$  20 VDC OR PEAK AC.  
INITIAL CONTACT RESISTANCE: 30 MILLIOHMS MAX.  
INSULATION RESISTANCE: 1,000 MEGOHMS MIN.  
DIELECTRIC STRENGTH: 500 VOLTS RMS  $\bullet$  SEA LEVEL.  
LIFE EXPECTANCY: 15,000 CYCLES.

**MECHANICAL:**


ACTUATION FORCE: 600  $\pm$  300 GRAMS.  
ACTUATOR TRAVEL: .079 IN.

**ENVIRONMENTAL:**

SOLDER HEAT RESISTANCE:  
OPERATING TEMPERATURE:  $-4^{\circ}\text{F}$  TO  $+185^{\circ}\text{F}$ , ( $-20^{\circ}\text{C}$  TO  $+85^{\circ}\text{C}$ ).  
STORAGE TEMPERATURE:  $-40^{\circ}\text{F}$  TO  $+212^{\circ}\text{F}$ , ( $-40^{\circ}\text{C}$  TO  $+100^{\circ}\text{C}$ ).

**NOTES:**

1. INTERPRET DRAWING PER ANSI Y14.5M 1982.

**CIRCUIT DIAGRAM**

MODEL NO.	PLATING
MSSA-3450	SILVER
MSSA-3450 G	GOLD

AUGAT D/N 40043-SD

THIS IS A C.A.D. GENERATED DRAWING.  
DO NOT MAKE MANUAL REVISIONS TO MASTER.



**TYCO** ELECTRONICS

TITLE: CUSTOMER DRAWING  
SLIDE SWITCH, (SP 4 POS.)  
MSSA-1450 SERIES

DWG. NO. **3-1437580-7** REV. **A**

PRODUCT CODE: SCALE: SHEET 1 OF 1

**CUSTOMER DRAWING**  
SPECIFICATIONS ARE SUBJECT TO CHANGES WITHOUT NOTICE



THIRD ANGLE  
PROJECTION

TOLERANCES (EXCEPT AS NOTED)  
ANGULAR =  $\pm 1^{\circ}$   
DECIMAL .XXX =  $\pm .010$

AUGAT CONFIDENTIAL  
This document contains information  
which is the exclusive property of  
Augat Inc.  
Distribution, reproduction or use by  
others is not permitted without the  
expressed written consent of Augat  
Inc.

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN MILLI-  
METERS. DO NOT SCALE PRINT

MATERIAL:  
SEE SPECIFICATIONS

FINISH:  
SEE SPECIFICATIONS

ORIGINAL DATE  
OF DRAWING: 9-17-96

DRAWN:  
C. THEODORE DATE:  
9-17-96

CHECKED: DATE:

APPROVED: DATE:

CODE IDENT. NO. 91506 DWG. SIZE  
C

NEXT ASSY:

REV **A**

REVISIONS  
**0G3C-0173-02**

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MSSA1450G](#)