




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19 .
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

		REVISIONS				
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
			O	RLSD -1 PER PR CM 88-7	2/23/88	TB /RS
				REVISED PER CM 1583		
			A	REV PER 0710-0427-95	24 SEP 88	PMF



1. WIRE RANGE : 2600-4900 CMA.



METRIC

770392-1

PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. MM TOLERANCES ON: DECIMALS ± 0.40 ANGLES ± 1°

CONTRACT NO

DP Whitaker 1-17-86

CHK R. S. 1-17-86

APPD Don Crane 17 Jan. 86

APPD

MATERIAL

0.50 BRASS

FINISH

AMP

AMP INCORPORATED
Harrisburg, Pa.

NAME

TERMINAL, STUD RETAINING,
AMPLIVAR™

SIZE

B

FSCM NO

00779

DRAWING NO

770392

SCALE 4:1

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[770392-1](#)