




0-1393280-2	V23086C1001A302
0-1393280-3	V23086C1001A303
0-1393280-5	V23086C1001A402
0-1393280-6	V23086C1001A403
9-1416000-8	V23086C1001A502
9-1416000-6	V23086C1001A602
9-1416000-0	V23086C1001X008
0-1393280-9	V23086C1002A303
1-1393280-1	V23086C1002A403
6-1414772-9	V23086C1002A502
2-1414987-3	V23086C1002A803
1-1413009-9	V23086C1004A303
8-1416000-7	V23086C1021A502
9-1416000-3	V23086C1021X011
1-1393280-4	V23086G1001X001
6-1414892-7	V23086G1501X028
5-1414993-2	V23086C1021X037
PART NUMBER	DESCRIPTION

Ansicht auf die Anschluesse
View on the terminals

Schaltbild
Circuit diagram



- 1) fuer Ebenheit und Geradheit
ISO 2768 - L
 - 2) Pinlaenge ohne Verzinnung
mit Verzinnung max. 3,8mm
- 1) for flatness and straightness
ISO 2768 - L
 - 2) Length of terminal without tin
with tin max. 3,8mm






PROPRIETARY THE REPRODUCTION, TRANSMISSION OR USE OF THIS DOCUMENT OR IT'S CONTENTS IS NOT PERMITTED WITHOUT EXPRESSED WRITTEN AUTHORITY. OFFENDERS WILL BE LIABLE FOR ALL DAMAGES. ALL RIGHTS, INCLUDING RIGHTS CREATED BY REGISTERED PATENT(S) GRANTED FOR A UTILITY MODEL OR DESIGN, ARE RESERVED.				CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD		PAPER SIZE A2
APPLICABLE SPEC.:				FINISH		
				DIMENSIONS APPLY PLATING		
				SCALE	5:1	WEIGHT ca. 4g
				MATERIAL		
				PART NAME		
				MicroK THT Dimension drawing		
				PART NO. C23303-A0086-A001-CD		
				SHT. 1 OF 2		
REV. CHANGE ORDER		DATE		APP.		


TE connectivity

B3	ECO-12-017225	26SEP2012	JFai	DWN.	97-10-23	Reiss
B2	ECO-08-027644	2008-11-06	JFai	APP.		
B1	ECO-07-012552	2007-05-29	JFai	REV.		
B	ECO-06-028631	2006-12-07	ASCH	LOCATION	Bin-P	
A	Migration	2006-06-30	ASCH			
04	WE06/A177	2006-06-28	ASCH			
03	WB03/A020	2003-01-20	ASCH			


Massbild Schliesser
Dimension drawing make-contact



Ansicht auf die Anschluesse
View on the terminals





Schaltbild
Circuit diagram



- 1) fuer Ebenheit und Geradheit
ISO 2768 - L
- 2) Pinlaenge ohne Verzinnung
mit Verzinnung max. 3,8mm

- 1) for flatness and straightness
ISO 2768 - L
- 2) Length of terminal without tin
with tin max. 3,8mm

PROPRIETARY THE REPRODUCTION, TRANSMISSION OR USE OF THIS DOCUMENT OR IT'S CONTENTS IS NOT PERMITTED WITHOUT EXPRESSED WRITTEN AUTHORITY. OFFENDERS WILL BE LIABLE FOR ALL DAMAGES. ALL RIGHTS, INCLUDING RIGHTS CREATED BY REGISTERED PATENT(S) GRANTED FOR A UTILITY MODEL OR DESIGN, ARE RESERVED.					CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD		PAPER SIZE A2		
APPLICABLE SPEC.:					FINISH				
					DIMENSIONS APPLY PLATING				
				TOLERANCE UNLESS SPECIFIED OTHERWISE ISO 2768-f mH 11				SCALE 5:1 WEIGHT ca. 4g	
				DIMENSIONS IN MM		MATERIAL			
				DATE		NAME		PART NAME	
B3	ECO-12-017225	26SEP2012	JFai	DWN.	97-10-23	Reiss		MicroK THT Dimension drawing	
B2	ECO-08-027644	2008-11-06	JFai	APP.					
B1	ECO-07-012552	2007-05-29	JFai	REV.					
B	ECO-06-028631	2006-12-07	ASCH	LOCATION	Bin-P				
A	Migration	2006-06-30	ASCH						
04	WE06/A177	2006-06-28	ASCH			PART NO.		SHT.	
03	WB03/A020	2003-01-20	ASCH			C23303-A0086-A001-CD		2	
REV. CHANGE ORDER		DATE	APP.					OF 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1393280-1](#)