




Wire And Cable > Hook Up Wire

22759/43-16-9



✓ ACTIVE

Raychem | CGS SP

TE Part # **22759/43-16-9**
TE Internal #: **732994-001**
Mil-Spec: **M22759/43-16-9**
Alias #: **4-1195725-8**

Cable Type : **Spec 55A**
Voltage Rating (V): **600**
Wire Size (AWG): **16**
Wire Size (mm²): **1.31**
Operating Temperature Range (°C): **-65 – 200**

⌵ Add to List | Similar Products

Compatible Parts & Tooling

We are here to help!
Get in touch with our product experts.

💬

CHAT WITH US

✉

EMAIL US

☎

CALL US



Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.	
Product Type Features	Cable Type : Spec 55A Cable Style : Primary Product Classification : Cable - High Performance - Spec 44, 55 & RCW Product Type : Wire
Configuration Features	Number of Strands : 19 Number of Conductors : 1
Electrical Characteristics	Voltage Rating (V): 600
Body Features	Wire Color : White
Dimensions	Strand Size (AWG): 29 Wire Size (AWG): 16 Wire Size (mm²): 1.31 Conductor Diameter : 1.35 mm [.053 in] Overall Outside Diameter : 1.96 mm [.077 in] Insulation Thickness (in): .009 Wire Diameter : 1.96 mm [.077 in]
Usage Conditions	Operating Temperature Range (°C): -65 – 200
Other	Wire Source : United States

Feedback

Compatible Parts

> [Contact Product Support](#)

Also in the Series

| [CGS SP](#)




Board-to-Board Connector Contacts (2)



Board-to-Board Headers & Receptacles (1)



Cable Actuated Position Sensors (17)



Convolute Tubing (15)

Feedback


Customers Also Bought






TE Part # 1-1757819-0
AMPLIMITE, ASY,
PLUG, STD, 109, ZN,
5, CT

Add to Cart



TE Part # H4P910RFZA
H4P 910R 1% 100PPM

View Product



TE Part # 362A014-4-0
362A014-4-0

View Product



TE Part # ACT26MD05SN
[V001]
STRAIGHT PLUG

View Product

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M22759/43-16-9](#)