



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**
Ratchet Configuration: **Not Releasable, Not Adjustable**
Die Sets Type: **Fixed In Tool**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Yes – Certificate Included**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Manual
Tooling Type	Double Action Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed



Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # CAT-UL8-250 ULTRA POD: Straight, Receptacle Assembly, Tin Plated, 0.25 inch	 TE Part # 42731-2 FASTON 250 REC TERMINAL 22-18 TPBR LP	 TE Part # 60878-2 FASTON 250 RECEPTACLE 22-18 AWG TPBR	 TE Part # 170187-2 250 FASTON,REC.,22-18 AWG,TPBR
 TE Part # 61316-1 FF 250 TAB 22-18AWG TPBR	 TE Part # 41969-2 FASTON 250 TERMINAL REC 22-18 AWG BR	 TE Part # 140760-2 250 FASTON,REC.,22-18 AWG,TPPB	 TE Part # 63609-2 FASTON 250 RECEPTACLE 22-18 AWG TPBR
 TE Part # 63127-1 FASTON 250 REC 22-18 AWG BR	 TE Part # 170183-1 250 FASTON,REC.,22-18 AWG,BR	 TE Part # 170183-2 250 FASTON,REC.,22-18 AWG,TPBR	 TE Part # 63609-1 FASTON 250 RECEPTACLE 22-18 AWG BR



TE Part # 63693-1
FASTON 250 RECEPTACLE 22-18 AWG BR

TE Part # CAT-UL8-2502
ULTRA POD: Straight, Receptacle Assembly, Unplated, .250 inch

TE Part # 62274-1
FASTON 250 18-22AWG TPBR

TE Part # 41969
FASTON 250(6.3 MM) REC 22-18 AWG TPBR

TE Part # 140760-3
250 FASTON,REC.,22-18 AWG,SPPB

TE Part # 170187-1
250 FASTON,REC.,22-18 AWG,BR

TE Part # 42731-1
.250 SRS FASTON RECEPT.

TE Part # 140760-4
250 FASTON,REC.,22-18 AWG,PB

Customers Also Bought

TE Part #2-2176389-1
RQ 1206 174R 0.1% 10PPM 5K RL

TE Part #749611-9
100 50SR PANEL MOUNT RCPT

TE Part #240345J001
V2-10.0-0-FSP-SM

TE Part #2-1393143-0
27E168=SOCKET,KU93,11,PC,NYL

TE Part #314964-1
HYP8/10 COPALUM SEALED 2/0AWG DIE SET

TE Part #7-103414-2
24 MODII HDR SRST SHRD .100CL

TE Part #NB11652001
ATUM-6/2-0-STK

Documents

- Datasheets & Catalog Pages

CERTI-CRIMPII-Premium-August-1-1773864-7

English
- Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English
- CRIMPING WHERE FORM MEETS FUNCTION

English
- Bottoming Dies



English

Product Specifications
Application Specification

English

Instruction Sheets
Instruction Sheet (U.S.)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[90166-1](#)