

DTM04-12PA

✓ ACTIVE

DEUTSCH | DEUTSCH DT, DEUTSCH DTM

TE Internal #: DTM04-12PA

Hybrid, Housing for Male Terminals, Wire-to-Wire, 12 Position, 4.19 mm [.165in] Centerline, Sealable, Gray, Wire & Cable

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Housings > DEUTSCH DTM HOUSINGS



Connector & Housing Type: **Housing for Male Terminals**

Mating Pin Diameter: **1.02 mm [.04 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **12**

Centerline (Pitch): **4.19 mm [.165 in]**

[All DEUTSCH DTM HOUSINGS \(86\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Blank Cavity Position	0
Number of Positions	12
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 48 V

Body Features

Cable Exit Angle	180°
Body Material	PA GF



Primary Product Color	Gray
Connector Code	A

Contact Features

Mating Pin Diameter	1.02 mm[.04 in]
Contact Current Rating (Max)	7.5 A

Mechanical Attachment

Mounting Feature	With
Terminal Position Assurance	Yes
Strain Relief	Add By Accessory
Mating Alignment Type	Polarized
Connector Mounting Type	Cable Mount (Free-Hanging), Fixing Screw

Housing Features

Centerline (Pitch)	4.19 mm[.165 in]
--------------------	------------------

Dimensions

Product Width	20.22 mm[.796 in]
Product Length	43.69 mm[1.72 in]
Product Height	40.01 mm[1.575 in]
Row-to-Row Spacing	7.11 mm[.28 in]
Accepts Wire Insulation Diameter Range	1.35 – 3.05 mm[.053 – .12 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Agency/Standard	SAE J2030
Degree of Protection	IP68, IP6K9K
UL Flammability Rating	20mm Flame Test per Standard UL-94

Packaging Features

Packaging Quantity	350
Packaging Method	Box

Other



Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D48-ST273
DEUTSCH SOLID CONTACTS



TE Part # DT-RT1
EXT TOOL, FRONT RELEASE













TE Part # CAT-D48-SP729
DEUTSCH SEALING PLUGS










TE Part # CAT-D485-CH8172
DEUTSCH DTM HOUSINGS



 TE Part # CAT-D485-W416 DEUTSCH DTM WEDGELOCKS	 TE Part # CAT-D487-M8649 DEUTSCH DT MOUNTING CLIPS	 TE Part # 1011-053-1205 SEAL RET, 12P, BLK, DTM, B	 TE Part # CAT-D48-SFT273 DEUTSCH STAMPED & FORMED CONTACTS
 TE Part # 1924487-2 MOUNTING CLIP, AMPSEAL 16	 TE Part # 1028-034-1205 BKSHL, 12P, BLK, REC, ST, NW 13/17	 TE Part # DTM12P-DC PROTECT CVR, 12P, REC, GRY, DTM	 TE Part # 1010-042-1206 SEAL, INTF, 12P, RED-ORG, DTM
 TE Part # DTM12P-BT BOOT, 12P, REC, ST, GRY	 TE Part # DTM12P-BT-BK BOOT, 12P, REC, ST, BLK		

Also in the Series

DEUTSCH DT


 Automotive Connector Caps & Covers (71)	 Automotive Connector Locks & Position Assurance(62)	 Automotive Headers(83)	 Automotive Housings(563)
 Automotive Seals & Cavity Plugs(4)	 Insertion & Extraction Tools(3)	 Other Automotive Connector Accessories(14)	

Also in the Series

DEUTSCH DTM



Automotive Connector Caps & Covers
(16)



Automotive Connector Locks &
Position Assurance(15)



Automotive Headers(29)



Automotive Housings(89)



Insertion & Extraction Tools(2)

Customers Also Bought



TE Part #DTM04-12PB
DEUTSCH DTM HOUSINGS



TE Part #WM-12P
DEUTSCH DTM WEDGELOCKS



TE Part #1060-20-0122
PIN, SF, SIZE 20, 16-22, NI/NI



TE Part #2266574-1
OCEAN_2.0_Applicator-S-062F



TE Part #7-2266574-7
OCEAN_2.0_SPARE_PART_KIT-062F

Documents

Product Drawings
REC, 12P, GRY, N, A

English

CAD Files
Customer View Model
ENG_CVM_CVM_DTM04-12PA_99.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_DTM04-12PA_99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_DTM04-12PA_99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

CONNECTOR SELECTOR

English

Product Specifications

[Engineering Report](#)

English

Product Environmental Compliance

[MD_DTM04-12PA_03222018522_dmtec](#)

English

[MD_DTM04-12PA_03222018522_dmtec](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[DTM04-12PA-KIT](#)