



HTCM-SCE-TP

TE Internal #: E61464-000  
HTCM-SCE-TP, Printable Tags, High Temperature, Operating Temperature Range -55 – 225 °C [-67 – 437 °F], White  
[View on TE.com >](#)

Identification & Labeling > Printable Tags > HTCM-SCE-TP HIGH TEMPERATURE MARKERS



Printable Tag Grade: **High Temperature**  
Operating Temperature Range: **-55 – 225 °C [-67 – 437 °F]**  
Primary Product Color: **White**

All HTCM-SCE-TP HIGH TEMPERATURE MARKERS (6)

Features

Product Type Features

|                     |                  |
|---------------------|------------------|
| Printable Tag Grade | High Temperature |
|---------------------|------------------|

Body Features

|                       |       |
|-----------------------|-------|
| Primary Product Color | White |
|-----------------------|-------|

Mechanical Attachment

|                          |   |
|--------------------------|---|
| Number of Tie-Wrap Holes | 6 |
|--------------------------|---|

Dimensions

|            |                |
|------------|----------------|
| Tag Height | 12.7 mm[.5 in] |
| Tag Length | 50.8 mm[2 in]  |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 225 °C[-67 – 437 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                    |                                                              |
|--------------------|--------------------------------------------------------------|
| Recommended Ribbon | See TE Document 411-121005 the Printer Product Ribbon Matrix |
|--------------------|--------------------------------------------------------------|

Printer/Label Features

|                     |                                                              |
|---------------------|--------------------------------------------------------------|
| Recommended Printer | See TE Document 411-121005 the Printer Product Ribbon Matrix |
| Printer Technology  | Thermal Transfer                                             |

Packaging Features

|                    |     |
|--------------------|-----|
| Packaging Quantity | 250 |
|--------------------|-----|

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free                                    |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |














Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                               |                                                                                                                               |                                                                                                                                       |                                                                                                                                       |
|-------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| <br>TE Part # 1-2186500-1<br>T3212-PRINTER | <br>TE Part # 1-2186502-1<br>T3224-PRINTER | <br>TE Part # 4-160968-1<br>CABLE TY 134X2.6 NAT | <br>TE Part # 2-160975-1<br>CABLE TY 200X4.8 NAT |
|-------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|



|                                                                                                                                          |                                                                                                                                                    |                                                                                                                                            |                                                                                                                                            |
|------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 4-160968-2<br/>CABLE TY 134X2.6 BLACK</p> |  <p>TE Part # 4-160971-2<br/>CABLE TY 140X3.6 BLACK</p>          |  <p>TE Part # 4-160975-2<br/>CABLE TY 200X4.8 BLA</p>   |  <p>TE Part # 2-100715-1<br/>CABLE TY 150X3,6NAT</p>    |
|  <p>TE Part # 2-100716-1<br/>CABLE TY 200X4,8NAT</p>   |  <p>TE Part # 2-160970-2<br/>CABLE TY 200X2.6 BLA</p>           |  <p>TE Part # 2-160978-1<br/>CABLE TY 360X4,8NAT</p>   |  <p>TE Part # 754073-000<br/>TMS-RJS-RIBBON-4HT</p>    |
|  <p>TE Part # 4-160970-2<br/>CABLE TY 200X2.6 BLA</p> |  <p>TE Part # 4-160975-1<br/>CABLE TY 200X4.8 NAT</p>          |  <p>TE Part # 4-160974-1<br/>CABLE TY 178X4,8NAT</p>  |  <p>TE Part # 2-160977-2<br/>CABLE TY 290X4.8 BLA</p> |
|  <p>TE Part # 2-160978-2<br/>CABLE TY 360X4,8BLA</p>  |  <p>TE Part # 2-160968-1<br/>FOAC CABLE TY NATURAL 134X2.6</p> |  <p>TE Part # 1-2186501-1<br/>T3212-SWARE-PRINTER</p> |  <p>TE Part # 1-2186503-1<br/>T3224-SWARE-PRINTER</p> |


Also in the Series | HTCM-SCE-TP



Printable Tags(6)

Customers Also Bought





TE Part #47820  
HYP8 TERMINYL 8AWG DIE SET



TE Part #59250  
T-HEAD PIDG 26-14 ASSY



TE Part #1577625-1  
TERMINAL RT PIDG PEEK STRATO 20 AWG



TE Part #1577631-1  
TERMINAL RT PIDG PEEK STRATO 18-16 AWG



TE Part #1577647-1  
TERMINAL RT PIDG PEEK STRATO 10 AWG



TE Part #170362-3  
MINI UNIVERSAL M-N-L SOCKET



TE Part #1577632-1  
TERMINAL RT PIDG PEEK STRATO 18-16 AWG



TE Part #474615-000  
D-106-6012



TE Part #ZPF000000000136664  
182-0908-20



TE Part #200980-000  
B-013-11CS2689

Documents

Product Drawings  
HTCM-SCE-TP-1/2-6H-9

English

Datasheets & Catalog Pages  
IDENTIFICATION SELECTION GUIDE

English

HTCM-SCE-TP Thermal Transfer Cable Marker

English

Product Specifications  
CABLE MARKER INSTALLATION GUIDE

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HTCM-SCE-TP-1/2-6H-9](#)