



CII

TE Internal #: 3-1617028-8

Half-Size Relays, Half-Size Relay Contact Arrangement 2 Form C, DPDT, 2 C/O, 26.5VDC Half-Size Relay Input Voltage

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Mil-Aero Relays > Half-Size Relays



Half-Size Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O**

Half-Size Relay Input Voltage: **26.5 VDC**

Half-Size Relay Contact Current Rating: **2 A**

Half-Size Relay Coil Voltage Rating: **26.5 VDC**

Half-Size Relay Coil Resistance: **700 Ω**

Features

Product Type Features

| | |
|----------------|-------------------------------------|
| Enclosure Type | Hermetically Sealed |
| Relay Type | Military/Aerospace High Performance |
| Coil Latching | Without |
| Product Type | Relay |
| MOSFET Driver | Without |

Configuration Features

| | |
|-------------------|---------|
| Transistor Driver | Without |
|-------------------|---------|

Electrical Characteristics

| | |
|-------------------------------------|---------------------------|
| Coil Magnetic System | Non-Polarized, Monostable |
| Actuating System | DC |
| Vibration | 30G's, 10 – 3000Hz |
| Shock | 100G's, 6ms |
| Coil Suppression Diode | Without |
| Coil Power Measurement | Milliwatts |
| Coil Polarity Protection Diode | Without |
| Half-Size Relay Input Voltage | 26.5 VDC |
| Half-Size Relay Coil Voltage Rating | 26.5 VDC |
| Half-Size Relay Coil Resistance | 700 Ω |



| | |
|---|---------|
| Half-Size Relay Coil Power Rating (DC) | 1003 mW |
| Half-Size Relay Contact Switching Voltage (Max) | 28 VDC |

Contact Features

| | |
|--|-----------------------|
| Half-Size Relay Contact Arrangement | 2 Form C, DPDT, 2 C/O |
| Half-Size Relay Contact Current Rating | 2 A |

Termination Features

| | |
|------------------|-----------------------|
| Termination Type | Solder Hook Terminals |
|------------------|-----------------------|

Mechanical Attachment

| | |
|-------------------------------|---------------|
| Half-Size Relay Mounting Type | Chassis Mount |
|-------------------------------|---------------|

Usage Conditions

| | |
|-----------------------------|--------------|
| Operating Temperature Range | -65 – 125 °C |
|-----------------------------|--------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Not Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not lead free process capable |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Model / Part # 2-1617109-6
PRMAC-12X = COTS T05

Customers Also Bought

TE Model / Part #823278-000
342A124-4/42-0

TE Model / Part #476759-000
502A834-25-0

TE Model / Part #880835-000
55A4824-24-9/96-9CS2275

TE Model / Part #DG1236R16-14P1
PLUG ASSY

TE Model / Part #268769-000
222A255-3-01/42-0

TE Model / Part #137317-000
55A1822-14-9/96-9CS2275

TE Model / Part #1757804-1
1034 7188 02

TE Model / Part #7-1617571-7
JMGSC-18PW=M39016/41-056P

TE Model / Part #8-1617352-9
JMAWT-18XP=M28776/1-017P

TE Model / Part #593774N001
S02-20-R-90CS1093

Documents

Product Drawings
HFW1106K13M = M39016/6-228M
English

Datasheets & Catalog Pages
5-1773450-5_sec1_HFW
English



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HFW1106K13M](#)