



Connectors > Card & Socket Connectors > Transistor Sockets



Number of Positions: 4

Profile: Low

Package: TO-5

Lead Size Accepted: .41 mm [.016 in]

Termination Method: Solder Pocket

Features

Product Type Features

Terminal Configuration	Contact
Profile	Low
Package	TO-5
Connector & Contact Terminates To	Printed Circuit Board
Product Type	Socket

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Sleeve Material	Brass
Sleeve Plating Material	Gold
Insulator Material	Fluoropolymer
Lead Size Accepted	.41 mm[.016 in]
Color	Black

Contact Features

Terminal Material	Beryllium Copper
Terminal Plating	Gold
Termination Method	Solder Pocket
Contact Current Rating (Max)	3 A
Socket Type	Transistor



Pin Diameter	2.54 mm[.1 in]
--------------	----------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Insulator Flammability Rating	UL 94V-0
-------------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought

8060-1G6=GOLD TRANSISTOR SOCKE


TE Part # 2-1437504-1
TE Internal #: 8060-1G6



TE Part #862498-1
LGH 2 CAV HSG PLUG



TE Part #1-5750913-2
26 50SR CABLE CONN KIT



TE Part #104693-7
70 50/50 HDR DRST
SFMNT .390




TE Part #85875-1
04 MODI HDR SRST .156CL




TE Part #87983-4
04 MODI BDMNT RCPT
SR .156CL



TE Part #3-2319848-3
END STACK
DIP2PJRECESSEALTUBE



TE Part #3-1879672-0
H8 20R 0.1% 25PPM



TE Part #6-1879675-8
H8 61K9 0.1% 25PPM



TE Part #2-2176306-0
RP 1E 0.1W 1K82 0.1%
25PPM 5K RL



TE Part #5-2176307-0
RP 1E 0.1W 40K2 0.1%
25PPM 5K RL

Documents

Product Drawings

8060-1G6=GOLD TRANSISTOR SOCKE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1437504-1_99.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1437504-1_99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1437504-1_99.3d_stp.zip

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8060-1G6](#)