

- 1

MOLDED CIRCUIT #1 IDENTIFIER IN LOCATION SHOWN.
- 2

MATERIAL:GLASS FILLED THERMOPLASTIC, UL 94-V0 RATED, COLOR: BLACK
- 3




NOTE DELETED
- 4

THE PRODUCT IS IN PROCESS FOR QUALIFICATION, AND IS NOT YET QUALIFIED
- 5

TE LOGO ON EITHER SIDE

| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | H1  | REVISED PER ECO-11-004587 | 11MAR2011 | RK  | HMR  |
|           | J   | REVISED PER ECR-22-132152 | 15JUN2022 | RK  | SD   |
|           | J1  | REVISED PER ECN-23-211206 | 24JUN2023 | RK  | MF   |
|           | J2  | REVISED PER ECN-24-281985 | 29AUG2024 | RK  | MF   |

|          |                                                              |           |             |                     |
|----------|--------------------------------------------------------------|-----------|-------------|---------------------|
| OBSOLETE | 91.44[3.600]                                                 | 35        | 72          | 3-102394-4          |
|          | 88.90[3.500]                                                 | 34        | 70          | 3-102394-3          |
|          | 86.36[3.400]                                                 | 33        | 68          | 3-102394-2          |
|          | 83.82[3.300]                                                 | 32        | 66          | 3-102394-1          |
|          | 81.28[3.200]                                                 | 31        | 64          | 3-102394-0          |
|          | 78.74[3.100]                                                 | 30        | 62          | 2-102394-9          |
|          | 76.20[3.000]                                                 | 29        | 60          | 2-102394-8          |
|          | 73.66[2.900]                                                 | 28        | 58          | 2-102394-7          |
|          | 71.12[2.800]                                                 | 27        | 56          | 2-102394-6          |
|          | 68.58[2.700]                                                 | 26        | 54          | 2-102394-5          |
|          | 66.04[2.600]                                                 | 25        | 52          | 2-102394-4          |
|          | 63.50[2.500]                                                 | 24        | 50          | 2-102394-3          |
|          | 60.96[2.400]                                                 | 23        | 48          | 2-102394-2          |
|          | 58.42[2.300]                                                 | 22        | 46          | 2-102394-1          |
|          | 55.88[2.200]                                                 | 21        | 44          | 2-102394-0          |
|          | 53.34[2.100]                                                 | 20        | 42          | 1-102394-9          |
|          | 50.80[2.000]                                                 | 19        | 40          | 1-102394-8          |
|          | 48.26[1.900]                                                 | 18        | 38          | 1-102394-7          |
|          | 45.72[1.800]                                                 | 17        | 36          | 1-102394-6          |
|          | 43.18[1.700]                                                 | 16        | 34          | 1-102394-5          |
| B        | 40.64[1.600]                                                 | 15        | 32          | 1-102394-4          |
|          | 38.10[1.500]                                                 | 14        | 30          | 1-102394-3          |
|          | 35.56[1.400]                                                 | 13        | 28          | 1-102394-2          |
|          | 33.02[1.300]                                                 | 12        | 26          | 1-102394-1          |
|          | 30.48[1.200]                                                 | 11        | 24          | 1-102394-0          |
|          | 27.94[1.100]                                                 | 10        | 22          | 102394-9            |
|          | 25.40[1.000]                                                 | 9         | 20          | 102394-8            |
|          | 22.86[.900]                                                  | 8         | 18          | 102394-7            |
|          | 20.32[.800]                                                  | 7         | 16          | 102394-6            |
|          | 17.78[.700]                                                  | 6         | 14          | 102394-5            |
| A        | 15.24[.600]                                                  | 5         | 12          | 102394-4            |
|          | 12.70[.500]                                                  | 4         | 10          | 102394-3            |
|          | 10.16[.400]                                                  | 3         | 8           | 102394-2            |
|          | 7.62[.300]                                                   | 2         | 6           | 102394-1            |
|          | B                                                            | A         | NO. OF POSN | PART NO.            |
|          | TE Connectivity                                              |           |             |                     |
|          | HOUSING, AMPMODU, MASS TERMINATION DOUBLE ROW, .100X.100 C/L |           |             |                     |
|          | SIZE                                                         | CAGE CODE | DRAWING NO  | RESTRICTED TO       |
|          | A2                                                           | 00779     | C-102394    | -                   |
|          | CUSTOMER DRAWING                                             |           | SCALE 4:1   | SHEET 1 OF 1 REV J2 |



SECTION X-X

METRIC

|                                        |  |                       |                 |  |
|----------------------------------------|--|-----------------------|-----------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN S. SHUEY 24JUL91  | TE Connectivity |  |
| DIMENSIONS: mm [Inch]                  |  | CHK M. RIDER 24JUL91  |                 |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD M. RIDER 24JUL91 | NAME            |  |
| 0 PLC ±                                |  | PRODUCT SPEC          | -               |  |
| 1 PLC ±                                |  | APPLICATION SPEC      | -               |  |
| 2 PLC ±0.13 [.005]                     |  | WEIGHT                | -               |  |
| 3 PLC ±                                |  | CUSTOMER DRAWING      | SCALE 4:1       |  |
| 4 PLC ±                                |  |                       | SHEET 1 OF 1    |  |
| ANGLES ±                               |  |                       | REV J2          |  |
| FINISH                                 |  |                       |                 |  |
| MATERIAL                               |  |                       |                 |  |
| 2                                      |  |                       |                 |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-102394-2](#)