

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
V		REVISED PER ECO-17-002584	08APR2017	BDA	MM
W		REVISED PER ECO-20-001323	29MAY2020	SM	JO

D

D

C

C



B

B

A

A

1. .000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
2. POINT OF MEASUREMENT FOR PLATING THICKNESS.
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
4. ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
5. .000100 BRIGHT TIN OVER .000050 NICKEL.
6. PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
7. .000100 MATTE TIN OVER .000050 NICKEL.
8. HIGH TEMPERATURE CONFIGURATION
9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
10. 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF



SECTION X-X

OBSOLETE
9

8	7	64.01 [2.520]	65.91 [2.595]	24	25	7-103634-4
8	7	61.47 [2.420]	63.37 [2.495]	23	24	7-103634-3
8	7	58.93 [2.320]	60.83 [2.395]	22	23	7-103634-2
8	7	56.39 [2.220]	58.29 [2.295]	21	22	7-103634-1
8	7	53.85 [2.120]	55.75 [2.195]	20	21	7-103634-0
8	7	51.31 [2.020]	53.21 [2.095]	19	20	6-103634-9
8	7	48.77 [1.920]	50.67 [1.995]	18	19	6-103634-8
8	7	46.23 [1.820]	48.13 [1.895]	17	18	6-103634-7
8	7	43.69 [1.720]	45.59 [1.795]	16	17	6-103634-6
8	7	41.15 [1.620]	43.05 [1.695]	15	16	6-103634-5
8	7	38.61 [1.520]	40.51 [1.595]	14	15	6-103634-4
8	7	36.07 [1.420]	37.97 [1.495]	13	14	6-103634-3
8	7	33.53 [1.320]	35.43 [1.395]	12	13	6-103634-2
8	7	30.99 [1.220]	32.89 [1.295]	11	12	6-103634-1
8	7	28.45 [1.120]	30.35 [1.195]	10	11	6-103634-0
8	7	25.91 [1.020]	27.81 [1.095]	9	10	5-103634-9
8	7	23.37 [.920]	25.27 [.995]	8	9	5-103634-8
8	7	20.83 [.820]	22.73 [.895]	7	8	5-103634-7
8	7	18.29 [.720]	20.19 [.795]	6	7	5-103634-6
8	7	15.75 [.620]	17.65 [.695]	5	6	5-103634-5
8	7	13.21 [.520]	15.11 [.595]	4	5	5-103634-4
8	7	10.67 [.420]	12.57 [.495]	3	4	5-103634-3
8	7	8.13 [.320]	10.03 [.395]	2	3	5-103634-2
8	7	5.59 [.220]	7.49 [.295]	1	2	5-103634-1
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

9 SUPERCEDED BY 7-103634-4

OBSOLETE
9

9 SUPERCEDED BY 6-103634-6

8	7	30.99 [1.220]	32.89 [1.295]	11	12	3-103634-4
8	7	25.91 [1.020]	27.81 [1.095]	9	10	3-103634-3
8	7	23.37 [.920]	25.27 [.995]	8	9	3-103634-2
8	7	18.29 [.720]	20.19 [.795]	6	7	3-103634-1
8	7	15.75 [.620]	17.65 [.695]	5	6	3-103634-0
8	7	5.59 [.220]	7.49 [.295]	1	2	2-103634-9
8	7	41.15 [1.620]	43.05 [1.695]	15	16	2-103634-8
8	7	13.21 [.520]	15.11 [.595]	4	5	2-103634-7
8	7	10.67 [.420]	12.57 [.495]	3	4	2-103634-6
8	7	8.13 [.320]	10.03 [.395]	2	3	2-103634-5
1	7	64.01 [2.520]	65.91 [2.595]	24	25	2-103634-4
1	7	61.47 [2.420]	63.37 [2.495]	23	24	2-103634-3
1	7	58.93 [2.320]	60.83 [2.395]	22	23	2-103634-2
1	7	56.39 [2.220]	58.29 [2.295]	21	22	2-103634-1
1	7	53.85 [2.120]	55.75 [2.195]	20	21	2-103634-0
1	7	51.31 [2.020]	53.21 [2.095]	19	20	1-103634-9
1	7	48.77 [1.920]	50.67 [1.995]	18	19	1-103634-8
1	7	46.23 [1.820]	48.13 [1.895]	17	18	1-103634-7
1	7	43.69 [1.720]	45.59 [1.795]	16	17	1-103634-6
1	7	41.15 [1.620]	43.05 [1.695]	15	16	1-103634-5
1	7	38.61 [1.520]	40.51 [1.595]	14	15	1-103634-4
1	7	36.07 [1.420]	37.97 [1.495]	13	14	1-103634-3
1	7	33.53 [1.320]	35.43 [1.395]	12	13	1-103634-2
1	7	30.99 [1.220]	32.89 [1.295]	11	12	1-103634-1
1	7	28.45 [1.120]	30.35 [1.195]	10	11	1-103634-0
1	7	25.91 [1.020]	27.81 [1.095]	9	10	103634-9
1	7	23.37 [.920]	25.27 [.995]	8	9	103634-8
1	7	20.83 [.820]	22.73 [.895]	7	8	103634-7
1	7	18.29 [.720]	20.19 [.795]	6	7	103634-6
1	7	15.75 [.620]	17.65 [.695]	5	6	103634-5
1	7	13.21 [.520]	15.11 [.595]	4	5	103634-4
1	7	10.67 [.420]	12.57 [.495]	3	4	103634-3
1	7	8.13 [.320]	10.03 [.395]	2	3	103634-2
1	7	5.59 [.220]	7.49 [.295]	1	2	103634-1
REMARK	PLATING	C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0. PLC
1. PLC
2. PLC
3. PLC
4. PLC
ANGLES

± -
± -
± -
± -
± -
± -

MATERIAL
HOUSING: FLAME RETARDANT
LOF,COLOR: BLACK
CONTACTS: BRASS

FINISH
SEE TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. SHUEY
CHK
L. CASTAGNA
APVD
L. CASTAGNA

3-5-91
3-27-91
3-27-91

PRODUCT SPEC
108-25034
APPLICATION SPEC
114-25026

SIZE
A1

DATE CODE
00779

DRAWING NO.
103634

CUSTOMER DRAWING

SCALE
4:1

SHEET
1

OF
1

REV
W

TE Connectivity

HDRASSY,RTANGLE,SINGLEROW,
2.54[.100]C/L0.64[.025]SQPST,
WITHPLZN&LATCHING,AMPMODULE

RESTRICTED TO

-

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103634-2](#)