

3640 0201 1.4nH +/-0.2nH 1K RL

✓ ACTIVE

Sigma | Sigma 3640

TE Part # 1-2176075-4

TE Internal #: 1-2176075-4

[View on TE.com >](#)



Passive Components > Inductors > High Frequency & RF Inductors



Inductor Type: **High Frequency**

Mount Style: **Surface Mount**

Packaging Method: **Reeled**

Dimensions: **.6 x .3 x .23 mm**

Tolerance: **2%**

Features

Product Type Features

Inductor Type	High Frequency
Shielded	No
Element Type	Thin Film
Size Code	0201

Electrical Characteristics

Self Resonant Frequency	9 GHz
Tolerance	2%
Inductance	.0014 μ H
Current Rating (Max)	250 mA
DC Resistance	.45 Ω

Body Features

Lead Type	Surface Mount Terminals
-----------	-------------------------

Mechanical Attachment

Mount Style	Surface Mount
-------------	---------------

Dimensions

Dimensions	.6 x .3 x .23 mm
------------	------------------

Packaging Features

Packaging Method	Reeled
------------------	--------

Other



Comment	Tolerance 0.2nH.
Quality Factor	8

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JUN 2016 (169)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # 6-1624108-3 3640 0402 7.2nH +/-0.2nH 1K RL	 TE Part # 7-1624108-0 3640 0402 18nH 2% 1K RL	 TE Part # 2-1624108-5 3640 0402 2.2nH +/-0.2nH 1K RL	 TE Part # 1624108-5 3640 0402 22nH 5% 10K RL
---	--	---	---





TE Part # 6-1624108-1
3640 0402 5.6nH +/-0.2nH
1K RL

Also in the Series | Sigma 3640



High Frequency & RF
Inductors(116)

Customers Also Bought




TE Part #1247002-2
MAGMATE "300 SERIE"
WITH MULTISPRING PIN



TE Part #2102429-1
Pin Assy, 320 Psn, Tin
Lead, Mezalok



TE Part #34228
SPLICE,BUDG BUTT 12-10



TE Part #6648259-1
SA END CAP, FIXED




TE Part #DTS26W25-29SA
PLUG ASSY




TE Part #5-2176087-2
RP 1J 0.166W 237R 0.1%
25PPM 1K RL



TE Part #2-2176075-8
3640 0201 2.8nH +/-0.2nH
1K RL



TE Part #6648454-1
MODULE, DOMINO



TE Part #6648499-1
M MODULE, PIN, DOMINO,
EXT THD



TE Part #563049-000
ST63-3-55-20-90



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-2176075-4_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2176075-4_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2176075-4_BA.3d_stp.zip](#)

English

Datasheets & Catalog Pages

[High Frequency Inductors SMD - Type 3640 Series - Tyco Electronics Passives](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2176075-4](#)