





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AB1	REVISED PER ECN-22-177079	29SEP2022	RK	MF





SECTION A-A



RECOMMENDED HOLE LAYOUT

- ① .000100 BRIGHT TIN—LEAD OVER .000050 NICKEL.
- ② POINT OF MEASUREMENT FOR PLATING THICKNESS.
- ③ THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- ④ ON ASSEMBLIES WITH FOUR OR MORE POSITIONS,
TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS,
ONE POLARIZATION SLOT.
- ⑤ .000100 BRIGHT TIN OVER .000050 NICKEL.
- ⑥ PRELIMINARY PART—NOT RELEASED FOR PRODUCTION.
- ⑦ .000100 MATTE TIN OVER .000050 NICKEL.
- ⑧ HIGH TEMPERATURE CONFIGURATION
- ⑨ STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- ⑩ SUPERSEDED BY P/N 5-103639-2.
- ⑪ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI
- ⑫ 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD
SHUT OFF

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.SHUEY 05MAR91		 TE Connectivity						
		CHK L.CASTAGNA 27MAR93								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L.CASTAGNA 27MAR93		NAME HDR ASY,VERT,SNGL ROW 2.54[100] C/L 0.64[025] SQ PST, WTH PLZN<CHNG,AMPMODU MTE				
		PRODUCT SPEC 108-25034								
		APPLICATION SPEC 114-25026								
		ANGLES ± -								
MATERIAL		FINISH		WEIGHT —	SIZE A2	CAGE CODE —	DRAWING NO C-103639	RESTRICTED TO —		
HOUSING:		SEE TABLE		CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 2	REV AR

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-103639-3](#)