

HYDRAULIC HANDTOOL HP 60 H,INCL.DIE SETS

✓ ACTIVE



AMP

TE Part # 1110956-7

TE Internal #: 1110956-7

[View on TE.com >](#)

Application Tooling > Portable Crimp Tools



Die Sets Type: **Removable/Interchangeable**

Certification: **Cannot be Certified**

Power Type: **Manual**

Tool Type: **Die Assembly**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Other
Die Sets Type	Removable/Interchangeable
Certification	Cannot be Certified
Power Type	Manual
Tool Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JUN 2016 (169)
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability









Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought

 <p>TE Part #1-1633919-6 ANVIL COMBINATION</p>	 <p>TE Part #2150234-1 OCEAN_2.0_APPLICATOR-E-110F180F</p>	 <p>TE Part #2151266-1 OCEAN-2.0-APPLICATOR-S-070F080BX</p>	 <p>TE Part #2836860-2 OCEAN_2.0_APPLICATOR-S-110F180F</p>
 <p>TE Part #3-1633932-1 ANVIL, COMBINATION</p>	 <p>TE Part #3-1803001-6 ANVIL, COMBINATION, END FEED</p>	 <p>TE Part #040488-000 RMW-63/19-1000/ADH-0</p>	 <p>TE Part #364306-000 RMW-75/22-1000/ADH-0</p>

Documents

Product Drawings
HYDRAULIC HANDTOOL HP 60 H,INCL.DIE SETS
German

Datasheets & Catalog Pages
Heavy Duty Connectors
English
CRIMPING WHERE FORM MEETS FUNCTION
English
Crimp Term Whitepaper-Use the Right Tool 1-1773953-1
English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1110956-7](#)