




Harnessing > Heat Shrink Components > Heat Shrink Boots



Molded Part Shape: **Straight**
Molded Part Shape Code: **202**
Lipped: **Yes**
Material Code: **3**
Material Systems Code: **10**

Features

Product Type Features

Molded Part Shape	Straight
-------------------	----------

Configuration Features

Lipped	Yes
--------	-----

Body Features

Material Code	3
Material Systems Code	10
Adhesive Pre-Coat	Yes
Material	Semi-Rigid Modified Polyolefin

Dimensions

Wire/Cable Outside Diameter	.9 in, .94 in, 1 in, 1.02 in, 1.1 in, 1.18 in, 1.26 in, 1.34 in, 1.42 in, 1.5 in, 24 mm, 26 mm, 28 mm, 30 mm, 32 mm, 34 mm, 36 mm, 38 mm
Cable Diameter Range	20.3 – 45.7 mm[.799 – 1.799 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Operation/Application

Power Cable Accessory	No
-----------------------	----

Industry Standards

Approved Standards	BS-G-198-5-DA, DEF Std 59-97 Issue 3 Type DA, SAE AS I 81765/1, Type I, UL 224,
--------------------	--



	File E85381
Government Qualified	No
Other	
Molded Part Shape Code	202
Fluid/Chemical Resistance	Occasional exposure to fluids
Adhesive Type	General Purpose Pre-Coat Adhesive

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Part # CJ2087-000
[HL2010E-KIT-120V](#)

Customers Also Bought




TE Part #251643N001
[202D174-12-60-0-CS5077](#)




TE Part #1-1811928-4
[8Q8 Size 25 Plug,A Key, OD](#)



TE Part #658937-000
[201M103-19B](#)



TE Part #722909-000
[55A0832-12-9/93/96CS2275](#)



TE Part #685041-000
[D-500-0457-1-612-079](#)




TE Part #YDTS20W13-35SCV001
[RECP ASSY](#)



TE Part #YDTS24F13-98SN0000
[JAM NUT RECEPTACLE](#)



TE Part #YDTS24F15-35SB0000
[JAM NUT RECEPTACLE](#)



TE Part #5-1589487-3
[STM065M6HN = THRU-HOLE](#)



TE Part #1-1589475-5
[STM065PC2DC036N = WDUALOBE](#)

Documents

Product Drawings

[202D185-3/42-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_-3](#)

English

Product Specifications

[Product Specification](#)



English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

English

Safety Datasheet

French

Safety Datasheet

German

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

English

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

English

Safety Datasheet

German

Safety Datasheet

Safety Datasheet

Safety Datasheet

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202D185-3/42-0](#)