





P		LTR	DESCRIPTION	DATE	DWN	APVD
	AD1		REVISED PER ECN-22-174625	16SEP2022	RK	MF



1. .000100 BRIGHT TIN—LEAD OVER .000050 NICKEL.
2. POINT OF MEASUREMENT FOR PLATING THICKNESS.
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
4. ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
5. SELECT POST TAILS FORMED TO PROVIDE CONNECTOR HOLD DOWN UNTIL SOLDERED. CONFIGURATION ACCEPTS 0.69[.027]—2.03[.080] THICK PRINTED CIRCUIT BOARD. (SEE DETAIL Z).
6. .000100 BRIGHT TIN OVER .000050 NICKEL.
7. PRELIMINARY PART — NOT RELEASED FOR PRODUCTION.
8. .000100 MATTE TIN OVER .000050 NICKEL.
9. HIGH TEMPERATURE CONFIGURATION.
10. STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
11. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINIS
12. 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

				23.37 [.920]	25.27 [.995]	8	9	3-103669-0
				8.13 [.320]	10.03 [.395]	2	3	2-103669-9
				15.75 [.620]	17.65 [.695]	5	6	2-103669-8
				13.21 [.520]	15.11 [.595]	4	5	2-103669-7
				10.67 [.420]	12.57 [.495]	3	4	2-103669-6
				5.59 [.220]	7.49 [.295]	1	2	2-103669-5
	OBSOLETE			64.01 [2.520]	65.91 [2.595]	24	25	2-103669-4
	OBSOLETE			61.47 [2.420]	63.37 [2.495]	23	24	2-103669-3
	OBSOLETE			58.93 [2.320]	60.83 [2.395]	22	23	2-103669-2
	OBSOLETE			56.39 [2.220]	58.29 [2.295]	21	22	2-103669-1
	OBSOLETE			53.85 [2.120]	55.75 [2.195]	20	21	2-103669-0
				51.31 [2.020]	53.21 [2.095]	19	20	1-103669-9
	OBSOLETE			48.77 [1.920]	50.67 [1.995]	18	19	1-103669-8
	OBSOLETE			46.23 [1.820]	48.13 [1.895]	17	18	1-103669-7
				43.69 [1.720]	45.59 [1.795]	16	17	1-103669-6
				41.15 [1.620]	43.05 [1.695]	15	16	1-103669-5
	OBSOLETE			38.61 [1.520]	40.51 [1.595]	14	15	1-103669-4
				36.07 [1.420]	37.97 [1.495]	13	14	1-103669-3
				33.53 [1.320]	35.43 [1.395]	12	13	1-103669-2
				30.99 [1.220]	32.89 [1.295]	11	12	1-103669-1
				28.45 [1.120]	30.35 [1.195]	10	11	1-103669-0
				25.91 [1.020]	27.81 [1.095]	9	10	103669-9
				23.37 [.920]	25.27 [.995]	8	9	103669-8
				20.83 [.820]	22.73 [.895]	7	8	103669-7
				18.29 [.720]	20.19 [.795]	6	7	103669-6
				15.75 [.620]	17.65 [.695]	5	6	103669-5
				13.21 [.520]	15.11 [.595]	4	5	103669-4
				10.67 [.420]	12.57 [.495]	3	4	103669-3
				8.13 [.320]	10.03 [.395]	2	3	103669-2
				5.59 [.220]	7.49 [.295]	1	2	103669-1
		REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SHUEY 3-9-91 CHK 2-14-92 M. RIDER		 TE Connectivity	
DIMENSIONS: INCHES		TO FRANCES UNLESS OTHERWISE SPECIFIED		NAME	
		APPLIC. SPEC 108-25034 114-25026		HDR ASSY, VERT, SR 2.54 [100] C/L 0.64 [025] SQ POST WITH PLCN, AMPMODU MTE	
MATERIAL		WEIGHT		SIZE GAGE CODE DRAWING NO A1 00779 C-103669	
HOUSING: LCP, CONTACTS: BRASS		SEE TABLE		RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 2 REV AD1	

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

11

OBSOLETE


9 10	8	64.01 [2.520]	65.91 [2.595]	24	25	7-103669-4
9 10	8	61.47 [2.420]	63.37 [2.495]	23	24	7-103669-3
9 10	8	58.93 [2.320]	60.83 [2.395]	22	23	7-103669-2
9 10	8	56.39 [2.220]	58.29 [2.295]	21	22	7-103669-1
9 10	8	53.85 [2.120]	55.75 [2.195]	20	21	7-103669-0
9 10	8	51.31 [2.020]	53.21 [2.095]	19	20	6-103669-9
9 10	8	48.77 [1.920]	50.67 [1.995]	18	19	6-103669-8
9 10	8	46.23 [1.820]	48.13 [1.895]	17	18	6-103669-7
9 10	8	43.69 [1.720]	45.59 [1.795]	16	17	6-103669-6
9 10	8	41.15 [1.620]	43.05 [1.695]	15	16	6-103669-5
9 10	8	38.61 [1.520]	40.51 [1.595]	14	15	6-103669-4
9 10	8	36.07 [1.420]	37.97 [1.495]	13	14	6-103669-3
9 10	8	33.53 [1.320]	35.43 [1.395]	12	13	6-103669-2
9 10	8	30.99 [1.220]	32.89 [1.295]	11	12	6-103669-1
9 10	8	28.45 [1.120]	30.35 [1.195]	10	11	6-103669-0
9 10	8	25.91 [1.020]	27.81 [1.095]	9	10	5-103669-9
9 10	8	23.37 [.920]	25.27 [.995]	8	9	5-103669-8
9 10	8	20.83 [.820]	22.73 [.895]	7	8	5-103669-7
9 10	8	18.29 [.720]	20.19 [.795]	6	7	5-103669-6
9 10	8	15.75 [.620]	17.65 [.695]	5	6	5-103669-5
9 10	8	13.21 [.520]	15.11 [.595]	4	5	5-103669-4
9 10	8	10.67 [.420]	12.57 [.495]	3	4	5-103669-3
9 10	8	8.13 [.320]	10.03 [.395]	2	3	5-103669-2
9 10	8	5.59 [.220]	7.49 [.295]	1	2	5-103669-1
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

11

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC ± .005

1. PLC ± .005

2. PLC ± .005

3. PLC ± .005

4. PLC ± .005

ANGLES ± .005

MATERIAL

HOUSING: LCP,
CONTACTS: BRASS

DWN
S. SHUEY
3-5-91

CHK
M. RIDER
2-14-92

APVD
M. RIDER
2-14-92

NAME

PRODUCT SPEC
108-25034

APPLICATION SPEC
114-25026

WEIGHT
—

CUSTOMER DRAWING

TE Connectivity

HDR ASSY, VERT, SR
2.54 .100 C/L 0.64 .025 SQ POST
WITH PLZN, AMPMODU MTE

SIZE
A1

CAGE CODE
00779

DRAWING NO
103669

RESTRICTED TO
—

SCALE
4:1

SHEET
2

OF
2

REV
AD1

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-103669-4](#)