



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H5	REVISED PER ECN-22-166059	25JUL2022	RK	MF



RECOMMENDED HOLE LAYOUT

- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 2 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 3 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 4 .000030 GOLD IN CONTACT AREA, .000100—.000200 MATTE TIN—LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 5 BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- 6 .000030 GOLD IN CONTACT AREA, .000100—.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 7 HIGH TEMPERATURE CONFIGURATION
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

		7	6	3.984	3.900	39	40	9-103765-0	
		7	6	3.484	3.400	34	35	8-	-5
		7	6	2.984	2.900	29	30	8-	-0
		7	6	2.484	2.400	24	25	7-	-5
		7	6	1.984	1.900	19	20	7-	-0
		7	6	1.484	1.400	14	15	6-	-5
		7	6	1.384	1.300	13	14	6-	-4
		7	6	1.284	1.200	12	13	6-	-3
		7	6	1.184	1.100	11	12	6-	-2
		7	6	1.084	1.000	10	11	6-	-1
		7	6	.984	.900	9	10	6-	-0
		7	6	.884	.800	8	9	5-	-9
		7	6	.784	.700	7	8	5-	-8
		7	6	.684	.600	6	7	5-	-7
		7	6	.584	.500	5	6	5-	-6
		7	6	.484	.400	4	5	5-	-5
		7	6	.384	.300	3	4	5-	-4
		7	6	.284	.200	2	3	5-	-3
		7	6	.184	.100	1	2	5-	-2
		7	6	.084	—	—	1	5-103765-1	
	OBSOLETE		4	3.984	3.900	39	40	4-103765-0	
	OBSOLETE		4	3.884	3.800	38	39	3-	-9
	OBSOLETE		4	3.784	3.700	37	38	3-	-8
	OBSOLETE		4	3.684	3.600	36	37	3-	-7
	OBSOLETE		4	3.584	3.500	35	36	3-	-6
8	OBSOLETE		4	3.484	3.400	34	35	3-	-5
	OBSOLETE		4	3.284	3.300	33	34	3-	-4
	OBSOLETE		4	3.284	3.200	32	33	3-	-3
	OBSOLETE		4	3.184	3.100	31	32	3-	-2
	OBSOLETE		4	3.084	3.000	30	31	3-	-1
8	OBSOLETE		4	2.984	2.900	29	30	3-	-0
	OBSOLETE		4	2.884	2.800	28	29	2-	-9
	OBSOLETE		4	2.784	2.700	27	28	2-	-8
	OBSOLETE		4	2.684	2.600	26	27	2-	-7
	OBSOLETE		4	2.584	2.500	25	26	2-	-6
8	OBSOLETE		4	2.484	2.400	24	25	2-	-5
	OBSOLETE		4	2.384	2.300	23	24	2-	-4
	OBSOLETE		4	2.284	2.200	22	23	2-	-3
	OBSOLETE		4	2.184	2.100	21	22	2-	-2
	OBSOLETE		4	2.084	2.000	20	21	2-	-1
	OBSOLETE		4	1.984	1.900	19	20	2-	-0
	OBSOLETE		4	1.884	1.800	18	19	1-	-9
	OBSOLETE		4	1.784	1.700	17	18	1-	-8
	OBSOLETE		4	1.684	1.600	16	17	1-	-7
	OBSOLETE		4	1.584	1.500	15	16	1-	-6
	OBSOLETE		4	1.484	1.400	14	15	1-	-5
BY 6-103765-4			4	1.384	1.300	13	14	1-	-4
8	OBSOLETE		4	1.284	1.200	12	13	1-	-3
	OBSOLETE		4	1.184	1.100	11	12	1-	-2
BY 6-103765-1			4	1.084	1.000	10	11	1-	-1
	8		4	.984	.900	9	10	1-	-0
	OBSOLETE		4	.884	.800	8	9		-9
8	OBSOLETE		4	.784	.700	7	8		-8
	OBSOLETE		4	.684	.600	6	7		-7
	OBSOLETE		4	.584	.500	5	6		-6
	OBSOLETE		4	.484	.400	4	5		-5
	OBSOLETE		4	.384	.300	3	4		-4
	OBSOLETE		4	.284	.200	2	3		-3
	OBSOLETE		4	.184	.100	1	2		-2
8	OBSOLETE		4	.084	—	—	1	103765-1	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. D. RINGLEY CHK R. ELICKER	24JUL85 24JUL85	 TE Connectivity	
DIMENSIONS: INCHES		APVD R. ELICKER	24JUL85		
TOLERANCES, UNLESS OTHERWISE SPECIFIED: INCHES 		NAME ASSY, MOD II, HEADER, BREAKAWAY, SR, RIGHT ANGLE 100, , WITH .025 SQUARE POSTS		RESTRICTED TO —	
0 PLC ± .— 1 PLC ± .— 2 PLC ± .— 3 PLC ± .005 4 PLC ± .— ANGLES ± .—		PRODUCT SPEC — APPLICATION SPEC —			
MATERIAL HOUSING: FLAME RETARDANT NONPHOSPHORIC COLOR-BLACK POSTS: COPPER ALLOY	FINISH SEE TABLE	WEIGHT —	SIZE A1	CAGE CODE 00779	DRAWING NO C-103765
CUSTOMER DRAWING			SCALE 4:1	SHEET 1	OF 1 REV H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103765-3](#)