




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	REVISED PER ECO-17-002210	10APR2017	RS	MM
	S	REVISED PER ECO-20-001323	19JUN2020	SM	JO

- 1 0.000381 [.000015] GOLD IN THE CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 THE NOTED DIMENSIONS APPLY FROM THE BASIC DIMENSION LINE (NOT THE POST CENTERLINE) TO THE SURFACE INDICATED
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 DIMENSIONS NOTED ARE FOR SOLDER STENCIL LAYOUT FOR USE WITH A 1.57±0.20 [.062±.008] THICK. PRINTED CIRCUIT BOARD
- 6 PARTS ARE PACKAGED IN GANG OF TUBES
- 7 0.000381 [.000015] GOLD IN THE CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON THE SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 9 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

SEE SHEET 2 FOR PART NUMBER TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G DOUTY 2-22-88	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK T C CLARK 2-22-88			
		APVD T C CLARK 2-22-88	NAME		
		PRODUCT SPEC	HEADER ASSY, AMPMODU MTE, RIGHT ANGLE, SINGLE ROW, .100 POSTS, WITH LATCH & HOLD DOWNS		
MATERIAL HOUSING : LCP COLOR : BLACK POSTS : BRASS		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
		FINISH	A2	00779	C=104361
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT	RESTRICTED TO		
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		CUSTOMER DRAWING	SCALE	SHEET	REV
SEE TABLE			4:1	1 OF 2	S

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - By -		ALL RIGHTS RESERVED.	

P		LTR	DESCRIPTION	DATE	DWN	APVD
		-	SEE SHEET 1	-	-	-

7	65.91	[2.595]	64.01	[2.520]	60.96	[2.400]	24	25	7-104361-4	
7	63.37	[2.495]	61.47	[2.420]	58.42	[2.300]	23	24	7-104361-3	
7	60.83	[2.395]	58.93	[2.320]	55.88	[2.200]	22	23	7-104361-2	
7	58.29	[2.295]	56.39	[2.220]	53.34	[2.100]	21	22	7-104361-1	
7	55.75	[2.195]	53.85	[2.120]	50.8	[2.000]	20	21	7-104361-0	
7	53.21	[2.095]	51.31	[2.020]	48.26	[1.900]	19	20	6-104361-9	
7	50.67	[1.995]	48.77	[1.920]	45.72	[1.800]	18	19	6-104361-8	
7	48.13	[1.895]	46.23	[1.820]	43.18	[1.700]	17	18	6-104361-7	
7	45.59	[1.795]	43.69	[1.720]	40.64	[1.600]	16	17	6-104361-6	
7	43.05	[1.695]	41.15	[1.620]	38.1	[1.500]	15	16	6-104361-5	
7	40.51	[1.595]	38.61	[1.520]	35.56	[1.400]	14	15	6-104361-4	
7	37.97	[1.495]	36.07	[1.420]	33.02	[1.300]	13	14	6-104361-3	
7	35.43	[1.395]	33.53	[1.320]	30.48	[1.200]	12	13	6-104361-2	
7	32.89	[1.295]	30.99	[1.220]	27.94	[1.100]	11	12	6-104361-1	
7	30.35	[1.195]	28.45	[1.120]	25.4	[1.000]	10	11	6-104361-0	
7	27.81	[1.095]	25.91	[1.020]	22.86	[.900]	9	10	5-104361-9	
7	25.27	[.995]	23.37	[.920]	20.32	[.800]	8	9	5-104361-8	
7	22.73	[.895]	20.83	[.820]	17.78	[.700]	7	8	5-104361-7	
7	20.19	[.795]	18.29	[.720]	15.24	[.600]	6	7	5-104361-6	
7	17.65	[.695]	15.75	[.620]	12.7	[.500]	5	6	5-104361-5	
7	15.11	[.595]	13.21	[.520]	10.16	[.400]	4	5	5-104361-4	
7	12.57	[.495]	10.67	[.420]	7.62	[.300]	3	4	5-104361-3	
7	10.03	[.395]	8.13	[.320]	5.08	[.200]	2	3	5-104361-2	
7	7.49	[.295]	5.59	[.220]	2.54	[.100]	1	2	5-104361-1	
8	SUPERSEDED BY 7-104361-4									
8	SUPERSEDED BY 7-104361-3									
8	SUPERSEDED BY 7-104361-2									
8	SUPERSEDED BY 7-104361-1									
8	SUPERSEDED BY 7-104361-0									
8	SUPERSEDED BY 6-104361-8									
8	SUPERSEDED BY 6-104361-7									
8	SUPERSEDED BY 6-104361-6									
8	SUPERSEDED BY 6-104361-5									
8	SUPERSEDED BY 6-104361-4									
8	SUPERSEDED BY 6-104361-3									
8	SUPERSEDED BY 6-104361-2									
8	SUPERSEDED BY 6-104361-1									
8	SUPERSEDED BY 6-104361-0									
1	65.91	[2.595]	64.01	[2.520]	60.96	[2.400]	24	25	2-104361-4	
1	63.37	[2.495]	61.47	[2.420]	58.42	[2.300]	23	24	2-104361-3	
1	60.83	[2.395]	58.93	[2.320]	55.88	[2.200]	22	23	2-104361-2	
1	58.29	[2.295]	56.39	[2.220]	53.34	[2.100]	21	22	2-104361-1	
1	55.75	[2.195]	53.85	[2.120]	50.8	[2.000]	20	21	2-104361-0	
1	53.21	[2.095]	51.31	[2.020]	48.26	[1.900]	19	20	1-104361-9	
1	50.67	[1.995]	48.77	[1.920]	45.72	[1.800]	18	19	1-104361-8	
1	48.13	[1.895]	46.23	[1.820]	43.18	[1.700]	17	18	1-104361-7	
1	45.59	[1.795]	43.69	[1.720]	40.64	[1.600]	16	17	1-104361-6	
1	43.05	[1.695]	41.15	[1.620]	38.1	[1.500]	15	16	1-104361-5	
1	40.51	[1.595]	38.61	[1.520]	35.56	[1.400]	14	15	1-104361-4	
1	37.97	[1.495]	36.07	[1.420]	33.02	[1.300]	13	14	1-104361-3	
1	35.43	[1.395]	33.53	[1.320]	30.48	[1.200]	12	13	1-104361-2	
1	32.89	[1.295]	30.99	[1.220]	27.94	[1.100]	11	12	1-104361-1	
1	30.35	[1.195]	28.45	[1.120]	25.4	[1.000]	10	11	1-104361-0	
1	27.81	[1.095]	25.91	[1.020]	22.86	[.900]	9	10	104361-9	
1	25.27	[.995]	23.37	[.920]	20.32	[.800]	8	9	104361-8	
1	22.73	[.895]	20.83	[.820]	17.78	[.700]	7	8	104361-7	
1	20.19	[.795]	18.29	[.720]	15.24	[.600]	6	7	104361-6	
1	17.65	[.695]	15.75	[.620]	12.7	[.500]	5	6	104361-5	
1	15.11	[.595]	13.21	[.520]	10.16	[.400]	4	5	104361-4	
1	12.57	[.495]	10.67	[.420]	7.62	[.300]	3	4	104361-3	
1	10.03	[.395]	8.13	[.320]	5.08	[.200]	2	3	104361-2	
1	7.49	[.295]	5.59	[.220]	2.54	[.100]	1	2	104361-1	
PLATING		D		C		B		A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G DOUTY 2-22-88	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK T C CLARK 2-22-88				
		APVD T C CLARK 2-22-88	NAME HEADER ASSY, AMPMODU MTE, RIGHT ANGLE, SINGLE ROW, .100 POSTS, WITH LATCH & HOLD DOWNS			
		PRODUCT SPEC —				
MATERIAL HOUSING : LCP COLOR : BLACK POSTS : BRASS		APPLICATION SPEC —	SIZE A2 CAGE CODE 00779 DRAWING NO C=104361			
		WEIGHT —				
SEE TABLE		CUSTOMER DRAWING		SCALE 4:1	SHEET 2 OF 2	REV S

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104361-7](#)