




What can we help you find?

[Products](#) [Industries](#) [Resources](#) [About TE](#) [My Account](#) [Innovation](#) [Support Center](#)**81044/12-26-9 Product Details**[Share](#)[Print](#)[Email](#)**81044/12-26-9**

(M81044/12-26-9)

TE Internal Number: 282206-005



Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Cable Type = Spec 44
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 26 AWG
- Voltage Rating = 600 VAC

[View all Features](#)**Quick Links**

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)**Documentation & Additional Information****Product Drawings:**

- [WIRE, ELECTRIC, RADIATION-CROSSLINKED, TIN-COATED CO ...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)**Product Features (Please use the Product Drawing for all design activity)****Product Type Features:**

- [Cable Type](#) = Spec 44
- [Cable Style](#) = Primary

Electrical Characteristics:

- Voltage Rating (VAC) = 600

Dimensions:

- Conductor Outer Diameter (mm [in]) = 0.50 [0.020]

Body Features:

- Wire Size (AWG/CM) = 26 AWG
- Conductor Type = Tin-Plated Copper
- Wire Color = White
- Nominal Outside Diameter (mm [in]) = 0.86 [0.034]
- Wire Diameter (mm [in]) = 0.86 [0.034]

Configuration Features:

- Number of Conductors = 1

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M81044/12-26-9
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Range (°C) = -65 - +150
- Wire Size - Details = 26 AWG 0.15 mm², 0.00024 in², 19 x 38 AWG

Operation/Application:

- Application = General Purpose - Lightweight

Packaging Features:

- Wire Source = United States

Other:

- Brand = Raychem

Corporate Information[About TE](#)[Investors](#)[News Room](#)[Supplier Portal](#)**Quick Links**[Distributor Inventory](#)[Product Cross Reference](#)[Documents & Drawings](#)[Product Compliance Support Center](#)**Customer Support**[Email or Chat With Us](#)[Find a Phone Number](#)[Knowledge Base](#)[Manage Your Account](#)

- Careers
- Site Map
- Terms & Conditions
- Privacy Policy
- AODA Accessibility Policy
- AODA Multi-Year Accessibility Plan

Keep Me Informed



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M81044/12-26-9](#)