

D

D

C

C

B


B

A

A

- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 4 POST PLATING: 0.00254–0.00508[.000100–.000200] MATTE TIN–LEAD OVER 0.00127[.000050] NICKEL ENTIRE POST.
- 5 HOUSING: LCP, COLOR–BLACK.
- 6 POST MATERIAL: COPPER ALLOY.
- 7 .000100–.000200 BRIGHT TIN OVER .000050 NICKEL ENTIRE POST.
- 8 POST PLATING: 0.00254–0.00508[.000100–.000200] MATTE TIN OVER 0.00127[.000050] NICKEL ENTIRE POST.
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
K2		REVISED PER ECN–22–185269	18NOV2022	RK	MF



RECOMMENDED PC BOARD MOUNTING DIMENSIONS
FOR .063 [1.60] THICK PC BOARD AND
.012 [.305] STENCIL THICK.

8	101.19 [3.984]	99.06 [3.900]	39	80	9–146250–0
8	98.65 [3.884]	96.52 [3.800]	38	78	8–146250–9
8	96.11 [3.784]	93.98 [3.700]	37	76	8–146250–8
8	93.57 [3.684]	91.44 [3.600]	36	74	8–146250–7
8	91.03 [3.584]	88.90 [3.500]	35	72	8–146250–6
8	88.49 [3.484]	86.36 [3.400]	34	70	8–146250–5
8	85.95 [3.384]	83.82 [3.300]	33	68	8–146250–4
8	83.41 [3.284]	81.28 [3.200]	32	66	8–146250–3
8	80.87 [3.184]	78.74 [3.100]	31	64	8–146250–2
8	78.33 [3.084]	76.20 [3.000]	30	62	8–146250–1
8	75.79 [2.984]	73.66 [2.900]	29	60	8–146250–0
8	73.25 [2.884]	71.12 [2.800]	28	58	7–146250–9
8	70.71 [2.784]	68.58 [2.700]	27	56	7–146250–8
8	68.17 [2.684]	66.04 [2.600]	26	54	7–146250–7
8	65.63 [2.584]	63.5 [2.500]	25	52	7–146250–6
8	63.09 [2.484]	60.96 [2.400]	24	50	7–146250–5
8	60.55 [2.384]	58.42 [2.300]	23	48	7–146250–4
8	58.01 [2.284]	55.88 [2.200]	22	46	7–146250–3
8	55.47 [2.184]	53.34 [2.100]	21	44	7–146250–2
8	52.93 [2.084]	50.80 [2.000]	20	42	7–146250–1
8	50.39 [1.984]	48.26 [1.900]	19	40	7–146250–0
8	47.85 [1.884]	45.72 [1.800]	18	38	6–146250–9
8	45.31 [1.784]	43.18 [1.700]	17	36	6–146250–8
8	42.77 [1.684]	40.64 [1.600]	16	34	6–146250–7
8	40.23 [1.584]	38.10 [1.500]	15	32	6–146250–6
8	37.69 [1.484]	35.56 [1.400]	14	30	6–146250–5
8	35.15 [1.384]	33.02 [1.300]	13	28	6–146250–4
8	32.61 [1.284]	30.48 [1.200]	12	26	6–146250–3
8	30.07 [1.184]	27.94 [1.100]	11	24	6–146250–2
8	27.53 [1.084]	25.40 [1.000]	10	22	6–146250–1
8	24.99 [.984]	22.86 [.900]	9	20	6–146250–0
8	22.45 [.884]	20.32 [.800]	8	18	5–146250–9
8	19.91 [.784]	17.78 [.700]	7	16	5–146250–8
8	17.37 [.684]	15.24 [.600]	6	14	5–146250–7
8	14.83 [.584]	12.70 [.500]	5	12	5–146250–6
8	12.29 [.484]	10.16 [.400]	4	10	5–146250–5
8	9.75 [.384]	7.62 [.300]	3	8	5–146250–4
8	7.21 [.284]	5.08 [.200]	2	6	5–146250–3
8	4.67 [.184]	2.54 [.100]	1	4	5–146250–2
8	[–]	[–]	0	2	5–146250–1
PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER

9	OBSELETE	4	101.19 [3.984]	99.06 [3.900]	39	80	4-146250-0	
	9 OBSELETE	4	98.65 [3.884]	96.52 [3.800]	38	78	3-146250-9	
		4	96.11 [3.784]	93.98 [3.700]	37	76	3-146250-8	
		4	93.57 [3.684]	91.44 [3.600]	36	74	3-146250-7	
		4	91.03 [3.584]	88.90 [3.500]	35	72	3-146250-6	
	9 OBSELETE	4	88.49 [3.484]	86.36 [3.400]	34	70	3-146250-5	
		4	85.95 [3.384]	83.82 [3.300]	33	68	3-146250-4	
		4	83.41 [3.284]	81.28 [3.200]	32	66	3-146250-3	
		4	80.87 [3.184]	78.74 [3.100]	31	64	3-146250-2	
		4	78.33 [3.084]	76.20 [3.000]	30	62	3-146250-1	
		4	75.79 [2.984]	73.66 [2.900]	29	60	3-146250-0	
		4	73.25 [2.884]	71.12 [2.800]	28	58	2-146250-9	
		4	70.71 [2.784]	68.58 [2.700]	27	56	2-146250-8	
		4	68.17 [2.684]	66.04 [2.600]	26	54	2-146250-7	
		4	65.63 [2.584]	63.5 [2.500]	25	52	2-146250-6	
		4	63.09 [2.484]	60.96 [2.400]	24	50	2-146250-5	
		4	60.55 [2.384]	58.42 [2.300]	23	48	2-146250-4	
		4	58.01 [2.284]	55.88 [2.200]	22	46	2-146250-3	
		4	55.47 [2.184]	53.34 [2.100]	21	44	2-146250-2	
		4	52.93 [2.084]	50.80 [2.000]	20	42	2-146250-1	
9		OBSELETE	4	50.39 [1.984]	48.26 [1.900]	19	40	2-146250-0
	9 OBSELETE	4	47.85 [1.884]	45.72 [1.800]	18	38	1-146250-9	
		4	45.31 [1.784]	43.18 [1.700]	17	36	1-146250-8	
		4	42.77 [1.684]	40.64 [1.600]	16	34	1-146250-7	
		4	40.23 [1.584]	38.10 [1.500]	15	32	1-146250-6	
		4	37.69 [1.484]	35.56 [1.400]	14	30	1-146250-5	
		4	35.15 [1.384]	33.02 [1.300]	13	28	1-146250-4	
		4	32.61 [1.284]	30.48 [1.200]	12	26	1-146250-3	
		4	30.07 [1.184]	27.94 [1.100]	11	24	1-146250-2	
		4	27.53 [1.084]	25.40 [1.000]	10	22	1-146250-1	
		4	24.99 [.984]	22.86 [.900]	9	20	1-146250-0	
	9 OBSELETE	4	22.45 [.884]	20.32 [.800]	8	18	146250-9	
		4	19.91 [.784]	17.78 [.700]	7	16	146250-8	
	9 SUPERCEDED	4	17.37 [.684]	15.24 [.600]	6	14	146250-7	
	9 OBSELETE	4	14.83 [.584]	12.70 [.500]	5	12	146250-6	
	9 SUPERCEDED	4	12.29 [.484]	10.16 [.400]	4	10	146250-5	
	9	OBSELETE	7	9.75 [.384]	7.62 [.300]	3	8	146250-4
		9	4	7.21 [.284]	5.08 [.200]	2	6	146250-3
			4	4.67 [.184]	2.54 [.100]	1	4	146250-2
			4	- [-]	- [-]	0	2	146250-1
		PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± 0.5[.02]
2 PLC ± 0.13[.005]
3 PLC ± 0.013[.0005]
4 PLC ± –
ANGLES ± –

MATERIAL

FINISH
SEE TABLE

DWN
T. HOFFMAN
8MAY95

CHK
G. DUBNICZKI
7JUN95

APVD
G. DUBNICZKI
7JUN95

NAME

PRODUCT SPEC

APPLICATION SPEC

WEIGHT –

CUSTOMER DRAWING

SIZE
A1

CAGE CODE
00779

DRAWING NO
146250

RESTRICTED TO
–

TE Connectivity

HEADER ASSEMBLY, MOD II,
BREAKAWAY, DOUBLE ROW,
HIGH TEMPERATURE

SCALE 4:1

SHEET 1 OF 1

REV K2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-146250-0](#)