

URB12350

Technical Datasheet



LITHIUM POWER®

Li-Ion LFP Benefits Over SLA

- Uniform voltage during discharge
- No need to provide trickle charging to retain battery's charge
- Significantly lighter weight for the same amount of energy
- Battery does not become gaseous during use
- Nominal voltage is maintained over a wider temperature range

Features

- Integrated carry handles
- Can be properly charged using a 2 phase SLA charger
- IEC62133, 2nd edition compliant

Applications

- Scooters / wheelchairs
- UPS battery replacement
- Solar battery

Technical Specifications

Part No	URB12350
Chemistry	Lithium Iron Phosphate (LFP)
IEC Designation	4IFR27/66-10
Average Voltage	12.8V
Nominal Capacity ¹	32.0Ah
Voltage Range	10.0V - 14.4V
Max. Continuous Discharge	65.0A
Max. Pulse Discharge ²	250 ± 10A
Energy ¹	410Wh
Energy Density	89Wh/kg, 105Wh/l
Weight	Approx. 4.6 ± 0.1kg (10.14 ± 0.22lbs)
Cycle Life ³	>1500 cycles
Operating Temperature	-20°C to 60°C discharging 0°C to 45°C charging
Storage Temperature	0°C to 40°C
Internal Resistance	≤35mΩ
Self-Discharge @ 23°C	<5% per month
Memory Effect	None
Exterior/Housing	Hard plastic, ABS
Terminals/Connector	M6 Screw Terminals
Size	Length: 195 ± 1mm (7.71in) Width: 127 ± 1mm (5.16in) Height: 165 ± 1mm (6.10in)
Communications	None
State of Charge Indicator	None
Protection	Overcharge: 3.90V (per cell) Over Discharge: 2.00V (per cell) Over Current: 250 ± 10A (5-20ms) Over Temperature: 65 ± 5°C Short Circuit Cell Imbalance
Charging	Connect the battery to a DC power source using correct polarity and apply a maximum voltage of 14.4V. Limit the current to the recommended rate of 6.4A and hold 14.4V until the current declines to 640mA. Maximum charge rate is 32.0A. Alternatively, you may apply a maximum charge voltage of 13.6V (limiting the current to 6.4A) and hold indefinitely to maintain the battery in a continuous standby state-of-charge of between 70-90%.
Safety	Material Safety Datasheet - MSDS00152 Refer also to Safety Guide UBM-5112
Certification	CB Scheme ID: JPTUV-053719 UL 2054
Transportation	Class 9 International and within U.S. ⁴ Excepted when shipped by motorcar or rail within U.S.
Harmonized Tariff Schedule	8507.60.0000

Notes

1. Using a C/5 discharge rate at 25°C.
2. Maximum pulse width of between 5ms and 20ms.
3. Number of consecutive C/5 rate discharges and recommended charges at 25±5°C until the battery reaches 80% of initial capacity.
4. Transportation regulations, classifications and lithium content are available on the Ultralife website



Constant Voltage Charge at 23°C	Voltage Regulation	Initial Current	Maximum Current
Standby Use	13.6V	6.4A	32A
Cycle Use	14.4V	16A	32A

URB12350

Newark, New York | +1 315-332-7100 | Fax: +1 315-331-7800

©2017 Ultralife Corporation • www.ultralifecorp.com • All information is subject to change without notice.

The information contained herein is for reference only and does not constitute a warranty of performance. • 24 OCT 17 UBM-0081 Rev: E



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ultralife:](#)

[URB12350](#)