





IQS127D on AZP112A05 Connection Guide

1 IQS127D on AZP112A05




2 PC board (AZP112A05)



3 CT-Tool Connections

IQS127 pins	CT210(A) pins	
	Programming	Streaming
GND	1	1
VDDHI	3	3
POUT	5	
CX	6	
TOUT/DATA		10





The IQS127D ProxSense® IC is a fully integrated capacitive sensor device:

- ☐ **IQS127D:** Dual outputs (Touch button AND Proximity sensor).

Features

- ☐ Automatic **Antenna Tuning Implementation (ATI)** - Automatic adjustment for optimal performance.
- ☐ Internal **Capacitor Implementation (ICI)** – reference capacitor on-chip
- ☐ Low Power, suitable for battery applications
- ☐ Supply voltage: 2.95V to 5.5V
- ☐ Advanced on-chip digital signal processing
- ☐ User selectable:
 - 4 Power Modes (13uA min)
 - IO sink / source
 - Time-out for stuck key
 - Output mode (Direct / Latch / Toggle)
 - Proximity and Touch Button sensitivity settings
- ☐ Minimum external components
- ☐ Keys:
 - Touch: 5mm x 5mm or larger (overlay thickness dependent)
 - Proximity: Various electrical options (wire / PCB trace / ITO / conductive foil)
 - Dielectric: Various non-metal materials (i.e. glass, plastic, painted surfaces)
 - Dielectric thickness: 6 mm plastic, 10 mm glass
- ☐ 1-Wire data streaming

Contact Information

Please visit www.azoteq.com for comprehensive datasheets, application notes, reference designs and a list of distributors for your region.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Azoteq:](#)

[IQS127DEV01S](#)