



IQS72xxxEV01 USER GUIDE

IQ Switch® - ProxFusion® Series









Table of Contents

IQS72XXXEV01 USER GUIDE	1
1 INTRODUCTION	3
2 SETTING UP FOR THE IQS72XXX STAMP	4
3 IQS7211A STAMP	4
4 IQS7222A STAMP	5
5 IQS7222B STAMP	6
6 IQS7222C STAMP	7
7 REFERENCE DESIGNS	8



1 Introduction

This user guide describes the operation of the IQS72xxxEV01 Evaluation Kit. The EV-Kit consists of 5 parts:

- IQS7211A Stamp + 5 x IC's
- IQS7222A Stamp + 5 x IC's
- IQS7222B Stamp + 5 x IC's
- IQS7222C Stamp + 5 x IC's
- Connector board

To visualise raw data from the EV-Kit, the stamp board can be interfaced to any personal computer with USB support, along with the CT210A, (CT210A sold separately) and the relevant IQS72xxx software Graphical User Interface (GUI) available to download from the Azoteq website. The purpose of the IQS72xxxEV01 EV-Kit is to help application and development engineers in evaluating the range of IC's included in this Kit and their capabilities. A picture of the evaluation kit is shown below.




Figure 1-1: EV-Kit representation




2 Setting up for the IQS72xxx Stamp

To interface the IQS72xxx Stamp to a PC we advise using the CT210A. The (CT210A is sold separately from this EV-Kit. This EV Kit can be setup with the following steps:

- Download & Install GUI from Azoteq website
- Connect the CT210A to the PC with a USB cable (use USB data cable only)
- Plug the ribbon cable into the CT210A
- Connect the connector board to the ribbon cable.
- Connect the 6-way cable into connector board on one end and on the stamp board at the other.
- Run the IQS72xxx GUI (latest version available from the www.azoteq.com website)

3 IQS7211A Stamp


- Connect the CT210A to the connector board.
- Connect connector board to IQS7211A stamp.
- Run IQS7211A GUI (available from Azoteq.com website)
- Click “Start Streaming” button
- GUI should look as follow.





4 IQS7222A Stamp


- Connect the CT210A to the connector board.
- Connect connector board to IQS7222A stamp.
- Run IQS7222A GUI (available from Azoteq.com website)
- Click “Start Streaming” button
- GUI should look as follow.





5 IQS7222B Stamp


- Connect the CT210A to the connector board.
- Connect connector board to IQS7222B stamp.
- Run IQS7222B GUI (available from Azoteq.com website)
- Click “Start Streaming” button
- GUI should look as follow.





6 IQS7222C Stamp

- Connect the CT210A to the connector board.
- Connect connector board to IQS7222C stamp.
- Run IQS7222C GUI (available from Azoteq.com website)
- Click “Start Streaming” button
- GUI should look as follow.



7 Reference Designs





Figure 7-1 IQS72xxx QFN20 Stamp Layout



	USA	Asia	South Africa
Physical Address	11940 Jollyville Suite 120-S Austin TX 78750 USA	Room 501A, Block A, T-Share International Centre, Taoyuan Road, Nanshan District, Shenzhen, Guangdong, PRC	1 Bergsig Avenue Paarl 7646 South Africa
Postal Address	11940 Jollyville Suite 120-S Austin TX 78750 USA	Room 501A, Block A, T-Share International Centre, Taoyuan Road, Nanshan District, Shenzhen, Guangdong, PRC	PO Box 3534 Paarl 7620 South Africa
Tel	+1 512 538 1995	+86 755 8303 5294 ext 808	+27 21 863 0033
Email	info@azoteq.com	info@azoteq.com	info@azoteq.com

Visit www.azoteq.com
for a list of distributors and worldwide representation.

Patents as listed on www.azoteq.com/patents-trademarks/ may relate to the device or usage of the device.

Azoteq®, Crystal Driver®, IQ Switch®, ProxSense®, ProxFusion®, LightSense™, SwipeSwitch™, and the  logo are trademarks of Azoteq.

The information in this Datasheet is believed to be accurate at the time of publication. Azoteq uses reasonable effort to maintain the information up-to-date and accurate, but does not warrant the accuracy, completeness or reliability of the information contained herein. All content and information are provided on an "as is" basis only, without any representations or warranties, express or implied, of any kind, including representations about the suitability of these products or information for any purpose. Azoteq disclaims all warranties and conditions with regard to these products and information, including but not limited to all implied warranties and conditions of merchantability, fitness for a particular purpose, title and non-infringement of any third party intellectual property rights. Azoteq assumes no liability for any damages or injury arising from any use of the information or the product or caused by, without limitation, failure of performance, error, omission, interruption, defect, delay in operation or transmission, even if Azoteq has been advised of the possibility of such damages. The applications mentioned herein are used solely for the purpose of illustration and Azoteq makes no warranty or representation that such applications will be suitable without further modification, nor recommends the use of its products for application that may present a risk to human life due to malfunction or otherwise. Azoteq products are not authorized for use as critical components in life support devices or systems. No licenses to patents are granted, implicitly, express or implied, by estoppel or otherwise, under any intellectual property rights. In the event that any of the abovementioned limitations or exclusions does not apply, it is agreed that Azoteq's total liability for all losses, damages and causes of action (in contract, tort (including without limitation, negligence) or otherwise) will not exceed the amount already paid by the customer for the products. Azoteq reserves the right to alter its products, to make corrections, deletions, modifications, enhancements, improvements and other changes to the content and information, its products, programs and services at any time or to move or discontinue any contents, products, programs or services without prior notification. For the most up-to-date information and binding Terms and Conditions please refer to www.azoteq.com.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Azoteq:](#)

[IQS72xxEV01-S](#) [IQS72xxxEV01-S](#)