

KZH Series

- Newly innovative electrolyte is employed to minimize impedance
- Endurance with ripple current: 5,000 to 6,000 hours at 105°C
- Non solvent resistant type
- RoHS2 Compliant

KZM
↑ Longer life
KZH
↑ Lower Z
KZE




SPECIFICATIONS

Items	Characteristics						
Category	-40 to +105℃						
Temperature Range							
Rated Voltage Range	6.3 to 35V _{dc}						
Capacitance Tolerance	±20% (M) (at 20℃, 120Hz)						
Leakage Current	I=0.01CV or 3μA, whichever is greater. Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V) (at 20℃ after 2 minutes)						
Dissipation Factor (tan δ)	Rated voltage (V _{dc})	6.3V	10V	16V	25V	35V	
	tan δ (Max.)	0.22	0.19	0.16	0.14	0.12	
	When nominal capacitance exceeds 1,000μF, add 0.02 to the value above for each 1,000μF increase. (at 20℃, 120Hz)						
Low Temperature Characteristics (Max. Impedance Ratio)	Z (-25℃) / Z (+20℃)	2max.					
	Z (-40℃) / Z (+20℃)	3max.					
Endurance	(at 120Hz)						
	The following specifications shall be satisfied when the capacitors are restored to 20℃ after subjected to DC voltage with the rated ripple current is applied (the peak voltage shall not exceed the rated voltage)for the specified period of time at 105℃.						
	Time	φ 5 & φ 6.3 : 5,000hours φ 8 to φ 16 : 6,000hours					
	Capacitance change	≤ ±25% of the initial value (6.3, 10V _{dc} : ≤ ±30%)					
	D.F. (tan δ)	≤200% of the initial specified value					
Shelf Life	Leakage current	≤The initial specified value					
	The following specifications shall be satisfied when the capacitors are restored to 20℃ after exposing them for 500 hours at 105℃ without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4.						
	Capacitance change	≤ ±25% of the initial value (6.3, 10V _{dc} : ≤ ±30%)					
	D.F. (tan δ)	≤200% of the initial specified value					
	Leakage current	≤The initial specified value					


DIMENSIONS [mm]

Terminal Code : E



φD	5	6.3	8	10	12.5	16
φd	0.5	0.5	0.6	0.6	0.6	0.8
F	2.0	2.5	3.5	5.0	5.0	7.5
φD'	φD+0.5max.					
L'	L+1.5max.					

PART NUMBERING SYSTEM



Please refer to "Product code guide (radial lead type)"



◆STANDARD RATINGS

WV (V _{dc})	Cap (μF)	Case size φD×L(mm)	Impedance (Ω max./100kHz)		Rated ripple current (mA rms/ 105°C, 100kHz)	Part No.
			20°C	-10°C		
6.3	220	5×11	0.24	0.80	330	EKZH6R3E□□221ME11D
	470	6.3×11	0.11	0.35	500	EKZH6R3E□□471MF11D
	820	8×11.5	0.062	0.19	900	EKZH6R3E□□821MHB5D
	1,200	8×15	0.048	0.15	1,210	EKZH6R3E□□122MH15D
	1,200	10×12.5	0.045	0.14	1,240	EKZH6R3E□□122MJC5S
	1,500	8×20	0.033	0.11	1,410	EKZH6R3E□□152MH20D
	1,800	10×16	0.032	0.10	1,650	EKZH6R3E□□182MJ16S
	2,200	10×20	0.020	0.060	1,960	EKZH6R3E□□222MJ20S
	2,700	10×25	0.018	0.054	2,250	EKZH6R3E□□272MJ25S
	3,900	12.5×20	0.017	0.043	2,480	EKZH6R3E□□392MK20S
	4,700	12.5×25	0.015	0.038	2,900	EKZH6R3E□□472MK25S
	5,600	12.5×30	0.013	0.033	3,450	EKZH6R3E□□562MK30S
	6,800	12.5×35	0.012	0.031	3,570	EKZH6R3E□□682MK35S
	6,800	16×20	0.015	0.038	3,250	EKZH6R3E□□682ML20S
	8,200	16×25	0.013	0.035	3,630	EKZH6R3E□□822ML25S
10	150	5×11	0.24	0.80	330	EKZH100E□□151ME11D
	330	6.3×11	0.11	0.35	500	EKZH100E□□331MF11D
	680	8×11.5	0.062	0.19	900	EKZH100E□□681MHB5D
	1,000	8×15	0.048	0.15	1,210	EKZH100E□□102MH15D
	1,000	10×12.5	0.045	0.14	1,240	EKZH100E□□102MJC5S
	1,500	8×20	0.033	0.11	1,410	EKZH100E□□152MH20D
	1,500	10×16	0.032	0.10	1,650	EKZH100E□□152MJ16S
	1,800	10×20	0.020	0.060	1,960	EKZH100E□□182MJ20S
	2,200	10×25	0.018	0.054	2,250	EKZH100E□□222MJ25S
	3,300	12.5×20	0.017	0.043	2,480	EKZH100E□□332MK20S
	3,900	12.5×25	0.015	0.038	2,900	EKZH100E□□392MK25S
	4,700	12.5×30	0.013	0.033	3,450	EKZH100E□□472MK30S
	4,700	16×20	0.015	0.038	3,250	EKZH100E□□472ML20S
	5,600	12.5×35	0.012	0.031	3,570	EKZH100E□□562MK35S
	6,800	16×25	0.013	0.035	3,630	EKZH100E□□682ML25S
16	100	5×11	0.24	0.80	330	EKZH160E□□101ME11D
	220	6.3×11	0.11	0.35	500	EKZH160E□□221MF11D
	470	8×11.5	0.062	0.19	900	EKZH160E□□471MHB5D
	680	8×15	0.048	0.15	1,210	EKZH160E□□681MH15D
	680	10×12.5	0.045	0.14	1,240	EKZH160E□□681MJC5S
	1,000	8×20	0.033	0.11	1,410	EKZH160E□□102MH20D
	1,000	10×16	0.032	0.10	1,650	EKZH160E□□102MJ16S
	1,500	10×20	0.020	0.060	1,960	EKZH160E□□152MJ20S
25	1,800	10×25	0.018	0.054	2,250	EKZH160E□□182MJ25S
	2,200	12.5×20	0.017	0.043	2,480	EKZH160E□□222MK20S
	2,700	12.5×25	0.015	0.038	2,900	EKZH160E□□272MK25S
	3,300	12.5×30	0.013	0.033	3,450	EKZH160E□□332MK30S
	3,300	16×20	0.015	0.038	3,250	EKZH160E□□332ML20S
	3,900	12.5×35	0.012	0.031	3,570	EKZH160E□□392MK35S
	4,700	16×25	0.013	0.035	3,630	EKZH160E□□472ML25S
35	68	5×11	0.24	0.80	330	EKZH250E□□680ME11D
	150	6.3×11	0.11	0.35	500	EKZH250E□□151MF11D
	330	8×11.5	0.062	0.19	900	EKZH250E□□331MHB5D
	390	8×15	0.048	0.15	1,210	EKZH250E□□391MH15D
	470	10×12.5	0.045	0.14	1,240	EKZH250E□□471MJC5S
	560	8×20	0.033	0.11	1,410	EKZH250E□□561MH20D
	680	10×16	0.032	0.10	1,650	EKZH250E□□681MJ16S
	820	10×20	0.020	0.060	1,960	EKZH250E□□821MJ20S
	1,000	10×25	0.018	0.054	2,250	EKZH250E□□102MJ25S
	1,500	12.5×20	0.017	0.043	2,480	EKZH250E□□152MK20S
	1,800	12.5×25	0.015	0.038	2,900	EKZH250E□□182MK25S
	2,200	12.5×30	0.013	0.033	3,450	EKZH250E□□222MK30S
	2,200	16×20	0.015	0.038	3,250	EKZH250E□□222ML20S
	2,700	12.5×35	0.012	0.031	3,570	EKZH250E□□272MK35S
	3,300	16×25	0.013	0.035	3,630	EKZH250E□□332ML25S
50	47	5×11	0.24	0.80	330	EKZH350E□□470ME11D
	100	6.3×11	0.11	0.35	500	EKZH350E□□101MF11D
	220	8×11.5	0.062	0.19	900	EKZH350E□□221MHB5D
	270	8×15	0.048	0.15	1,210	EKZH350E□□271MH15D
	330	10×12.5	0.045	0.14	1,240	EKZH350E□□331MJC5S
	390	8×20	0.033	0.11	1,410	EKZH350E□□391MH20D
	470	10×16	0.032	0.10	1,650	EKZH350E□□471MJ16S
	560	10×20	0.020	0.060	1,960	EKZH350E□□561MJ20S
	680	10×25	0.018	0.054	2,250	EKZH350E□□681MJ25S
	1,000	12.5×20	0.017	0.043	2,480	EKZH350E□□102MK20S
	1,200	12.5×25	0.015	0.038	2,900	EKZH350E□□122MK25S
	1,500	12.5×30	0.013	0.033	3,450	EKZH350E□□152MK30S
	1,500	16×20	0.015	0.038	3,250	EKZH350E□□152ML20S
	1,800	12.5×35	0.012	0.031	3,570	EKZH350E□□182MK35S
	2,200	16×25	0.013	0.035	3,630	EKZH350E□□222ML25S

□□ : Enter the appropriate lead forming or taping code.

Production of the products shown in is scheduled to be discontinued.

◆RATED RIPLE CURRENT MULTIPLIERS

●Frequency Multipliers

Capacitance(μF)	Frequency(Hz)			
	120	1k	10k	100k
0.47 to 150	0.40	0.75	0.90	1.00
220 to 560	0.50	0.85	0.94	1.00
680 to 1,800	0.60	0.87	0.95	1.00
2,200 to 3,900	0.75	0.90	0.95	1.00
4,700 to 8,200	0.85	0.95	0.98	1.00

The deterioration of aluminum electrolytic capacitors accelerates their life due to the internal heating produced by ripple current. For details, refer to Section "5-3 Ripple Current Effect on Lifetime" in the catalog, Technical Note.



- Always read "Notes on Use" before using the product in order to enable you to use the product correctly and prevent any faults and accidents from occurring.
- Request the Product Specification on the product of NIPPON CHEMI-CON CORPORATION to refer to it as well as this brochure prior to the order of the products. Some specific notes on use of the ordered product may be described in the specifications.
- The products listed in this catalog are designed and manufactured for general electronics equipment use and are not intended for use in applications that can adversely affect human life; where the malfunction of equipment may cause damage to life or property. In addition, our products are not intended to be used in specific applications that may cause a major social impact. Please consult with us in advance of usage of our products in the following listed applications. ① Aerospace equipment ② Power generation equipment such as thermal power, nuclear power etc. ③ Medical equipment ④ Transport equipment (automobiles, trains, ships, etc.) ⑤ Transportation control equipment ⑥ Disaster prevention / crime prevention equipment ⑦ Highly publicized information processing equipment ⑧ Submarine equipment ⑨ Other applications that are not considered general-purpose applications.
- The circuits described as examples in this catalog and the "delivery specifications" are featured in order to show the operations and usage of our products, however, this fact does not guarantee that the circuits are available to function in your equipment systems. We are not in any case responsible for any failures or damage caused by the use of information contained herein. You should examine our products, of which the characteristics are described in the "delivery specifications" and other documents, and determine whether or not our products suit your requirements according to the specifications of your equipment systems. Therefore, you bear final responsibility regarding the use of our products.
Please make sure that you take appropriate safety measures such as use of redundant design and malfunction prevention measures in order to prevent fatal accidents and/or fires in the event any of our products malfunction.
- We strongly recommend our customers to purchase Nippon Chemi-Con products only through our official sales channels. We assume no responsibility for any defects or damages caused by using products purchased from outside our official sales channel or of counterfeit goods. In addition, we will ask the customer to pay the investigation cost for products purchased outside our official sales channel.
- We reserve the right to discontinue production and delivery of products. We do not guarantee that all the products included in this catalog will be available in the future.
The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products
- We continually strive to improve the quality and reliability of our products, but in any case that our product does not meet our published specifications, please stop using it promptly and contact us immediately. As for compensation for non-conforming goods delivered by Chemi-Con, we will limit it only to goods found in non-compliance of our published specifications. This may be accomplished by a no cost replacement of non-conforming individual products, a credit of the piece price paid per each individual non-conforming product, or in other ways deemed necessary.
In addition, we have an established system with enhanced traceability, therefore we will limit the applicable lot items for any potential compensation.

[Part Numbering System](#)

[Part Numbering System \(Appendix\)](#)

[Standardization](#)

[Available Items by Manufacturing Locations](#)

[Environmental Measures](#)

[Technical Note](#)

[Precautions and Guidelines](#)

[Recommended Soldering Conditions](#)

[Taping, Lead-preforming and Packaging](#)

[Available Terminals for Snap-in and Screw Mount Type](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chemi-Con:](#)

EKZH160ELL182MJ25S	EKZH250ELL102MJ25S	EKZH160ELL332MK30S	EKZH350ELL331MJC5S
EKZH350ELL122MK25S	EKZH350ELL182MK35S	EKZH250ELL182MK25S	EKZH160ETD471MHB5D
EKZH250ETD471MJC5S	EKZH100ELL102MH15D	EKZH100ELL151ME11D	EKZH100ELL182MJ20S
EKZH100ELL222MJ25S	EKZH100ELL331MF11D	EKZH100ELL332MK20S	EKZH100ELL472MK30S
EKZH100ELL472ML20S	EKZH100ELL562MK35S	EKZH100ELL681MHB5D	EKZH100ELL682ML25S
EKZH160ELL152MJ20S	EKZH160ELL392MK35S	EKZH160ELL472ML25S	EKZH160ELL681MH15D
EKZH250ELL222ML20S	EKZH250ELL272MK35S	EKZH250ELL332ML25S	EKZH250ELL680ME11D
EKZH350ELL152MK30S	EKZH350ELL271MH15D	EKZH350ELL471MJ16S	EKZH350ELL681MJ25S
EKZH6R3ELL122MH15D	EKZH6R3ELL182MJ16S	EKZH6R3ELL222MJ20S	EKZH6R3ELL272MJ25S
EKZH6R3ELL392MK20S	EKZH6R3ELL472MK25S	EKZH6R3ELL562MK30S	EKZH6R3ELL682MK35S
EKZH6R3ELL682ML20S	EKZH6R3ELL821MHB5D	EKZH6R3ELL822ML25S	EKZH250ELL331MHB5D
EKZH100ELL102MJC5S	EKZH6R3ELL152MH20D	EKZH160ELL102MJ16S	EKZH250ELL681MJ16S
EKZH250ELL152MK20S	EKZH350ELL221MHB5D	EKZH350ELL561MJ20S	EKZH350ELL152ML20S
EKZH160ELL221MF11D	EKZH100ELL152MH20D	EKZH100ELL152MJ16S	EKZH100ELL392MK25S
EKZH160ELL102MH20D	EKZH160ELL222MK20S	EKZH160ELL272MK25S	EKZH160ELL681MJC5S
EKZH160ETD101ME11D	EKZH160ETD332ML20S	EKZH250ELL151MF11D	EKZH250ELL222MK30S
EKZH250ELL391MH15D	EKZH250ELL561MH20D	EKZH250ETD821MJ20S	EKZH350ELL101MF11D
EKZH350ELL102MK20S	EKZH350ELL222ML25S	EKZH350ELL391MH20D	EKZH350ELL470ME11D
EKZH6R3ELL122MJC5S	EKZH6R3ELL471MF11D	EKZH6R3ETD221ME11D	EKZH250EMC102MJ20S
EKZH160ETC221MF11D	EKZH160ETC101ME11D	EKZH250ETD331MHB5D	EKZH160ETD221MF11D
EKZH350ELL470ME11S	EKZH350ETD221MHB5D	EKZH160ELL221MF11S	EKZH250ETD152MK20S
EKZH250ETD681MJ16S	EKZH100ETD102MJC5S	EKZH350ETD221MHB51	EKZH350ETE102MK20S
EKZH160ELL182MMJ25S	EKZH350ELL470ME111	EKZH6R3ETD471MF11D	EKZH350ETD470ME11D
EKZH350ETC101MF11D	EKZH6R3ETD122MJC5S	EKZH250ETD331MJC5S	EKZH160ETC471MHB5D
EKZH350E470ME11S	EKZH350E470ME111	EKZH250E331MHB5D	EKZH1603102MH20D