

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AA1	REVISED PER ECN-24-248739	22JAN2024	MM	LR





TABLE OF DIMENSIONS														
PART NUMBER	H			J			K MAX b	P ±10% b	JO ±10% b	S ±.03 b	T ±.03 b	W MIN b	B REF b	FIT SHIELD ADAPTER ENTRY SIZES
	MIN		MAX	MIN		MAX								
	-.71 a	50,51,770, 780 a 	b	-.71 a	50,51,770, 780 a 	b								
202C611	.69 [17,5]	.56 [14,2]	.27 [6,9]	.56 [14,2]	.44 [11,2]	.19 [4,8]	.83 [21,1]	4.75 [120,7]	.69 [17,5]	.06 [1,52]	.05 [1,27]	.013 [0,33]	2.46 [62,5]	03 THRU 05
202C621	1.04 [26,4]	.88 [22,4]	.46 [11,7]	1.04 [26,4]	.70 [17,8]	.32 [8,1]	1.05 [26,7]	5.25 [133,4]	.78 [19,8]	.06 [1,52]	.05 [1,27]	.018 [0,46]	2.67 [67,8]	06 THRU 09
202C632	1.50 [38,1]	1.34 [34,0]	.69 [17,5]	1.50 [38,1]	1.06 [26,9]	.50 [12,7]	1.29 [32,8]	5.75 [146,1]	.88 [22,4]	.07 [1,78]	.05 [1,27]	.020 [0,51]	2.89 [73,4]	10 THRU 12
202C642	1.88 [47,8]	1.74 [44,2]	.88 [22,4]	1.88 [47,8]	1.44 [36,6]	.69 [17,5]	1.49 [37,8]	6.25 [158,8]	1.00 [25,4]	.07 [1,78]	.05 [1,27]	.024 [0,61]	3.08 [78,2]	13 THRU 17
202C653	2.16 [54,9]	2.12 [53,8]	1.10 [27,9]	2.16 [54,9]	1.80 [45,7]	.88 [22,4]	1.69 [42,9]	6.75 [171,5]	1.12 [28,4]	.07 [1,78]	.08 [2,03]	.024 [0,61]	3.26 [82,8]	18 THRU 25
202C663	3.04 [77,2]	2.25 [57,2]	1.60 [40,6]	2.15 [54,6]	2.25 [57,2]	.90 [22,9]	2.45 [62,2]	9.30 [236,2]	1.38 [35,1]	.08 [2,03]	.08 [2,03]	.026 [0,66]	5.45 [138,4]	26 THRU 28

TE Connectivity. All Rights Reserved.

2023



DIMENSIONS: INCHES		DWN M MAZARIEGOS	14DEC2023	MATERIAL -	FINISH -
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK C LIMA	-	TE Connectivity	
		APVD L RODRIGUEZ	-		
		PRODUCT SPEC -	-		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC -	-	NAME UNI-BOOT	
		WEIGHT 0	-	SIZE A4	CAGE CODE 06090
		DRAWING NO C-202C611THRU663			RESTRICTED TO -
CUSTOMER DRAWING				SCALE DNS	SHEET 1 OF 2
				REV AA1	

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

Material Dash Number	Material Description	SPEC Number	Coating Slash Number
-50	FLEXIBLE VPB	RT-1313	/86, /164
-51	FLEXIBLE EPB	RT-1321	/86, /164
-71	FLEXIBLE POLYOLEFIN	RT-1316	/42, /86, /180
-770	NBCCS	RT-770 TYPE II	
-780 	NBCCS	RT-780 TYPE II	

Ordering Information

202C6**-*-/**-0	
↑	COLOR DESIGNATOR
↑	Adhesive Slash Number (if required see compatibility chart)
↑	Material Dash Number (see compatibility chart)
↑	Base Part Number

NOTES:

- ALL DIMENSIONS ARE IN $\frac{\text{INCHES}}{[\text{MILLIMETERS}]}$
- DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
 - AS SUPPLIED
 - AFTER UNRESTRICTED RECOVERY
-  COATING (ADHESIVE): IS OPTIONAL AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS. WHEN COATING IS ADDED, ENTRY DIAMETER WILL BE REDUCED BY .06 MAX.
- "S" AND "T" DIMENSIONS APPLY TO A MINIMUM OF 240° OF THE CIRCUMFERENCE.
-  MATERIAL -780 IS AVAILABLE FOR PART NO. 202C611 ONLY

TE Connectivity. All Rights Reserved.

2023



DIMENSIONS:		DWN	14DEC2023	MATERIAL		FINISH							
INCHES		CHK	—	TE Connectivity									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	—										
		PRODUCT SPEC						NAME					
0 PLC	± —	APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
1 PLC	± —												
2 PLC	± —	WEIGHT		A4		00779		C-202C611THRU663		—			
3 PLC	± —												
4 PLC	± —	CUSTOMER DRAWING		SCALE		DNS		SHEET		2 of 2		REV	
ANGLES	± —												
													



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202C653-71-0](#) [202C621-51-0-CS5325](#) [202C653-71-0-CS8395](#) [202C642-71-0-CS8395](#) [202C653-50-0-CS5325](#)