







KIT CONTENTS

VALUE	PRODUCT NUMBER	TCPN	DESCRIPTION	QUANTITY
10R	CRGH2512J10R	2-1879501-5	CRGH2512 5% 10R 2W	100
12R	CRGH2512J12R	2-1879501-7	CRGH2512 5% 12R 2W	100
15R	CRGH2512J15R	2-1879501-9	CRGH2512 5% 15R 2W	100
18R	CRGH2512J18R	3-1879501-1	CRGH2512 5% 18R 2W	100
22R	CRGH2512J22R	3-1879501-3	CRGH2512 5% 22R 2W	100
27R	CRGH2512J27R	3-1879501-5	CRGH2512 5% 27R 2W	100
33R	CRGH2512J33R	3-1879501-7	CRGH2512 5% 33R 2W	100
39R	CRGH2512J39R	3-1879501-9	CRGH2512 5% 39R 2W	100
47R	CRGH2512J47R	4-1879501-1	CRGH2512 5% 47R 2W	100
56R	CRGH2512J56R	4-1879501-3	CRGH2512 5% 56R 2W	100
68R	CRGH2512J68R	4-1879501-5	CRGH2512 5% 68R 2W	100
82R	CRGH2512J82R	4-1879501-7	CRGH2512 5% 82R 2W	100
100R	CRGH2512J100R	4-1879501-9	CRGH2512 5% 100R 2W	100
120R	CRGH2512J120R	5-1879501-1	CRGH2512 5% 120R 2W	100
150R	CRGH2512J150R	5-1879501-3	CRGH2512 5% 150R 2W	100
180R	CRGH2512J180R	5-1879501-5	CRGH2512 5% 180R 2W	100
200R	CRGH2512J200R	5-1879501-6	CRGH2512 5% 200R 2W	100
220R	CRGH2512J220R	5-1879501-7	CRGH2512 5% 220R 2W	100
270R	CRGH2512J270R	5-1879501-9	CRGH2512 5% 270R 2W	100
300R	CRGH2512J300R	6-1879501-0	CRGH2512 5% 300R 2W	100
330R	CRGH2512J330R	6-1879501-1	CRGH2512 5% 330R 2W	100
390R	CRGH2512J390R	6-1879501-3	CRGH2512 5% 390R 2W	100
470R	CRGH2512J470R	6-1879501-5	CRGH2512 5% 470R 2W	100
560R	CRGH2512J560R	6-1879501-7	CRGH2512 5% 560R 2W	100
680R	CRGH2512J680R	6-1879501-9	CRGH2512 5% 680R 2W	100
820R	CRGH2512J820R	7-1879501-1	CRGH2512 5% 820R 2W	100
1K0	CRGH2512J1K0	7-1879501-3	CRGH2512 5% 1K0 2W	100
1K2	CRGH2512J1K2	7-1879501-5	CRGH2512 5% 1K2 2W	100

P	LTR	DESCRIPTION	DATE	DWN	APVD
	BA	INITIAL RELEASE	26SEP2019	SB	AP



PCB LAYOUT PLAN


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26SEP2019 SHRICHARANA B		 TE Connectivity	
		CHK 26SEP2019 ALLAN P			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CRGH 2512 5% 10R-1M0 LAB-KIT	
		0 PLC ±		PRODUCT SPEC	
		1 PLC ±		-	
		2 PLC ±		APPLICATION SPEC	
		3 PLC ±		-	
		4 PLC ±		-	
		ANGLES ±		WEIGHT -	
MATERIAL -		FINISH -		SIZE A3	
				CAGE CODE 00779	
				DRAWING NO C-2176439-5	
				RESTRICTED TO	
				SCALE 40:1	
				SHEET 1 OF 2	
				REV BA	

KIT CONTENTS

VALUE	PRODUCT NUMBER	TCPN	DESCRIPTION	QUANTITY
1K5	CRGH2512J1K5	7-1879501-7	CRGH2512 5% 1K5 2W	100
1K8	CRGH2512J1K8	7-1879501-9	CRGH2512 5% 1K8 2W	100
2K2	CRGH2512J2K2	8-1879501-1	CRGH2512 5% 2K2 2W	100
2K7	CRGH2512J2K7	8-1879501-3	CRGH2512 5% 2K7 2W	100
3K3	CRGH2512J3K3	8-1879501-5	CRGH2512 5% 3K3 2W	100
3K9	CRGH2512J3K9	8-1879501-7	CRGH2512 5% 3K9 2W	100
4K7	CRGH2512J4K7	8-1879501-9	CRGH2512 5% 4K7 2W	100
5K6	CRGH2512J5K6	9-1879501-1	CRGH2512 5% 5K6 2W	100
6K8	CRGH2512J6K8	9-1879501-3	CRGH2512 5% 6K8 2W	100
8K2	CRGH2512J8K2	9-1879501-5	CRGH2512 5% 8K2 2W	100
10K	CRGH2512J10K	9-1879501-7	CRGH2512 5% 10K 2W	100
12K	CRGH2512J12K	9-1879501-9	CRGH2512 5% 12K 2W	100
15K	CRGH2512J15K	1879502-2	CRGH2512 5% 15K 2W	100
18K	CRGH2512J18K	1879502-4	CRGH2512 5% 18K 2W	100
22K	CRGH2512J22K	1879502-6	CRGH2512 5% 22K 2W	100
27K	CRGH2512J27K	1879502-8	CRGH2512 5% 27K 2W	100
33K	CRGH2512J33K	1-1879502-0	CRGH2512 5% 33K 2W	100
39K	CRGH2512J39K	1-1879502-2	CRGH2512 5% 39K 2W	100
47K	CRGH2512J47K	1-1879502-4	CRGH2512 5% 47K 2W	100
56K	CRGH2512J56K	1-1879502-6	CRGH2512 5% 56K 2W	100
68K	CRGH2512J68K	1-1879502-8	CRGH2512 5% 68K 2W	100
82K	CRGH2512J82K	2-1879502-0	CRGH2512 5% 82K 2W	100
100K	CRGH2512J100K	2-1879502-2	CRGH2512 5% 100K 2W	100
120K	CRGH2512J120K	2-1879502-4	CRGH2512 5% 120K 2W	100
150K	CRGH2512J150K	2-1879502-6	CRGH2512 5% 150K 2W	100
180K	CRGH2512J180K	2-1879502-8	CRGH2512 5% 180K 2W	100
220K	CRGH2512J220K	3-1879502-0	CRGH2512 5% 220K 2W	100
270K	CRGH2512J270K	3-1879502-2	CRGH2512 5% 270K 2W	100

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

VALUE	PRODUCT NUMBER	TCPN	DESCRIPTION	QUANTITY
330K	CRGH2512J330K	3-1879502-4	CRGH2512 5% 330K 2W	100
390K	CRGH2512J390K	3-1879502-6	CRGH2512 5% 390K 2W	100
470K	CRGH2512J470K	3-1879502-8	CRGH2512 5% 470K 2W	100
560K	CRGH2512J560K	4-1879502-0	CRGH2512 5% 560K 2W	100
680K	CRGH2512J680K	4-1879502-2	CRGH2512 5% 680K 2W	100
820K	CRGH2512J820K	4-1879502-4	CRGH2512 5% 820K 2W	100
1M0	CRGH2512J1M0	4-1879502-6	CRGH2512 5% 1M0 2W	100
1M2	CRGH2512J1M2	4-1879502-8	CRGH2512 5% 1M2 2W	100
1M5	CRGH2512J1M5	5-1879502-0	CRGH2512 5% 1M5 2W	100
1M8	CRGH2512J1M8	5-1879502-2	CRGH2512 5% 1M8 2W	100
2M2	CRGH2512J2M2	5-1879502-4	CRGH2512 5% 2M2 2W	100
2M7	CRGH2512J2M7	5-1879502-6	CRGH2512 5% 2M7 2W	100
3M3	CRGH2512J3M3	5-1879502-8	CRGH2512 5% 3M3 2W	100
3M9	CRGH2512J3M9	6-1879502-0	CRGH2512 5% 3M9 2W	100
4M7	CRGH2512J4M7	6-1879502-2	CRGH2512 5% 4M7 2W	100
5M6	CRGH2512J5M6	6-1879502-4	CRGH2512 5% 5M6 2W	100
6M8	CRGH2512J6M8	6-1879502-6	CRGH2512 5% 6M8 2W	100
8M2	CRGH2512J8M2	6-1879502-8	CRGH2512 5% 8M2 2W	100
10M	CRGH2512J10M	7-1879502-0	CRGH2512 5% 10M 2W	100

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26SEP2019 SHRIC HARANA B		 TE Connectivity	
		CHK 26SEP2019 ALLAN P			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CRGH 2512 5% 10R-1M0 LAB-KIT	
		0 PLC ±-		PRODUCT SPEC	
		1 PLC ±-		-	
		2 PLC ±-		APPLICATION SPEC	
		3 PLC ±-		-	
		4 PLC ±-		SIZE	
		ANGLES ±		CAGE CODE	
MATERIAL		FINISH		DRAWING NO	
-		-		RESTRICTED TO	
CUSTOMER DRAWING				SCALE 40:1	
				SHEET 2 OF 2	
				REV BA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[CRGH2512J-LAB-KIT](#)