






△ MATERIAL: PBT, 15% GLASS-FILLED
COLOR: BLACK


△ HOUSING SHIPPED WITH SECONDARY LOCK IN PRE-LOCK POSITION, AS SHOWN. SECONDARY LOCK MAY CLOSE INADVERTANTLY DURING SHIPPING, IF THIS OCCURS, RELOCATE SECONDARY LOCK TO OPEN POSITION PRIOR TO INSERTION OF TERMINALS.

3. PRODUCT INCORPORATES CLIP SLOT AND RETAINER CLIPLOCK AS DEFINED BY EWCAP-005-II, REV B.
4. CAP HOUSING WILL ACCEPT GENERATION Y BLADE CONTACTS.
5. FOR ASSEMBLY AND REPAIR INSTRUCTIONS SEE TE SPEC 408-32069.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RUSTY WORTHINGTON	06SEP2013		
		CHK RANDY SIMMONS	06SEP2013		
DIMENSIONS:		APVD RANDY SIMMONS	06SEP2013	NAME	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	HOUSING, 4 POSITION, CONTACTS GENERATION Y			
	0 PLC ±. 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±. 4 PLC ±. ANGLES ±°	PRODUCT SPEC - APPLICATION SPEC -			
MATERIAL	FINISH	WEIGHT	-	SIZE CAGE CODE DRAWING NO	RESTRICTED TO
	-	CUSTOMER DRAWING		A100779G=2203535	-
			SCALE	SHEET	REV
			4:1	1 OF 2	B


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




2203535-1
KEY A




2203535-2
KEY B




2203535-3
KEY C




2203535-4
KEY D




2203535-5
KEY E




2203535-6
KEY F



2203535-7
KEY G



2203535-8
KEY H

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: 06SEP2013 RUSTY WORTHINGTON	 TE Connectivity	
		CHK: 06SEP2013 RANDY SIMMONS		
DIMENSIONS:		APVD: 06SEP2013 RANDY SIMMONS	NAME	
mm		PRODUCT SPEC	HOUSING, 4 POSITION, CONTACTS GENERATION Y	
		APPLICATION SPEC		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT	SIZE	CAGE CODE
0 PLC ±.1		-	A100779	C=2203535
1 PLC ±0.3		CUSTOMER DRAWING	SCALE	4:1
2 PLC ±0.20			SHEET	2 OF 2
3 PLC ±.1			REV	B
4 PLC ±.1				
ANGLES				
FINISH				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2203535-2](#)