





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP(ECN-23-231219)	15SEP2023	ED	WH



RECOMMENDED
CABLE STRIPPING DIM'S



NOTES:

- 1
- PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- 2
- ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- 3
- ELECTRICAL CHARACTERISTICS :
FREQUENCY RANGE : DC-4GHz
NOMINAL IMPEDANCE : 50 OHMS
INSULATION RESISTANCE : 5000 MOHMS
WORKING VOLTAGE : 335 VRMS MAX
DIELECTRIC WITHSTANDING VOLTAGE : 750 VOLTS MAX
VSWR : 1.2 MAX (DC-4GHz)
CONTACT RESISTANCE :
CENTER CONTACT : 3 mOHMS MAX
OUTER CONTACT : 2 mOHMS MAX;
- 4
- MECHANICAL CHARACTERISTICS :
DURABILITY : 500 CYCLES
CABLE RETENTION FORCE(Cable assembly): 10 lbs min.
- 5
- TEMPERATURE RANGE: -65°-+165°;
- 6
- CRIMPED FERRULE,HEX CRIMP SIZE .128";
CRIMPED CONTACT PIN,SQ. CRIMP SIZE 0.7mm;
- 7
- RoHS: COMPLIANT.

	1	BRIGHT TIN 200u"/NICKEL/COPPER	BRASS	FERRULE	10
	1	GOLD 50u"/NICKEL/COPPER	BRASS	CONTACT PIN	9
	1	NICKEL 100u"/COPPER	BRASS	WASHER	8
	1	NICKEL 100u"/COPPER	SK5	SPRING	7
	1	RED	SILICONE	GASKET	6
	1	NICKEL 100u"/COPPER	BRASS	BARREL	5
	1	GOLD 50u"/NICKEL/COPPER	PHOSPHOR BRONZE	CONTACT PIN	4
	1	NATURAL	PTFE	INSULATOR	3
	1	NICKEL 100u"/COPPER	BERYLLIUM COPPER	OUTER CONTACT	2
	1	NICKEL 100u"/COPPER	BRASS	SHELL	1
	2466287-1	PLATING	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY		PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ED 11SEP2023	TE Connectivity		
		CHK ED 11SEP2023			
DIMENSIONS: mm		APVD WH 11SEP2023	NAME BNC PLUG,STRAIGHT,CRIMP, MATCH WITH RG174,188,316,4GHz		
		PRODUCT SPEC	-		
		APPLICATION SPEC	-		
MATERIAL SEE TABLE		WEIGHT -	SIZE A2	CAGE CODE 00779	RESTRICTED TO -
		FINISH -	DRAWING NO C-2466287		
CUSTOMER DRAWING			SCALE 8:1	SHEET 1 OF 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2466287-1](#)