



23 Series T-3 1/4 & T-5 Lampholders Minature Wedge Base



Overview

The 23 Series lampholders are designed for automotive and appliance applications. Most lamp holders can be supplied as either non-grounded or grounded units with printed circuit board or solder lug terminals or 6" wire leads. Many bracket and mounting options are available including plug buttons for 5/8" mounting holes and a 518" twist and lock socket. Lampholders are designed for use in low voltage applications with T-5 & T-3 1/4 wedge base lamps.

Key features

- Miniature wedge base non-grounded or grounded lampholders
- Black nylon housing
- 6" wire leads, printed circuit board or solder lug terminals
- Maximum ratings: 20 Watts, 28 Volts
- UL recognized • UL File E20356

Specifications

Housing:

Black nylon, other colors also available. Rated maximum temperature 85°C.

Contacts: brass

Terminals:

Solder lug: electro tined brass, 0.110" length x 0.010" thick, with one wire hole 3/32"x1/16" in diameter. Non-grounded units are supplied with two terminals. Grounded units are supplied with one terminal.

Printed circuit board terminals: brass

Wire Leads: #22 AWG, black, stranded tinned copper, PVC insulated, UL/CSA rated 105 °C, stripped 1/2". Non-grounded units are supplied with two 6" wire leads. Grounded units are supplied with one 6" wire lead. Custom wire lengths, stripping, termination and wire types are also available.

Mounting:


Brackets: 0.025" to 0.032" zinc plated steel.

Plug buttons: for 5/8" mounting hole, nylon or zinc plated steel.


Twist & Lock: for 5/8" mounting hole.

Maximum rating: 20 Watts, 28 Volts

Dimensions




Dimensions are in inches



Dimensions

* UL Recognition not available on these models.

Dimensions are in inches



Compliances and Approvals



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

23-207-1