






P	LTR	DESCRIPTION	DATE	DWN	APVD
	AF2	REVISED PER ECR-12-013810	24SEP2012	JR	TM
	AF3	REVISED PER ECN-23-233438	02OCT2023	WLS	VS



NOTES:

- 1 PLATE OVERALL WITH 0.00127 [.000050] MIN NICKEL, THEN TIP PLATE WITH 0.00076 [.000030] MIN GOLD IN THE MATING AREA.
- 2 PLATE OVERALL WITH 0.00127 [.000050] MIN NICKEL, THEN PLATE IN THE MATING AREA AND STRIPE THE INSIDE OF THE WIRE BARREL WITH 0.00076 [.000030] MIN GOLD.
3. WIRE RANGE: 0.5 - 2mm² [20 - 14 AWG].
4. INSULATION RANGE: 3.30[.130] MAX DIA.
5. APPLICATION TYPE: MINI.
6. DIMENSIONS IN BRACKETS ARE IN INCHES.

1	0.33[.012] BRASS	61118-7
2	0.33[.012] PH BZ	61118-6
2	0.33[.012] BRASS	61118-5
PRE-TIN	0.33[.012] PH BZ	61118-4
-	0.33[.012] BRASS	61118-2
PRE-TIN	0.33[.012] BRASS	61118-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK	20NOV1992	TE Connectivity		
		CHK R. SWING	20NOV1992			
		APVD D. SELF	09DEC1992	NAME PIN COMMERCIAL MATE-N-LOK -		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE A3		
		0 PLC ± 1 PLC ± 2 PLC ±0.25[.010] 3 PLC ± 4 PLC ± ANGLES ±1°		CAGE CODE 00779		
MATERIAL -		FINISH -		DRAWING NO C-61118		
				RESTRICTED TO -		
				SCALE 5:1		
				SHEET 1 OF 1		
				REV AF3		
				CUSTOMER DRAWING		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[61118-1 \(Mouser Reel\)](#) [61118-1 \(Cut Strip\)](#)