





REVISIONS			
REV	DESCRIPTION	DATE	APPV
A	INITIAL RELEASE FROM X1	6-SEP-11	BPM
B	ADDED PART NUMBER TABLE AND SECOND SHEET; UPDATED NOTE 3	23-JUL-18	CLL

PART NUMBER		PACKAGING	
BAT-HLD-012-THM		BULK	
BAT-HLD-012-THM-TR		TAPE & REEL	
WARNING: THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT IS THE SOLE PROPERTY OF LINX TECHNOLOGIES, AND SHALL BE TREATED AS SUCH. NO DISCLOSURE OR REPRODUCTION OF THIS DOCUMENT IS PERMITTED, IN WHOLE OR IN PART, WITHOUT THE EXPRESS WRITTEN PERMISSION OF LINX TECHNOLOGIES OR ITS DESIGNATED AGENTS.		 159 ORT LANE MERLIN, OR 97532	
MATERIAL: PHOSPHOR BRONZE #C-5191		TITLE: BATTERY HOLDER CR1216, CR1225 THROUGH HOLE MOUNT	
WEIGHT:		SIZE B	REV A
FINISH: NICKEL PLATE		DWG. NO. C-BAT-HLD-012-THM-pp	
INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5. .X $\pm$ 2.0 .XX $\pm$ 1.0 .XXX $\pm$.500 ANGLES: $\pm$ 1° SURFACE: 		SCALE: 3:1	SHEET 1 OF 2
DRAWN: S.HOGAN ENGR:		DT: 8-JUN-11 DT: 23-JUL-18	DO NOT SCALE DRAWING



- NOTES: (UNLESS OTHERWISE SPECIFIED)
- 1. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].
 - 2. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$.
 - 3. MATERIAL: BLACK POLYSTYRENE.
 - 4. PACKING LENGTH PER 22" REEL: 29.4 m.
 - 5. COMPONENT LOAD PER 13" REEL: 550.
 - 6. ANGLE TOLERANCE: $\pm 1^\circ$
 - 7. CARRIER CAMBER IS WITHIN 1 mm IN 250 mm.

W	24.00±0.30	P	16.00±0.10	A0	8.80±0.10	B0	14.20±0.10
S		P0	4.00±0.10	A1	7.55 ^{+0.15} _{-0.05}	B1	13.50±0.10
E	1.75±0.10	P2	2.00±0.10	A2		B2	
F	11.50±0.10	D0	∅1.50 ^{+0.10} _{-0.00}	K0	7.50±0.10	K2	0.65±0.10
T	0.40±0.05	D1		K1	3.45±0.10	COLOR: BK/ANT	

SIZE	DWG. NO.	REV
B	BAT-HLD-012-THM-TR	B
SCALE: 8:1	DO NOT SCALE DRAWING	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[BAT-HLD-012-THM](#)