

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE PER E-21-003453	16DEC2021	AP	IG
	A1	REVISED PER PCN-22-154423	30SEP2022	AM	IG
	B	REVISED PER PCN-23-192205	05FEB2024	RK	CB

FIGURE 1




FIGURE 2
SHORT CAP






FIGURE 3
LONG CAP



ALT. VIEW FOR
PARTS FROM US



CONTACT SIZE	WIRE RANGE	INSULATION OD SEALING RANGE	SEAL IDENTIFICATION
16	14-20 AWG [2.5-0.5mm ²]	.088-.145 [2.23-3.68] .053-.120 [1.35-3.05]	STANDARD SEAL EXTRA THIN SEAL E-SEAL

TE INTERNAL PART NUMBER	DEUTSCH PART NUMBER	PN REV	HOUSING COLOR	STANDARD SEAL	EXTRA THIN SEAL E-SEAL	BLOCKED SEAL	SHORT CAP	LONG CAP	FIGURE
DT04-08PX	DT04-08PX	A	ALL	X					1
DT04-08PX-C015	DT04-08PX-C015	F	ALL		X				1
DT04-08PX-C017	DT04-08PX-C017	B	ALL			X	X		2
DT04-08PX-CE01	DT04-08PX-CE01	D	ALL		X		X		2
DT04-08PA-CE02	DT04-08PA-CE02	B	BLACK		X				1
DT04-08PA-CE03	DT04-08PA-CE03	B	BLACK		X		X		2
DT04-08PA-CE04	DT04-08PA-CE04	C	GRAY		X			X	3
DT04-08PA-CE09	DT04-08PA-CE09	AC	BLACK		X			X	3
DT04-08PA-CE26	DT04-08PA-CE26	A	BLACK			X	X		2
DT04-08PX-E003	DT04-08PX-E003	B	ALL	X			X		2
DT04-08PA-E004	DT04-08PA-E004	A	BLACK	X					1
DT04-08PA-E005	DT04-08PA-E005	A	BLACK	X			X		2
DT04-08PX-E008	DT04-08PX-E008	B	ALL	X				X	3
DT04-08PA-EE01	DT04-08PA-EE01	A	BLACK	X				X	3
DT04-08PX-EP04	DT04-08PX-EP04	D	ALL	X			X		2
DT04-08PX-P004	DT04-08PX-P004	C	ALL	X					1

6. MARKING FOR PARTS PRODUCED IN CHINA:

- XXXX IDENTIFIES THE MODIFICATION NUMBER, IF APPLICABLE. EXAMPLE: "E003" FOR DT04-08PA-E003, OR BLANK FOR DT04-08PA
- DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGIT. (17 = 2017)
MONTH: THIRD DIGIT, EXCLUDING 1. A = JAN, B = FEB, C = MARCH ... (K = OCTOBER)
DAY: FOURTH AND FIFTH DIGITS (14 = 14th DAY)
HOUR: SIXTH AND SEVENTH DIGITS (11 = 11AM)
- DIAL DATE CODE LOCATED ON HOUSING AND/OR CAP.
-CN LOCATED ON HOUSING AND/OR CAP.

5. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE CUSTOMER DRAWING 0425-015-0000.

7. MARKING FOR PARTS PRODUCED IN US:
-DATE CODE:
YEAR TO BE LAST NUMERICAL DIGIT, EX: 1 = 2021
MONTH UYVES SEQUENTIAL ALPHA CHARACTERS, EX: A = JANUARY
-DEUTSCH

- 4. "E" IDENTIFIES E-SEAL, LOCATED APPROX. AS SHOWN.
- 3. MATERIAL: HOUSING: PA66 GF15, SEE TABLE FOR COLOR
SHORT, LONG CAP: PA66 GF15, BLACK
GROMMET: E-SEAL VMO (BURNT ORANGE)
N-SEAL VMO (RED-ORANGE)
BLOCKED VMO (RED-ORANGE)

- 2. THIS RECEPTACLE MATES WITH DT06-08SX-XXXX PLUG (X = A,B,C,D KEY, XXXX = ALL MODIFICATIONS)
- 1. SECONDARY WEDGE LOCK SOLD SEPARATELY: W8P-XXXX. (XXXX = ALL MODIFICATIONS)

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
IN [mm]

MATERIAL
3

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±0.025 (0.64)
4 PLC ±
ANGLES ±0°30'0"
FINISH

DWN
A. POLO
CHK
R. MESSENGER
APVD
J. GRANTCHAROVA
PRODUCT SPEC
108-151009
APPLICATION SPEC
114-151009
WEIGHT

16DEC2021
16DEC2021
16DEC2021
108-151009
114-151009

CUSTOMER DRAWING

SCALE 5:2

SHEET 1 OF 2

REV B

TE Connectivity

8 WAY RECEPTACLE, STANDARD SEAL
EXTRA THIN SEAL, SHORT AND LONG
CAP, DT SERIES

SIZE 4AFU8
CAGE CODE
DRAWING NO
DT04-08PX-XXXX

RESTRICTED TO


4805 (3/13)

DT04-08PA-XXXX
KEY -A-
HOUSING COLOR: GRAY
SEE PN TABLE FOR BLACK PNs


DT04-08PB-XXXX
KEY -B-
HOUSING COLOR: BLACK

DT04-08PC-XXXX
KEY -C-
HOUSING COLOR: GREEN


DT04-08PD-XXXX
KEY -D-
HOUSING COLOR: BROWN




KEY -A-



KEY -B-



KEY -C-



KEY -D-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[DT04-08PA](#)