



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-20-017666	29DEC2020	GK	MN

LABEL AND LINER DESIGN



PRESENTATION



DESCRIPTION	TEPN	MATERIAL DESCRIPTION	TTDS	WEIGHT (g)	ROLL DIAMETER (mm) ± 10	ROLL DIAMETER (Inch) ± 0.393
EET-1555P-4	5-1768018-7	YELLOW POLYESTER	TTDS-174	0.101	153.53	6.04
EET-1555P-8A	5-1768018-8	SILVER POLYESTER	TTDS-175	0.080	153.53	6.04
EET-1555P-9	5-1768018-9	WHITE POLYESTER	TTDS-177	0.077	148.17	5.83
EET-1555PY-9	6-1768018-0	WHITE POLYETHYLENE	TTDS-178	0.091	165.13	6.50

INSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 5000

ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:												
	<table border="0"> <tr><td>0 PLC</td><td>± .</td></tr> <tr><td>1 PLC</td><td>± .</td></tr> <tr><td>2 PLC</td><td>± .</td></tr> <tr><td>3 PLC</td><td>± .</td></tr> <tr><td>4 PLC</td><td>± .</td></tr> <tr><td>ANGLES</td><td>± .</td></tr> </table>	0 PLC	± .	1 PLC	± .	2 PLC	± .	3 PLC	± .	4 PLC	± .	ANGLES	± .
0 PLC	± .												
1 PLC	± .												
2 PLC	± .												
3 PLC	± .												
4 PLC	± .												
ANGLES	± .												
MATERIAL	FINISH												
SEE TABLE	—												

DWN	29DEC2020	 TE Connectivity						
GOPALAKRISHNA HV								
CHK	29DEC2020	NAME EET LABELS 15.00mm x 55.00mm — —						
MIKE NUTTALL								
APVD	29DEC2020							
MIKE NUTTALL								
PRODUCT SPEC								
SEE TABLE		SIZE CAGE CODE DRAWING NO RESTRICTED TO						
APPLICATION SPEC								
—								
WEIGHT	SEE TABLE	A3	C2290	C-EET-1555		—		
CUSTOMER DRAWING			SCALE	NTS	SHEET	1 OF 1	REV	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1768018-8](#)