











MOUNTING CONDITIONS




SCALE 2:1




DETAIL Y
SCALE 5:1

DETAIL Z
SCALE 5:1



Notice :

- 1) PERMITTED TONQUE 6 Nm MAX. WHEN MIN 4 TURNS
- 2) SOCKET HOUSING
TE INTERFACE 2 POS. MQS CODE A,
APPROPRIATE FOR SOCKET HOUSING 2 POS. MQS,
TE PART NO. 1-967644-1
PRESCRIBED WIRE CROSS SECTION = 0,35mm² MIN
- 3) HEXAGON SOCKET BOTTOM HEAD SCREW EN ISO 7380 M6 WITH
WASHER ISO 7090/ 7089



PART ALIAS	TCPN	REV
V23720-A0112-B001	2-2317670-1	C

THE REPRODUCTION, TRANSMISSION OR USE OF THIS DOCUMENT OR IT'S CONTENTS IS NOT PERMITTED WITHOUT EXPRESSED WRITTEN AUTHORITY. OFFENDERS WILL BE LIABLE FOR ALL DAMAGES. ALL RIGHTS, INCLUDING RIGHTS CREATED BY REGISTERED PATENT(S) GRANTED FOR A UTILITY MODEL OR DESIGN, ARE RESERVED.		CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD	PAPER SIZE A1
APPLICABLE SPEC. :		FINISH	
		DIMENSIONS APPLY	PLATING
		SCALE	1:1
		WEIGHT	600g
		MATERIAL	---
		PARTY NAME	EVC 250-800 24V RELAY
		DWG NO.	V23720-A0112-B001-CD
		SHT.	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2317670-1](#)