




Dual N-Channel 30-V (D-S) MOSFET with Schottky Diode

PRODUCT SUMMARY

	V _{DS} (V)	r _{DS(on)} (Ω)	I _D (A)
Channel-1	30	0.021 @ V _{GS} = 10 V	7.0
		0.0325 @ V _{GS} = 4.5 V	5.6
Channel-2		0.020 @ V _{GS} = 10 V	7.4
		0.0265 @ V _{GS} = 4.5 V	6.4

SCHOTTKY PRODUCT SUMMARY

V _{DS} (V)	V _{SD} (V) Diode Forward Voltage	I _F (A)
30	0.50 V @ 1.0 A	2.0




Ordering Information: Si4814DY
Si4814DY-T1 (with Tape and Reel)

FEATURES

- LITTLE FOOT® Plus Integrated Schottky
- Alternative Pinning for Additional Layout Options
- 100% R_g Tested

APPLICATIONS

- DC/DC Converters
– Notebook



ABSOLUTE MAXIMUM RATINGS (T_A = 25 °C UNLESS OTHERWISE NOTED)

Parameter	Symbol	Channel-1		Channel-2		Unit
		10 secs	Steady State	10 secs	Steady State	
Drain-Source Voltage	V _{DS}	30				V
Gate-Source Voltage	V _{GS}	20				V
Continuous Drain Current (T _J = 150 °C) ^a	I _D	7.0	5.5	7.4	5.7	A
		5.6	4.3	6	4.5	
Pulsed Drain Current	I _{DM}	40		40		A
Continuous Source Current (Diode Conduction) ^a	I _S	1.7	1.0	1.8	0.95	A
Maximum Power Dissipation ^a	P _D	1.9	1.1	2.0	1.16	W
		1.2	0.71	1.3	0.74	
Operating Junction and Storage Temperature Range	T _J , T _{stg}	-55 to 150				°C

THERMAL RESISTANCE RATINGS

Parameter		Symbol	Channel-1		Channel-2		Unit
			Typ	Max	Typ	Max	
Maximum Junction-to-Ambient ^a	t ≤ 10 sec	R _{thJA}	52	65	47	60	°C/W
	Steady-State		90	112	85	107	
Maximum Junction-to-Foot (Drain)	Steady-State	R _{thJF}	30	38	28	35	°C/W

Notes

a. Surface Mounted on 1" x 1" FR4 Board.

MOSFET SPECIFICATIONS (T _J = 25 °C UNLESS OTHERWISE NOTED)							
Parameter	Symbol	Test Condition		Min	Typ ^a	Max	Unit
Static							
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	Ch-1	0.8			V
			Ch-2	0.8			
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = 20 V	Ch-1			100	nA
			Ch-2			100	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 30 V, V _{GS} = 0 V	Ch-1			1	μA
			Ch-2			100	
		V _{DS} = 30 V, V _{GS} = 0 V, T _J = 85 °C	Ch-1			15	
			Ch-2			2000	
On-State Drain Current ^b	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 10 V	Ch-1	20			A
			Ch-2	20			
Drain-Source On-State Resistance ^b	r _{DS(on)}	V _{GS} = 10 V, I _D = 7.0 A	Ch-1		0.0175	0.021	Ω
		V _{GS} = 10 V, I _D = 7.4 A	Ch-2		0.0165	0.020	
		V _{GS} = 4.5 V, I _D = 5.6 A	Ch-1		0.027	0.0325	
		V _{GS} = 4.5 V, I _D = 6.4 A	Ch-2		0.022	0.0265	
Forward Transconductance ^b	g _{fs}	V _{DS} = 15 V, I _D = 7.0 A	Ch-1		17		S
		V _{DS} = 15 V, I _D = 7.4 A	Ch-2		20		
Diode Forward Voltage ^b	V _{SD}	I _S = 1.7 A, V _{GS} = 0 V	Ch-1		0.7	1.1	V
		I _S = 1 A, V _{GS} = 0 V	Ch-2		0.47	0.5	
Dynamic ^a							
Total Gate Charge	Q _g	Channel-1 V _{DS} = 15 V, V _{GS} = 5 V, I _D = 7.0 A Channel-2 V _{DS} = 15 V, V _{GS} = 5 V, I _D = -7.4 A	Ch-1		6.5	10	nC
Gate-Source Charge	Q _{gs}		Ch-2		9.7	15	
			Ch-1		1.5		
Gate-Drain Charge	Q _{gd}		Ch-2		2.6		
			Ch-1		2.7		
Gate Resistance	R _g		Ch-2		3.8		
		Ch-1	0.5	1.6	2.6	Ω	
Turn-On Delay Time	t _{d(on)}	Ch-2	0.5	1.8	3.1		
		Rise Time	t _r	Ch-1		12	20
Ch-2				13	20		
Ch-1				13	20		
Ch-2				13	20		
Turn-Off Delay Time	t _{d(off)}	Ch-1		22	35		
		Ch-2		29	45		
Fall Time	t _f	Ch-1		8	15		
		Ch-2		12	20		
Source-Drain Reverse Recovery Time	t _{rr}	I _F = 1.3 A, di/dt = 100 A/μs	Ch-1		50	80	
		I _F = 2.2 A, di/dt = 100 μA/μs	Ch-2		46	80	

Notes

- a. Guaranteed by design, not subject to production testing.
 b. Pulse test; pulse width $\leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$.


SCHOTTKY SPECIFICATIONS ($T_J = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)							
Parameter	Symbol	Test Condition		Min	Typ	Max	Unit
Forward Voltage Drop	V_F	$I_F = 1.0\ \text{A}$			0.47	0.50	V
		$I_F = 1.0\ \text{A}, T_J = 125^\circ\text{C}$			0.36	0.42	
Maximum Reverse Leakage Current	I_{rm}	$V_r = 30\ \text{V}$			0.004	0.100	mA
		$V_r = 30\ \text{V}, T_J = 100^\circ\text{C}$			0.7	10	
		$V_r = -30\ \text{V}, T_J = 125^\circ\text{C}$			3.0	20	
Junction Capacitance	C_T	$V_r = 10\ \text{V}$			50		pF




TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

CHANNEL-1


Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current




Capacitance



Gate Charge








On-Resistance vs. Junction Temperature



TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)



CHANNEL-1











TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

CHANNEL-1



TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)

CHANNEL-2







TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)

CHANNEL-2


Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage




Reverse Current vs. Junction Temperature



Single Pulse Power, Junction-to-Ambient





Safe Operating Area



TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)

CHANNEL-2





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SI4814DY-T1-E3](#) [SI4814DY](#)