



## Optocoupler, Phototransistor Output, (Dual, Quad Channel), 110 °C Rated


Dual Channel



Quad Channel



1179015-1



### FEATURES

- Operating temperature from - 55 °C to + 110 °C
- Identical channel to channel footprint
- Dual and quad packages feature:
  - Reduced board space
  - Lower pin and parts count
  - Better channel to channel CTR match
  - Improved common mode rejection
- Isolation test voltage, 5300 V<sub>RMS</sub>
- Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC

### AGENCY APPROVALS

- UL1577, file no. E52744 system code H, double protection
- CSA 93751
- BSI IEC 60950; IEC 60065
- DIN EN 60747-5-2 (VDE 0884)/DIN EN 60747-5-5 pending



**RoHS**  
COMPLIANT

### DESCRIPTION

The ILD1615, ILQ1615 are multi-channel 110 °C rated phototransistor optocouplers that use GaAs IRLED emitters and high gain NPN phototransistors. These devices are constructed using over/under leadframe optical coupling and double molded insulation technology resulting a withstand test voltage of 7500 V<sub>AC PEAK</sub> and a working voltage of 1700 V<sub>RMS</sub>.

The binned min./max. and linear CTR characteristics make these devices well suited for DC or AC voltage detection. Eliminating the phototransistor base connection provides added electrical noise immunity from the transients found in many industrial control environments.


Because of guaranteed maximum non-saturated and saturated switching characteristics, the ILD1615, ILQ1615 can be used in medium speed data I/O and control systems. The binned min./max. CTR specification allow easy worst case interface calculations for both level detection and switching applications. Interfacing with a CMOS logic is enhanced by the guaranteed CTR at I<sub>F</sub> = 1.0 mA.

### ORDERING INFORMATION



PART NUMBER  
x = D (Dual) or Q (Quad)

CTR  
BIN



| AGENCY CERTIFIED/PACKAGE | DUAL CHANNEL | QUAD CHANNEL |
|--------------------------|--------------|--------------|
|                          | CTR (%)      |              |
| UL, CSA, BSI             | 160 to 320   | 160 to 320   |
| DIP-8                    | ILD1615-4    | -            |
| DIP-16                   | -            | ILQ1615-4    |

| ABSOLUTE MAXIMUM RATINGS ( $T_{amb} = 25\text{ °C}$ , unless otherwise specified) |  |            |                |           |
|---|--|------------|----------------|-----------|
| PARAMETER   | TEST CONDITION                                   | SYMBOL     | VALUE          | UNIT      |
| <b>INPUT</b>  |  |            |                |           |
| Peak reverse voltage  |  | $V_R$      | 6.0            | V         |
| Forward current   |  | $I_F$      | 60             | mA        |
| Surge current   |  | $I_{FSM}$  | 1.5            | A         |
| Power dissipation   |  | $P_{diss}$ | 100            | mW        |
| Derate linearly from 25 °C  |  |            | 1.0            | mW/°C     |
| <b>OUTPUT</b>   |  |            |                |           |
| Collector emitter breakdown voltage   |  | $BV_{CEO}$ | 70             | V         |
| Emitter collector breakdown voltage   |  | $BV_{ECO}$ | 7.0            | V         |
| Collector current   |  | $I_C$      | 50             | mA        |
|   | $t < 1.0\text{ ms}$                              | $I_C$      | 100            | mA        |
| Power dissipation   |  | $P_{diss}$ | 150            | mW        |
| Derate linearly from 25 °C  |  |            | 1.5            | mW/°C     |
| <b>COUPLER</b>  |  |            |                |           |
| Storage temperature   |  | $T_{stg}$  | - 55 to + 150  | °C        |
| Operating temperature   |  | $T_{amb}$  | - 55 to + 110  | °C        |
| Soldering temperature <sup>(1)</sup>  | 2.0 mm distance from case bottom                 | $T_{sld}$  | 260            | °C        |
| Package power dissipation ILD1615   |  |            | 400            | mW        |
| Derate linearly from 25 °C  |  |            | 5.33           | mW/°C     |
| Package power dissipation ILQ1615   |  |            | 500            | mW        |
| Derate linearly from 25 °C  |  |            | 6.67           | mW/°C     |
| Isolation test voltage  | $t = 1.0\text{ s}$                               | $V_{ISO}$  | 5300           | $V_{RMS}$ |
| Creepage distance   |  |            | $\geq 7.0$     | mm        |
| Clearance distance  |  |            | $\geq 7.0$     | mm        |
| Isolation resistance  | $V_{IO} = 500\text{ V}, T_{amb} = 25\text{ °C}$  | $R_{IO}$   | $\geq 10^{12}$ | $\Omega$  |
|   | $V_{IO} = 500\text{ V}, T_{amb} = 100\text{ °C}$ | $R_{IO}$   | $\geq 10^{11}$ | $\Omega$  |

## Notes

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability.

<sup>(1)</sup> Refer to wave profile for soldering conditions for through hole devices.

| ELECTRICAL CHARACTERISTICS ( $T_{amb} = 25\text{ °C}$ , unless otherwise specified) |   |                                    |           |           |        |               |
|---|---|------------------------------------|-----------|-----------|--------|---------------|
| PARAMETER   | TEST CONDITION                              | SYMBOL                             | MIN.      | TYP.      | MAX.   | UNIT          |
| <b>INPUT</b>  |   |                                    |           |           |        |               |
| Forward voltage   | $I_F = 10\text{ mA}$                        | $V_F$                              | 1.0       | 1.15      | 1.3    | V             |
| Breakdown voltage   | $I_R = 10\text{ }\mu\text{A}$               | $V_{BR}$                           | 6.0       | 30        |        | V             |
| Reverse current   | $V_R = 6.0\text{ V}$                        | $I_R$                              |           | 0.01      | 10     | $\mu\text{A}$ |
| Capacitance   | $V_R = 0\text{ V}, f = 1.0\text{ MHz}$      | $C_O$                              |           | 25        |        | pF            |
| <b>OUTPUT</b>   |   |                                    |           |           |        |               |
| Collector emitter capacitance   | $V_{CE} = 5.0\text{ V}, f = 1.0\text{ MHz}$ | $C_{CE}$                           |           | 6.8       |        | pF            |
| Collector emitter leakage current   | $V_{CE} = 10\text{ V}$                      | $I_{CEO}$                          |           | 5.0       | 100    | nA            |
| Collector emitter breakdown voltage   | $I_{CE} = 0.5\text{ mA}$                    | $BV_{CEO}$                         | 70        |           |        | V             |
| Emitter collector breakdown voltage   | $I_E = 0.1\text{ mA}$                       | $BV_{ECO}$                         | 7.0       |           |        | V             |
| <b>PACKAGE TRANSFER CHARACTERISTICS</b>   |   |                                    |           |           |        |               |
| Channel/channel CTR match   | $I_F = 10\text{ mA}, V_{CE} = 5.0\text{ V}$ | CTR <sub>X</sub> /CTR <sub>Y</sub> | 1 to 1    |           | 2 to 1 |               |
| <b>COUPLER</b>  |   |                                    |           |           |        |               |
| Capacitance (input to output)   | $V_{IO} = 0\text{ V}, f = 1.0\text{ MHz}$   | $C_{IO}$                           |           | 0.8       |        | pF            |
| Insulation resistance   | $V_{IO} = 500\text{ V}, T_A = 25\text{ °C}$ | $R_S$                              | $10^{12}$ | $10^{14}$ |        | $\Omega$      |
| Channel to channel isolation  |   |                                    | 500       |           |        | $V_{AC}$      |

## Note

- Minimum and maximum values are tested requirements. Typical values are characteristics of the device and are the result of engineering evaluations. Typical values are for information only and are not part of the testing requirements.

**CURRENT TRANSFER RATIO** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

| PARAMETER   | TEST CONDITION                                  | PART      | SYMBOL        | MIN. | TYP. | MAX. | UNIT |
|---|---|-----------|---------------|------|------|------|------|
| Current transfer ratio<br>(collector emitter saturated) | $I_F = 1.0\text{ mA}$ , $V_{CE} = 0.4\text{ V}$ | ILD1615-4 | $CTR_{CEsat}$ |      | 100  |      | %    |
|   |   | ILQ1615-4 |               |      |      |      |      |
| Current transfer ratio<br>(collector emitter)           | $I_F = 10\text{ mA}$ , $V_{CE} = 5.0\text{ V}$  | ILD1615-4 | $CTR_{CE}$    | 160  | 200  | 320  | %    |
|   |   | ILQ1615-4 |               |      |      |      |      |
|   | $I_F = 1.0\text{ mA}$ , $V_{CE} = 5.0\text{ V}$ | ILD1615-4 | $CTR_{CE}$    | 56   | 90   |      | %    |
|   |   | ILQ1615-4 |               |      |      |      |      |

**SWITCHING CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

| PARAMETER            | TEST CONDITION  | PART | SYMBOL    | MIN. | TYP. | MAX. | UNIT          |
|----------------------|---|------|-----------|------|------|------|---------------|
| <b>NON-SATURATED</b> |   |      |           |      |      |      |               |
| Turn-on time         | $I_F = 10\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 75\text{ }\Omega$ ,<br>50 % of $V_{PP}$           |      | $t_{on}$  |      | 3.0  |      | $\mu\text{s}$ |
| Rise time            | $I_F = 10\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 75\text{ }\Omega$ ,<br>50 % of $V_{PP}$           |      | $t_r$     |      | 2.0  |      | $\mu\text{s}$ |
| Turn-off time        | $I_F = 10\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 75\text{ }\Omega$ ,<br>50 % of $V_{PP}$           |      | $t_{off}$ |      | 2.3  |      | $\mu\text{s}$ |
| Fall time            | $I_F = 10\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 75\text{ }\Omega$ ,<br>50 % of $V_{PP}$           |      | $t_f$     |      | 2.0  |      | $\mu\text{s}$ |
| Propagation H to L   | $I_F = 10\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 75\text{ }\Omega$ ,<br>50 % of $V_{PP}$           |      | $t_{PHL}$ |      | 1.1  |      | $\mu\text{s}$ |
| Propagation L to H   | $I_F = 10\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 75\text{ }\Omega$ ,<br>50 % of $V_{PP}$           |      | $t_{PLH}$ |      | 2.5  |      | $\mu\text{s}$ |
| <b>SATURATED</b>     |   |      |           |      |      |      |               |
| Turn-on time         | $I_F = 5.0\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 1.0\text{ k}\Omega$ ,<br>$V_{HT} = 1.5\text{ V}$ |      | $t_{on}$  |      | 6.0  |      | $\mu\text{s}$ |
| Rise time            | $I_F = 5.0\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 1.0\text{ k}\Omega$ ,<br>$V_{HT} = 1.5\text{ V}$ |      | $t_r$     |      | 4.6  |      | $\mu\text{s}$ |
| Turn-off time        | $I_F = 5.0\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 1.0\text{ k}\Omega$ ,<br>$V_{HT} = 1.5\text{ V}$ |      | $t_{off}$ |      | 25   |      | $\mu\text{s}$ |
| Fall time            | $I_F = 5.0\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 1.0\text{ k}\Omega$ ,<br>$V_{HT} = 1.5\text{ V}$ |      | $t_f$     |      | 15   |      | $\mu\text{s}$ |
| Propagation H to L   | $I_F = 5.0\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 1.0\text{ k}\Omega$ ,<br>$V_{HT} = 1.5\text{ V}$ |      | $t_{PHL}$ |      | 5.4  |      | $\mu\text{s}$ |
| Propagation L to H   | $I_F = 5.0\text{ mA}$ , $V_{CC} = 5.0\text{ V}$ , $R_L = 1.0\text{ k}\Omega$ ,<br>$V_{HT} = 1.5\text{ V}$ |      | $t_{PLH}$ |      | 7.4  |      | $\mu\text{s}$ |

**COMMON MODE TRANSIENT IMMUNITY** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

| PARAMETER                         | TEST CONDITION   | SYMBOL   | MIN. | TYP. | MAX. | UNIT             |
|-----------------------------------|--|----------|------|------|------|------------------|
| Common mode rejection output high | $V_{CM} = 50\text{ V}_{P-P}$ , $R_L = 1.0\text{ k}\Omega$ , $I_F = 0\text{ mA}$  | $CM_H$   |      | 5000 |      | V/ $\mu\text{s}$ |
| Common mode rejection output low  | $V_{CM} = 50\text{ V}_{P-P}$ , $R_L = 1.0\text{ k}\Omega$ , $I_F = 10\text{ mA}$ | $CM_L$   |      | 5000 |      | V/ $\mu\text{s}$ |
| Common mode coupling capacitance  |  | $C_{CM}$ |      | 0.01 |      | pF               |

## TYPICAL CHARACTERISTICS ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)




Fig. 1 - Permissible Power Dissipation vs. Temperature Non-Saturation Operation




Fig. 4 - Collector to Emitter Dark Current vs. Ambient Temperature




Fig. 2 - Forward Voltage vs. Forward Current




Fig. 5 - Normalized Current vs. Collector Emitter Saturation Voltage




Fig. 3 - Collector Current vs. Collector Emitter Voltage




Fig. 6 - Normalized Current Transfer Ratio vs. Ambient Temperature




Fig. 7 - Normalized CTR vs. Temperature




Fig. 10 - Forward Resistance vs. Forward Current




Fig. 8 - Normalized CTR vs. Forward Current




Fig. 11 - Forward Resistance vs. Forward Current




Fig. 9 - Normalized CTR vs. Forward Current





# ILD1615, ILQ1615

Vishay Semiconductors





Optocoupler, Phototransistor Output,  
(Dual, Quad Channel), 110 °C Rated



## PACKAGE DIMENSIONS in millimeters





i178006



i178007

## PACKAGE MARKING





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[ILD1615-4](#) [ILQ1615-4](#)