





REV. 0
DCO# 143125

COIL: @ 25°C
 RESISTANCE 98 OHMS $\pm 10\%$
 NOMINAL VOLTAGE 6.0 VDC
 MUST OPERATE 3.5 VDC
 MUST RELEASE 2.0 VDC MAX, 0.28 VDC MIN

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C
 NOTES: OPERATE TIME 2.0 MS MAX.
 RELEASE TIME 1.5 MS MAX.
 CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. BSH 07/26/01

2K. 7/26/01

CII Technologies
 advanced control electronic solutions

CUST. QPL
 CUST. NO. M39016/9-014L REV.

"JMA" RELAY

JMAW-6XL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMAW-6XL](#)