



intercontec
products

Kontaktbuchse 1 mm geschlitzt

Einsatzbereich: - 623 Isolierkörper
- 923 Isolierkörper, 8/9-polig

TE Teile Nr.: 60-0011-011-000
IC Ref. Nr.: 60.011.11

Elektrische Werte

Bemessungsstrom max. 10 A*
Durchgangswiderstand < 5 mOhm

Werkstoff

Kontakt Messing, vergoldet

Anschluss

Anschlussart Crimp
Anschlussbereich 0,06 - 1,0 mm^{2 1)}
0,14 - 1,0 mm^{2 2)}
- für Isolationscrimp max. ø2,1 mm
Abisolierlänge 6 mm
Crimpeinstellungen sind individuell zu wählen

Mechanische Werte

Steckzyklen 500

Werkzeuge (nicht im Lieferumfang enthalten)

digitale Crimpzange TE Teile Nr.: C0-0235-000-000 ¹⁾ oder C0-0236-000-000 ²⁾
IC Ref. Nr.: C0.235.00 ¹⁾ oder C0.236.00 ²⁾

analoge Crimpzange TE Teile Nr.: C0-0101-000-000 ¹⁾ oder C0-0201-000-000 ²⁾
IC Ref. Nr.: C0.101.00 ¹⁾ oder C0.201.00 ²⁾



Positioniereinsatz TE Teile Nr.: C0-0003-000-000
IC Ref. Nr.: C0.003.00

Crimpen - kraftunterstützt

Crimpmaschine TE Teile Nr.: WA-1672-000-000
IC Ref. Nr.: WA10672

digitaler Crimpeinsatz, klein TE Teile Nr.: C0-0372-000-000 ¹⁾
IC Ref. Nr.: C0.372.00 ¹⁾

digitaler Crimpeinsatz, mittel TE Teile Nr.: C0-0373-000-000 ²⁾
IC Ref. Nr.: C0.373.00 ²⁾



Hauptabmessungen
Kontaktbuchse

© 2018 TE Connectivity.

TE Connectivity, TE connectivity (logo), intercontec (logo) und speedtec sind Marken.

Auch wenn TE Connectivity (TE) bemüht ist, die Korrektheit der Informationen in diesem Beitrag sicherzustellen, übernimmt TE keinerlei Gewährleistung dafür, dass diese fehlerfrei, zutreffend, korrekt, verlässlich oder aktuell sind. TE behält sich das Recht vor, die in diesem Beitrag genannten Informationen jederzeit ohne Ankündigung zu ändern. TE weist ausdrücklich jegliche Gewährleistung hinsichtlich der in diesem Beitrag genannten Informationen zurück, einschließlich der implizierten Gewährleistung der Marktgängigkeit oder Eignung für bestimmte Zwecke. Die Maßangaben in diesem Beitrag dienen ausschließlich zu Referenzzwecken und Änderungen sind vorbehalten. Änderungen der Spezifikationen sind vorbehalten. Bitte fragen Sie TE nach den aktuellen Maßangaben und Designspezifikationen

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz



* Bei max. Anschlussquerschnitt



intercontec
products

Contact Socket 1 mm slotted

for: - 623 Insulation Insert
- 923 Insulation Insert, 8/9-pin

TE part number: 60-0011-011-000
IC reference number: 60.011.11

Electrical Data

rated current max. 10 A*
contact resistance < 5 mOhm

Material

contact brass, gold plated

Termination

kind of termination crimp
cross-section 0.06 - 1.0 mm² ¹⁾
0.14 - 1.0 mm² ²⁾
- for insulation crimp max. ø2.1 mm
stripping length 6 mm
crimp settings select individually

Mechanical Data

mating cycles 500

Tools (not part of product contents)

digital crimping tool TE part no.: C0-0235-000-000 ¹⁾ or C0-0236-000-000 ²⁾
IC ref. no.: C0.235.00 ¹⁾ or C0.236.00 ²⁾

analog crimping tool TE part no.: C0-0101-000-000 ¹⁾ or C0-0201-000-000 ²⁾
IC ref. no.: C0.101.00 ¹⁾ or C0.201.00 ²⁾



positioner TE part no.: C0-0003-000-000
IC ref. no.: C0.003.00

power crimping

crimping machine TE part no.: WA-1672-000-000
IC ref. no.: WA10672

digital crimp insert, small TE part no.: C0-0372-000-000 ¹⁾
IC ref. no.: C0.372.00 ¹⁾

digital crimp insert, medium TE part no.: C0-0373-000-000 ²⁾
IC ref. no.: C0.373.00 ²⁾



Main Dimensions
contact socket

© 2017 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz



* for max. wire cross-section

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[60.011.11](#)