



## ADP-2.4F-2.4F

### 2.4 mm Jack to 2.4 mm Jack Adapter

The ADP-2.4F-2.4F is a 2.4 mm jack to 2.4 mm jack adapter. Operating from 0 Hz to 50 GHz, the ADP-2.4F-2.4F combines superior performance, compact size, and a convenient threaded mating interface to provide a reliable, easy-to-use adapter. Linx adapters are ideal for precision applications. Additionally, all Linx adapters meet RoHS lead free standards and are tested to meet requirements for corrosion resistance, vibration, mechanical and thermal shock.

#### FEATURES

- 0 Hz to 50 GHz operation
- Passivated stainless steel body
  - Superior corrosion resistance
- 2.4 mm jack (female socket) connection
  - Gold plated beryllium copper center contact

#### APPLICATIONS

- Radar, Satellite Communications, Experimental
- Industrial, Commercial, Enterprise
- Test and measurement

#### TABLE 1. ELECTRICAL SPECIFICATIONS

Parameter	Value
Impedance	50 $\Omega$
Frequency Range	0 to 50 GHz
Contact Resistance	Center: $\leq 6.0$ m $\Omega$ Outer: $\leq 2.0$ m $\Omega$
Insertion Loss (dB max.)	1.0
VSWR (max.)	1.3

#### ORDERING INFORMATION

Part Number	Description
ADP-2.4F-2.4F	2.4 mm jack (female socket) to 2.4 mm jack (female socket) adapter

Available from Linx Technologies and select distributors and representatives.

## PRODUCT DIMENSIONS




TABLE 2. ADAPTER COMPONENTS

ADP-2.4F-2.4F	Connector A 2.4 mm jack (female socket)		Connector B 2.4 mm jack (female socket)	
Connector Part	Material	Finish	Material	Finish
Body	Stainless Steel	Passivated*	Stainless Steel	Passivated*
Center Contact	Beryllium Copper	Gold	Beryllium Copper	Gold
Insulator	Air	-	Air	-

\*Use of stainless steel tools may damage passivated finish.

## ADAPTER PERFORMANCE

Table 3 shows insertion loss and VSWR values for the ADP-2.4F-2.4F adapter at commonly used frequencies. Insertion loss is the loss of signal power (gain) resulting from the insertion of a device in a transmission line. VSWR describes how efficiently power is transmitted through the adapter. A lower VSWR value indicates better performance at a given frequency.

TABLE 3. INSERTION LOSS AND VSWR FOR THE ADP-2.4F-2.4F ADAPTER

Band	Ku	K	Ka	Q
Frequency Range	12 GHz to 18 GHz	18 GHz to 27 GHz	27 GHz to 40 GHz	33 GHz to 50 GHz
Insertion Loss (dB max.)	0.2	1.0	0.8	1.0
VSWR (max.)	1.1	1.2	1.2	1.3

**TABLE 4. MECHANICAL SPECIFICATIONS**

ADP-2.4F-2.4F	Connector A 2.4 mm jack (female socket)	Connector B 2.4 mm jack (female socket)
Mounting Type	Inline, Free-hanging	
Fastening Type	M7 Threaded Coupling	M7 Threaded Coupling
Interface in Accordance with	IEC-61169-40	IEC-61169-40
Durability	500 cycles min.	500 cycles min.
Recommended Torque	8.0 in.-lbs	8.0 in.-lbs
Weight	4.8 g (0.17 oz)	

**TABLE 5. ENVIRONMENTAL SPECIFICATIONS**

ADP-2.4F-2.4F	Connector A 2.4 mm jack (female socket)	Connector B 2.4 mm jack (female socket)
Mounting Type	Inline, Free-hanging	
Fastening Type	M7 Threaded Coupling	M7 Threaded Coupling
Interface in Accordance with	IEC-61169-40	IEC-61169-40
Durability	500 cycles min.	500 cycles min.
Recommended Torque	8.0 in.-lbs	8.0 in.-lbs
Weight	4.8 g (0.17 oz)	

## PACKAGING INFORMATION

The ADP-2.4F-2.4F adapter is placed in an ESD safe plastic bag and sealed in Polyethylene bags of 25 pcs. Four bags (100 pcs.) are packaged in a box. Distribution channels may offer alternative packaging options. Connector ends are protected by a blue LDPE plastic cap.

## TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

## te.com

TE Connectivity, TE, TE connectivity (logo), Linx and Linx Technologies are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2023 TE Connectivity. All Rights Reserved.

1/23 Original

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[ADP-2.4F-2.4F](#)