



EASY-LOCK PLASTIC SIGNAL CONNECTORS (PSC)

TE Connectivity (TE) easy locking plastic signal connectors are designed based on the easy application concept, supports up to 5A current for reliable connections in industrial applications. This solution provides standard IP67 protections, can support machine crimping process to improve the assembly efficiency and provides a virtually error free installation and mating in the field. They support designers to carry various signals from wire gauge AWG18-24 connections.

BENEFITS

- Helps improve mating efficiency and reduce operating time
- Machine crimping supports efficiency
- High reliability helps protect communication
- Wide range of wire selection for customer flexibility
- Helps reduce design complexity and supports consistency
- Quick identification and virtually error-proof matching
- Audible 'click' to provide for the mating accuracy

FEATURES

- Lock latch design
- IP67 protection
- Gold and Tin plated contacts optional
- Similar panel design on 8/12 positions
- 3 different keys design
- UL/TUV/CE qualified

EASY-LOCK PLASTIC SIGNAL CONNECTORS (PSC)

APPLICATIONS

- Battery energy storage system
- Industrial robotics
- Industrial machinery
- Warehouse automation equipment

MECHANICAL

- IP67/quick locking

ELECTRICAL

- 63V/5A (Max)

MATERIALS

- PBT, Brass

STANDARDS

- UL1977, TUV61984

SPECIFICATIONS

- 108-137685

PRODUCT INFORMATION

Part number	Part description	Part number	Part description
2469979-1	EASYLOCK PLASTIC SIGNAL CONN,FE,8P,A KEY	T2210001010-000	DIA1.0 MALE STAMPING CONTACT,AU PLATED
2469979-2	EASYLOCK PLASTIC SIGNAL CONN,FE,8P,B KEY	T2210001010-001	DIA1.0 MALE STAMPING CONTACT,TIN PLATED
2469979-3	EASYLOCK PLASTIC SIGNAL CONN,FE,8P,C KEY	T2210001010-010	DIA1.0 MALE STAMPING CONTACT,AU PLATED
2470002-1	EASYLOCK PLASTIC SIGNAL CONN,M,8P,A KEY	T2210001010-011	DIA1.0 MALE STAMPING CONTACT,TIN PLATED
2470002-2	EASYLOCK PLASTIC SIGNAL CONN,M,8P,B KEY	T2210002010-030	DIA1.0 FEMALE STAMPING CONTACT,AU PLATED
2470002-3	EASYLOCK PLASTIC SIGNAL CONN,M,8P,C KEY	T2210002010-031	DIA1.0 FEMALE STAMPING CONTACT,SN PLATED
2473754-1	SINGLE WIRE SEAL	T2210002010-040	DIA1.0 FEMALE STAMPING CONTACT,AU PLATED
2473754-2	SINGLE WIRE SEAL	T2210002010-041	DIA1.0 FEMALE STAMPING CONTACT,SN PLATED
2473754-3	BLIND PLUG		

te.com

© 2024 TE Connectivity. All Rights Reserved.

TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks owned or licensed by TE Connectivity. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE reserves the right to make any changes to the information contained herein without prior notice. Information contained herein are for reference purposes only and TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. TE assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. Consult TE for the latest dimensions and design specifications.

05/24 AK

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2470002-1](#) [T2210002010-030](#) [2473754-3](#) [T2210002010-040](#) [T2210001010-010](#) [T2210001010-001](#) [T2210001010-011](#) [2470002-3](#) [2469979-1](#) [2469979-2](#) [2470002-2](#) [2469979-3](#) [T2210002010-041](#) [T2210001010-000](#) [2473754-1](#)
[2473754-2](#) [T2210002010-031](#)