


MicroCon

0.8 mm Connectors



MicroCon DUAL ROW 0.8 MM CONNECTOR

The dual-row MicroCon connector series with 0.8 mm pitch is excellent for various demanding applications in the industrial, medical, lighting, automotive and consumer market. Due to the small dimensions - the 50-pin male connectors show dimensions of only 24.2 mm x 4.7 mm with different heights - robustness was crucial during the development. The male connectors are provided with reinforced sidewalls. More secure mating is provided by coding and blind-mate guide alignments, providing an increased locking range. A special feature for this miniaturized device size is the double-sided spring contact. The reliable and high-quality spring contacts are based on a time-tested principle which has been continuously scaled down for smaller dimensions. Parallel (Mezzanine), right angle (90 °) and coplanar configurations are available to support various PCB applications. With different heights for the male and female connectors, Board-to-Board distances from 5 mm to 19 mm can be realized for Mezzanine applications. Despite the miniaturization, the new connectors offer a high mating tolerance with allowed misalignment tolerances of longitudinal and transverse axes of ± 0.7 mm. The allowed angular inclination tolerance is specified with ± 4 degrees. The male and female connectors are available with Surface Mount Technology (SMT) termination. The robust plastic housing of the female connector resists high temperature and is suitable for lead-free reflow soldering. Tape and reel packaging supports automatic assembly.



TECHNICAL DETAILS

Pitch	0.8 mm
No. of Pins	12 - 100 possible
Packaging	Tape and reel for automatic assembly
Current rating per contact	up to 2.3 A at 20 °C
Datarate	up to 3 Gbit/s
Termination technology	SMT
Variants	Vertical male
	Right angle male (available 2023)
	Vertical female
	Right angle female
	Cable assemblies (available 2023)

CAPABILITIES



Stacked boards (Mezzanine)



Extender card (coplanar)



Orthogonal boards



Orthogonal boards



Wire-to-Board (available 2023)



Wire-to-Board (available 2023)

ADVANTAGES

High Reliable Contact Design

- reliable, dual-beam female contact
- rolled, homogeneous surface, provides more secure contact mating
- wide contact surfaces between the mated pairs
- extremely low surface roughness significantly reduces abrasion
- low contact resistance



Polarization / Mating Face

- mating face polarization helps prevent mismating and incorrect connection
- insertion chamfers in the capture range provide more secure mating
- distinctive guide elements for precise insertion



Robust Solder Clips

- outstanding retention forces on the circuit board
- soldering brackets absorb mechanical stress and are able to resist high shock and vibration loads



Lockable Cable Assemblies


- available 2023
- integrated locking lever; can be manually released without tools
- increased protection against accidental release of Wire-to-Board connections
- cable guide provides strain relief



ADVANTAGES

Locating Pegs

- geometrically heterogeneous locating pegs for more precise positioning on the circuit board
- enables excellent compensation of PCB holes for both positive and negative tolerances



Stacked Boards / Mezzanine

Board-to-Board Height	Male Connector Stacking Height	Female Connector Stacking Height
5.00 - 6.00 mm	1 mm	4 mm
6.00 - 7.00 mm	2 mm	4 mm
7.00 - 8.00 mm	1 mm	6 mm
8.00 - 9.00 mm	2 mm	6 mm
9.00 - 10.00 mm	1 mm	8 mm
10.00 - 11.00 mm	2 mm	8 mm
13.00 - 14.00 mm (available 2023)	9 mm (available 2023)	4 mm
14.00 - 15.00 mm (available 2023)	10 mm (available 2023)	4 mm
15.00 - 16.00 mm (available 2023)	9 mm (available 2023)	6 mm
16.00 - 17.00 mm (available 2023)	10 mm (available 2023)	6 mm
17.00 - 18.00 mm (available 2023)	9 mm (available 2023)	8 mm
18.00 - 19.00 mm (available 2023)	10 mm (available 2023)	8 mm



PROCESSING

Tape and Reel Packaging

- transport safe packaging
- automatic assembly



Automatic Assembly and Reflow Soldering

- for efficient processing on modern assembly lines




MATING CONDITIONS

Allowed Inclination for a more Secure Self-Centering



Allowed Misalignment Tolerances for a more Secure Self-Centering



ELECTRICAL AND MECHANICAL CHARACTERISTICS

Technical Data

		Female, Vertical and Right Angle	
Description	Standard	Male, Right Angle	Male, Vertical
Climate category	DIN EN 60068-1 test b	55 / 125 / 56	
Operating temperature		-55 / 125 °C	
Storage conditions * (see page 13)	IEC 60721-3-1	-	1K6
	JDEC-J-STD-020	information will follow	-
Current rating per contact	IEC60512-5-2 Test 5b	16 pin Version 2.82 A at 20 °C 50 pin Version 2.10 A at 20 °C 100 pin Version 1.47 A at 20 °C	
Air- and creepage distance		0.25 mm	
Operating voltage	IEC 60664	The permissible operating voltages depend on the customer application and on the applicable or specified safety requirements. Insulation coordination according to IEC 60664-1 has to be regarded for the complete electrical device. Therefore, the maximum creepage and clearance distances of the mated connectors are specified for consideration as a part of the whole current path. In practice, reductions in creepage or clearance distances may occur due to the conductive pattern of the printed board or the wiring used, and have to be taken into account separately. As a result the creepage and clearance distances for the application may be reduced compared to those of the connector.	
Dielectric strength	IEC 60512 test 4a	contact – contact 500 V _{rms}	
Contact resistance	IEC 60512 test 2a	< 35 mΩ	
Insulation resistance	IEC 60512 test 3a	> 100 MΩ	
Vibration, sine	IEC 60512 test 6d	10 – 2000 Hz 20 g	
Contact disturbance (while vibration test)	IEC 60512 test 2e	< 1 μs	
Shock halfsine	IEC 60512 test 6c	50 g 11 ms	
Contact disturbance (while shock test)	IEC 60512 test 2e	< 1 μs	
Mechanical operation	IEC 60512 test 9a	> 500 mating cycles	
Insertion and withdrawal force	IEC 60512 test 13b	typical value 0.5 N per contact	
Processing Conditions			
Reflow soldering temperature max.	JEDEC J-STD-020	20 - 40 s at 260 °C	
Coplanarity		< 0.1 mm	

ELECTRICAL AND MECHANICAL CHARACTERISTICS


Technical Data

			Female, Vertical and Right Angle
Description	Standard	Male, Right Angle	Male, Vertical
Housing Material			
Insulation body		PPA	LCP
CTI value	IEC 60112	600	175
UL flame rating		UL 94 V-0	
UL file plastic material		E90350	E83005
Contact Material			
Base material		Cu alloy	
Mating area		gold plating	
Termination area		Sn	
Clip Material			
Base material		Cu alloy	
Plating		Sn	

ELECTRICAL AND MECHANICAL CABLE CHARACTERISTICS

Technical Data Flat Ribbon Cables (available 2023)

Description	Standard cable (PVC)
Cross section	AWG-34 / 0.02 mm²
Conductor	solid Cu wire, tinned, 0.02 mm²
Coded wire	available
Insulation	PVC gray (similar to RAL 7032)
Insulation thickness	min. 0.08 mm
Shore hardness	94 ±3 (Shore A)
Bending radius	single: 7.5 x thickness
	multiple: 25 x thickness
Technical Data	
Temperature range	-30/105 °C (fixed)
	-10/105 °C (mobile)
Dielectric strength	500 V _{rms}
Conductor resistance	≤ 980 Ω/km at 20 °C
Insulation resistance	≥ 20 MΩ x km at 20 °C
Impedance	130 Ω (wire-wire)
	80 Ω (Ground-Signal-Ground)
RoHS	compliant
Flame rating	UL 1581 Sec. 1090 (Horizontal Flame Test)
	IEC 60332-2-2




RIGHT ANGLE FEMALE

Product Specification

- SMT termination
- 2 - 100 pins possible
- tape and reel packaging for automatic assembly
- blind mate guide alignment for more secure mating
- for available part numbers please refer to our website




Dimensional Drawings



No. of Contacts	A	B
12	6.00	9.00
16	7.60	10.60
26	11.60	14.60
32	14.00	17.00
40	17.20	20.20
50	21.20	24.20
68	28.40	31.40
80	33.40	36.20
100	41.20	44.20

All dimensions in mm

Recommended Layout




RIGHT ANGLE MALE

Product Specification

- SMT termination
- 2 - 100 pins possible
- tape and reel packaging for automatic assembly
- blind mate guide alignment for more secure mating
- for available part numbers please refer to our website




Dimensional Drawings



No. of Contacts	A	B
12	6.00	9.00
16	7.60	10.60
26	11.60	14.60
32	14.00	17.00
40	17.20	20.20
50	21.20	24.20
68	28.40	31.40
80	33.40	36.20
100	41.20	44.20

All dimensions in mm

Recommended Layout




VERTICAL FEMALE

Product Specification

- SMT Termination
- 2 - 100 pins possible
- various heights up to 8 mm possible
- tape and reel packaging for automatic assembly
- blind mate guide alignment for more secure mating
- for available part numbers please refer to our website



Dimensional Drawings




No. of Contacts	A	B
12	6.00	8.70
16	7.60	10.30
26	11.60	14.30
32	14.00	16.70
40	17.20	19.90
50	21.20	23.90
68	28.40	31.10
80	33.20	35.90
100	41.20	43.90

Stacking height X	C
4	4.60
6	6.60
8	8.60

All dimensions in mm

Recommended Layout




VERTICAL MALE

Product Specification

- SMT Termination
- 2 - 100 pins possible
- various heights up to 2mm (10 mm available 2023) possible
- tape and reel packaging for automatic assembly
- blind mate guide alignment for more secure mating
- for available part numbers please refer to our website



Dimensional Drawings




No. of Contacts	A	B
12	6.00	9.00
16	7.60	10.60
26	11.60	14.60
32	14.00	17.00
40	17.20	19.20
50	21.20	24.20
68	28.40	31.40
80	33.20	36.20
100	41.20	44.20

Stacking height X	C
1	4.80
2	5.80

All dimensions in mm

Recommended Layout






CABLE ASSEMBLIES

Product Specification

- available 2023
- IDC termination
- 2 - 68 pins possible
- various cable lengths possible
- ribbon cable AWG 34
- 90° cable outlet
- blind mate guide alignment for more secure mating



Dimensional Drawings 50 pin version



ADDITIONAL INFORMATION ON STORAGE CONDITIONS

Moisture Sensitivity Level (MSL) relates to the packaging and handling precautions for plastic encapsulated surface mount packages and other packages made with moisture-permeable materials. The MSL is an electronic industry rating that describes how long a potentially moisture sensitive device can be exposed to ambient temperature and humidity conditions (e.g. 30°C and 60% Relative Humidity) prior to being soldered in place. Semiconductor devices absorb moisture and may be damaged during surface mount reflow, when moisture trapped inside the component expands. The expansion of trapped moisture can result in internal cracks or delamination of the plastic. In the most severe case, the component will bulge and pop. This is also known as the so-called „popcorn“ effect.

The parameters for testing of the moisture sensitivity and for the storage and handling of such nonhermetic surface mount devices are defined in the JEDEC J-STD-020 standard.

In general, connectors are different from semiconductor devices, however they undergo the same soldering process and hence need to resist the same temperature requirements. Therefore, ERNI tests the connector devices according to the same MSL test parameters defined for nonhermetic surface mount devices in JEDEC J-STD-020.

To prove the applicability of shelf life conditions and support later solder processability, these MSL tests are accelerated in time by applying higher temperature and humidity. The subsequent exposure to solder heat in the test procedure is performed with higher temperatures than those allowed as the maximum temperature for the actual soldering process.

Usually, plastics materials show moisture absorption parameters with non-negligible dependency of the storage temperature. This circumstance makes modern connector materials like high performance Polyphthalamide (PPA) even more sensitive to moisture absorption under high test-temperature influence. The moisture “soak conditions” in the test procedure is 85°C, whereas the storage temperature is limited to 30°C. In consequence, samples may fail in these MSL tests, although their storage and solder process properties perfectly fit those present in state-of-the-art electronics manufacturing.

The classification of groups of environmental storage conditions from 1k1 to 1k11 is defined in the IEC 60721-3-1 standard. In JEDEC J-STD-020, the floor life conditions are limited to only two groups, either 30°C/85%RH or 30°C/60%RH with respective floor life times of the components. Unfortunately, no exact relation exists between the assumed storage conditions between JEDEC J-STD-020 and IEC 60721-3-1. Under the general assumption that no bedewing of water on the surface of electronic devices during storage takes place, ERNI connectors with PPA plastics material can be stored in those storage conditions with 30°C/60%RH given in the JEDEC J-STD-020 standard without any additional drying or “baking” needs. Hence, although the ERNI connectors with high performance PPA plastics material did not pass the harsh MSL1 test conditions, under normal storage conditions there is no need to pack them in Moisture Barrier Bags (MBB). In consequence, the ERNI connectors can be stored under 30°C/60%RH conditions without drying or MBB packing needs.

Connect With Us

We make it easy to connect with our experts and are ready to provide the support you need. Visit www.te.com/support to chat with a Product Information Specialist.

te.com

2022 TE Connectivity. All Rights Reserved.

TE Connectivity, TE connectivity (logo) ERNI, MicroCon and Every Connection Counts are trademarks owned or licensed by the TE Connectivity family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

074606 03/22 Original

CATALOG

TE Connectivity

ERNI Electronics GmbH & Co. KG
a TE Connectivity Ltd. company
Seestraße 9
73099 Adelberg
Germany

Tel +49 7166 50-0
www.te.com
www.erni.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[294148](#) [294148-E](#)