




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Wire**

Number of Positions: **3**

Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

| | |
|-----------------------------------|--------------|
| Connector Product Type | Housing |
| Connector & Housing Type | Receptacle |
| Connector System | Wire-to-Wire |
| Sealable | No |
| Connector & Contact Terminates To | Wire & Cable |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 3 |
| Number of Rows | 1 |

Electrical Characteristics

| | |
|-------------------|---------|
| Operating Voltage | 250 VAC |
|-------------------|---------|

Body Features

| | |
|-----------------------|----------|
| Connector Profile | Standard |
| Primary Product Color | Natural |

Contact Features

| | |
|--|--|
| | |
|--|--|



| | |
|------------------------------|--------|
| Contact Layout | Inline |
| Contact Type | Socket |
| Contact Current Rating (Max) | 2 A |

Termination Features

| | |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

Mechanical Attachment

| | |
|-------------------------|----------------------------|
| Strain Relief | Without |
| Panel Mount Feature | Without |
| PCB Mount Retention | Without |
| Mating Retention Type | Lock |
| Mating Retention | With |
| Connector Mounting Type | Cable Mount (Free-Hanging) |

Housing Features

| | |
|-----------------------------|------------------|
| Housing Entry Configuration | Both Ends Closed |
| Housing Material | Nylon 66 |
| Centerline (Pitch) | 2.5 mm[.098 in] |

Dimensions

| | |
|------------------|---------|
| Connector Length | 9.4 mm |
| Connector Height | 5.75 mm |

Usage Conditions

| | |
|-----------------------------|--------------------------|
| Operating Temperature Range | -20 – 95 °C[-4 – 203 °F] |
|-----------------------------|--------------------------|

Operation/Application

| | |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Industry Standards

| | |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

| | |
|--------------------|------|
| Packaging Quantity | 1000 |
| Packaging Method | Bag |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|



| | |
|---|--|
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Melamine (3% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | | | |
|--|---|--|---|
|  <div>TE Part # 170205-3 EIS CONTACT LP</div> |  <div>TE Part # 170204-4 170262-4 LP E1CRIMP SNAP IN</div> |  <div>TE Part # 170205-1 E.I. SERIES CONTACT LP</div> |  <div>TE Part # 170204-1 EIS RECPT CONTACT</div> |
|  <div>TE Part # 170205-2 E.I. SERIES CONTACT LP</div> |  <div>TE Part # 170204-2 EIS CONTACT</div> |  <div>TE Part # 172211-3 EIS CAP HSG FREE HANG 3P NATUTURAL</div> |  <div>TE Part # 170263-2 E.I.S. CONTACT</div> |



TE Part # 170262-4
EIS CONNECTOR FORMING

TE Part # 170262-2
EIS CONTACT

TE Part # 170262-1
EIS CONTACT

TE Part # 170263-1
EIS CONTACT

TE Part # 170263-3
EIS CONNECTOR FORMING

TE Part # 170262-3
E.I.S CONTACT

Customers Also Bought

TE Part #1-179553-2
Receptacle and Tab Housing: 5.08 mm Pitch, 250-600V

TE Part #178803-3
Receptacle and Tab Housing: 3.81 mm pitch, 250V

TE Part #1-175218-2
DYNAMIC D-3 REC CONT. L AU 0.38 L /P

TE Part #170204-4
170262-4 LP E1CRIMP SNAP IN

TE Part #770421-1
01P UMNLCAP HSG NATL

Documents

Product Drawings
3P REC HSG CRIMP EI SER
Japanese

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_172486-3_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_172486-3_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_172486-3_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773972-5_EIS_Connectors_Brochure](#)

English

Product Specifications

[Crimping of AMP EI Series Connector Contacts](#)

Japanese

[Application Specification](#)

Japanese

Agency Approvals

[Agency Approval Document](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[172486-3](#)