




Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**  
Ratchet Configuration: **Operator Releasable & Adjustable**  
Die Sets Type: **Removable/Interchangeable**  
Specification Type: **TE Product Specification (114-)**  
TE Certification: **Cannot be Certified**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Other
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	Standard Die Envelope (SDE) Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 354940-1  
PRO-CRIMPER III FRAME W/O DIES




TE Part # 9-1478240-0  
SDE SA PEW12 HAND TOOL FRAME- NO DIES




TE Part # 679304-1  
PNEUMATIC HEAD ASSEMBLY


Customers Also Bought




TE Part #900839-000  
202A121-25/86-0




TE Part #931635-000  
202D132-25/225-0




TE Part #EL7665-000  
TMS-CT-50M-1/2-OUT-9




TE Part #806677-000  
214A032-25-0




TE Part #1053354-1  
2062 0000 00,SMA PCB VERT JACK




TE Part #7-2176398-7  
3502 3R3 5%



TE Part #3-1617758-0  
FCB-205-0122M=M83536/1-022M



TE Part #620001-000  
D-100-00



Documents

Datasheets & Catalog Pages

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1804039-1](#)