



Relays & Contactors > Relays > Power Relays



Power Relay Type: **Standard**

Coil Magnetic System: **Bistable, 1 Coil**

Coil Power Rating DC: **50 mW**

Coil Resistance: **4500  $\Omega$**

Coil Voltage Rating: **15 VDC**

Features

Product Type Features

Power Relay Type	Standard
------------------	----------

Electrical Characteristics

Coil Magnetic System	Bistable, 1 Coil
Coil Power Rating DC	50 mW
Coil Resistance	4500 $\Omega$
Coil Voltage Rating	15 VDC
Contact Switching Load (Min)	10mA @ .02V
Contact Switching Voltage (Max)	125 VDC
Contact Voltage Rating	125 VDC

Contact Features

Contact Arrangement	1 Form C (CO)
Contact Current Class	1 A
Contact Current Rating (Max)	1 A
Contact Material	PdNi+Au
Contact Number of Poles	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------




EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #DTT-20-03  
CRIMP TOOL




TE Part #HDP24-24-16SE-L015  
REC, 16P, BLK, E, THD, 12, S




TE Part #K1007153  
Toggle Switch 08-1-1-13




TE Part #DRC16-70SBE-P013UK  
PLG, 70P, BLK, E, SEAL BOND, B



TE Part #YHDP26-24-35PEL017  
PLG, 35P, BLK, E, RNG, 16/20, P



TE Part #2-2176245-2  
CRGS1206 5% 56R



TE Part #K1002956  
Toggle Switch 08-4-1-13



TE Part #K1008699  
Relay 26-60-05



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-1393776-2\_C.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-1393776-2\_C.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-1393776-2\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Definitions General Purpose Relays

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1393776-2](#)